



REV.	DATE	DRAWN	REVISION
A	29AUG94	JAD	PRN: 62-459
B	29DEC94	BMC/HAR	PRN: 62-466
C	13SEP95	LJI	PRN: 62-503B
D	11OCT96	SWD	PRN: S-93-23
E	22JUN2000	VNI	PRN: PK-31
F	07OCT2004	MJR/MDY	PRN: P2004-1144

ALL DIMENSIONS ARE
IN MILLIMETERS.
ALL DIMENSIONS WITHOUT
TOLERANCES ARE REFERENCE.




GRIP RANGE		INDIVIDUALLY PACKAGED ASSEMBLY PART NUMBER			
MIN-MAX	MIN-MAX	TEXTURED CHROME	POLISHED CHROME	BLACK POWDER COATED	SILVER METALLIC POLYESTER URETHANE POWDER COATED
6 - 16	56 - 66	62-43-101-2	62-43-111-2	62-43-151-2	62-43-161-2
16 - 26	46 - 56	62-43-201-2	62-43-211-2	62-43-251-2	62-43-261-2
26 - 36	36 - 46	62-43-301-2	62-43-311-2	62-43-351-2	62-43-361-2

GRIP RANGE		BULK LAYER PACKED ASSEMBLY PART NUMBER			
MIN-MAX	MIN-MAX	TEXTURED CHROME	POLISHED CHROME	BLACK POWDER COATED	SILVER METALLIC POLYESTER URETHANE POWDER COATED
6 - 16	56 - 66	62-43-101-3	62-43-111-3	62-43-151-3	62-43-161-3
16 - 26	46 - 56	62-43-201-3	62-43-211-3	62-43-251-3	62-43-261-3
26 - 36	36 - 46	62-43-301-3	62-43-311-3	62-43-351-3	62-43-361-3



NOTES

1. THREAD SIZE OF SHAFT IS M8 AND THE SCREW/ LOCKWASHER ASSEMBLY IS M5.
2. THICKER PANELS REQUIRE A LONGER SCREW/ LOCKWASHER COMBINATION (NOT SUPPLIED).
3. ASSEMBLE AS SHOWN AND ROTATE PAWL TO THE DESIRED LATCHING POSITION.
4. PAWL SHOULD BE ADJUSTED TO *GRIP* MEASUREMENT WITH THE DOOR OPEN AND THE LEVER IN THE *LATCHED* POSITION. USE TWO WRENCHES TO TIGHTEN JAM NUTS.
5. FOR MOST EFFECTIVE ENVIRONMENTAL SEALING, USE A CUP GASKET AND SEAL THE MOUNTING SCREW THREADS.



PANEL PREPARATION

MATERIAL AND FINISH

LEVER, HOUSING AND LOCK PLUG: DIE CAST ZINC, SEE TABLE.
SHAFT: 12L14 STEEL, ZINC ALLOY PLATE BRIGHT CHROMATE, PLUS SEALER OR WITH BLACK ORGANIC COATING.
SHAFT O-RING: SYNTHETIC RUBBER, NATURAL
CAM: 1010 STEEL, ZINC ALLOY PLATE BRIGHT CHROMATE, PLUS SEALER OR WITH BLACK ORGANIC COATING.
PIN: 303 STAINLESS STEEL, PASSIVATED.
WASHER: 1010 STEEL, ZINC PLATED BRIGHT OR BLACK OXIDE.
SPRINGS: 302 STAINLESS STEEL, PASSIVATED
BEARING WASHER, PAWL, PAWL RETAINING CLIP & BRACKET: 1010 STEEL, ZINC ALLOY PLATE BRIGHT CHROMATE, PLUS SEALER.
LOCKWASHER: SPRING STEEL, ZINC ALLOY PLATE BRIGHT CHROMATE, PLUS SEALER.
NUTS & SCREW/LOCKWASHER ASS'Y.: LOW CARBON STEEL, ZINC ALLOY PLATE BRIGHT CHROMATE, PLUS SEALER.
CUP GASKET: SYNTHETIC RUBBER, NATURAL
LOCK PLATE: STAINLESS STEEL, PASSIVATED OR BLACK OXIDE.