

2.5x5mm RECTANGULAR SOLID LAMP

WP383IDT

HIGH EFFICIENCY RED


Features

- LOW POWER CONSUMPTION.
- RELIABLE AND RUGGED.
- EXCELLENT UNIFORMITY OF LIGHT OUTPUT.
- SUITABLE FOR LEVEL INDICATOR.
- LONG LIFE SOLID STATE RELIABILITY.
- RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

Package Dimensions



Notes

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25 (0.01")$ unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

SPEC NO: DSAF0510 REV NO: V.2 DATE: APR/21/2005 PAGE: 1 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003861

Kingbright

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) @ 10mA		Viewing Angle
		,	Min. Typ.		201/2
WP383IDT	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	3	5	110°

Note

Electrical / Optical Characteristics at T_A=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	IF=20mA
λD	Dominant Wavelength	High Efficiency Red	625		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	IF=20mA
С	Capacitance	High Efficiency Red	15		pF	VF=0V;f=1MHz
VF	Forward Voltage	High Efficiency Red	2.0	2.5	V	IF=20mA
İR	Reverse Current	High Efficiency Red		10	uA	VR = 5V

Absolute Maximum Ratings at Ta=25°C

Parameter	High Efficiency Red	Units		
Power dissipation	105	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	160	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	ead Solder Temperature [2] 260°C For 3 Seconds			
Lead Solder Temperature [3]	ead Solder Temperature [3] 260°C For 5 Seconds			

Notes:


- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAF0510 REV NO: V.2 DATE: APR/21/2005 PAGE: 2 OF 4

APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003861


^{1.} θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright



SPEC NO: DSAF0510 REV NO: V.2 DATE: APR/21/2005 PAGE: 3 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003861

Kingbright





Remarks

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

1. Wavelength: +/-1nm

2. Luminous Intensity: +/-15%

3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAF0510 REV NO: V.2 DATE: APR/21/2005 PAGE: 4 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003861