



Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Pack Cont.
MAT							
111-92080	MAT8SS7	230	7.0	60	445	SS316	100
111-92120	MAT12SS7	330	7.0	90	445	SS316	100
111-92160	MAT16SS7	430	7.0	120	445	SS316	100
111-92240	MAT24SS7	630	7.0	180	445	SS316	100
111-93080	MAT8SS12	230	12.0	60	445	SS316	100
111-93120	MAT12SS12	330	12.0	90	445	SS316	100
111-93160	MAT16SS12	430	12.0	120	445	SS316	100
111-93240	MAT24SS12	630	11.7	180	670	SS316	100

All Dimensions in mm. Subject to technical changes.

