## Safety Relay SR6 D/M

- 4 pole safety relay with either 2 NO+2 NC or 3 NO+1 NC contacts
- Forcibly guided contacts according to EN 50205
- Rated current 8 A
- High insulation distances for safe separation of electrical circuits

## Applications

Emergency shut-off, press control, machine control, elevator and escalator control, safety modules




## Approvals


REGNr. 128935, c Sus E214024, Grad 968/EL 350.03/06	
Technical data of approved types on request	

### Contact data

Contact configuration	3 NO contacts and 1 NC contact
	or
	2 NO contacts and 2 NC contacts
Contact set	single contact, forcibly guided
	type A according to EN 50205
Type of interruption	micro disconnection
Rated voltage / max. switching voltage AC	250 / 400 VAC
Rated current	8 A
Maximum breaking capacity AC	2000 VA
Contact material	AgSnO <sub>2</sub>
Minimum contact load	10 mA / 5 V
Contact resistance	≤ 100 mOhm / 1 A / 24 VDC
	≤ 20 Ohm / 10 mA / 5 VDC
Rated frequency of operation with / without load	6 min <sup>-1</sup> / 150 min <sup>-1</sup>







**Coil operating range DC** 

# SR61 NOSR61 NO\*) load on one pole

<u>1 NO</u>

EN60947-5-1

Contact ratings

Type Contact Load\*)

Coil data
-----------

Rated coil voltage range DC coil	5110 VDC
Operative range to IEC 61810	2

IEC 947-5-1 (AC15) utilization category 250 VAC / 5 A

IEC 947-5-1 (DC13) utilization category 24 VDC / 6 A

#### Coil versions, DC-coil

Coil	Rated	Operate	Release / Reset	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDČ	VDC	VDČ	Ohm	mW
005	5	3.8	0.5	21±10%	1190
006	6	4.5	0.6	30±10%	1200
009	9	6.8	0.9	68±10%	1191
012	12	9.0	1.2	120±10%	1200
018	18	13.5	1.8	270±10%	1200
021	21	15.8	2.1	368±10%	1198
024	24	18.0	2.4	480±10%	1200
036	36	27.0	3.6	1080±10%	1200
040	40	30.0	4.0	1333±10%	1200
048	48	36.0	4.8	1920±10%	1200
060	60	45.0	6.0	3000±12%	1200
110	110	82.5	11.0	10080±12%	1200
				1 1 S S	

All figures are given for coil without preenergization, at ambient temperature +23°C Other coil voltages on request

Datasheet Rev. HK1 Issued 2008/11 www.tycoelectronics.com www.schrackrelays.com

Dimensions are in mm unless otherwise specified and are shown for reference purposes only.

Product specification according to IEC 61810-1. Product data, technical parameters, test conditions and

Ambient

temp. [°C

23°C

23°C

Cycles

6,050

6,050

processing information only to be used together with the 'Definitions' section in the catalogue or at schrackrelays.com

.I voltage (U/U<sub>rtd</sub>) 1

Coil

1,0 U<sub>rto</sub>

0,8

0,6 -20

S0402-F

0

+20

in the 'Schrack' section.

Recommended

+40

+60

Ambient temperature [°C]

+80

1

voltage range


Specifications subject to change.

## Safety Relay SR6 D/M (Continued)


Insulation				
Dielectric strength coil-contact circuit	3000 V <sub>rms</sub>			
open contact circuit	1500 V <sub>rms</sub>			
adjacent contact circuits	3000 / 4000 V <sub>rms</sub> (in longitudinal direction)			
Clearance / creepage coil-contact circuit	≥ 5.5 / 5.5 mm			
adjacent contact circui	ts ≥ 5.5 / 5.5 mm			
	$\geq$ 15 / 15 mm (in longitudinal direction)			
Material group of insulation parts	Illa			
Tracking index of relay base	PTI 250			
Insulation to IEC 61810-1				
Type of insulation coil-contact circuit	basic			
open contact circui	t micro disconnection			
adjacent contact ci	rcuits reinforced (in longitudinal dir)			
Rated insulation voltage	250 V			
Pollution degree	2			
Rated voltage system	230 / 400 V			
Overvoltage category	III			
Insulation to EN 50178				
Type of insulation coil-contact circuit	reinforced			
adjacent contact ci	rcuits reinforced			
Other data				
Mechanical endurance	10x10 <sup>6</sup> cycles			
Material	Tox to cycles			
RoHS - Directive 2002/95/EC	compliant as per product date code 0407			
Environment	· · · ·			
Ambient temperature range	-25+70°C			
Vibration resistance (function) NO / NC contact > 8 / 2.5 g, 10200 Hz				
Shock resistance (function) NO / NC	contact $> 10 / 2.5$ g, 16 ms half sine			
Category of protection	RT III <sup>1)</sup>			
Processing				
Resistance to soldering heat	260°C/5s			
Relay weight	30 g			
Packaging unit	10 pcs			
<sup>1</sup> ) please contact technical support for washing para	ameters			

## PCB layout / terminal assignment Bottom view on solder pins

## 2 NO+2 NC versions




3 NO + 1 NC version



## Dimensions

Accessories PCB socket and hold down clip



contact technical support

Dimensions are in mm unless otherwise specified and are shown for reference purposes only. Product specification according to IEC 61810-1. Product data, technical parameters, test conditions and

processing information only to be used together with the 'Definitions' section in the catalogue or at schrackrelays.com in the 'Schrack' section.

2

Specifications subject to change.

## Safety Relay SR6 D/M (Continued)

Typical product key	SR6	D	4	012
	Typical product key	Typical product key SR6	Typical product key SR6 D	Typical product key SR6 D 4

Other types on request

Product key	Туре	Contact configuration	Contact material	Coil	Part number
SR6D4012	4-pole	2 NO + 2 NC	AgSnO <sub>2</sub>	12 VDC	1415078-1
SR6D4018	safety relay	contacts	-	18 VDC	7-1415354-1
SR6D4021				21 VDC	8-1415353-1
SR6D4024				24 VDC	6-1415027-1
SR6D4040				40 VDC	9-1415366-1
SR6D4110				110 VDC	1415062-1
SR6M4006		3 NO + 1 NC		6 VDC	6-1415053-1
SR6M4012		contacts		12 VDC	7-1415353-1
SR6M4018				18 VDC	1415354-1
SR6M4021				21 VDC	6-1415353-1
SR6M4024				24 VDC	3-1415353-1
SR6M4110				110 VDC	1-1415354-1

in the 'Schrack' section.

3

Specifications subject to change.