



# Tubes

## Tubes, test, with rim, medium wall **PYREX®**

- High quality test tubes designed and constructed for optimum performance
- **Manufactured from Pyrex® borosilicate glass which gives superior performance to neutral borosilicate and soda-lime glass**
  - Allows use at high temperatures
  - Excellent resistance to chemical attack
- Conforms to ISO 4142



Catalogue number	Dimensions OD x length mm	Wall thickness mm
1620/02M	10 x 75	1.0
1620/04M	12 x 75	1.0
1620/06M	12 x 100	1.0
1620/09M	16 x 100	1.2
1620/10M	16 x 125	1.2
1620/12M	16 x 150	1.2
1620/14M	16 x 160	1.2
1620/15M	18 x 180	1.2
1620/16M	18 x 150	1.2
1620/20M	24 x 150	1.2
1620/22M	24 x 200	1.2

**i** For advice on the safe heating of Pyrex® glassware, please refer to the Technical Information Section on page 14.

## Tubes, test, with rim, heavy wall **PYREX®**

- Test tubes with a heavy wall to provide extra mechanical strength
- **Robust construction reduces possibility of breakages:**
  - Lower replacement costs
  - Improved user safety
- Pyrex® borosilicate glass for high resistance to thermal shock and chemical attack
- Conforms to ISO 4142

Catalogue number	Dimensions OD x length mm	Wall thickness mm
1624/02M	10 x 75	1.5
1624/04M	12 x 75	1.5
1624/06M	12 x 100	1.5
1624/10M	16 x 125	1.8
1624/12M	16 x 150	1.8
1624/16M	18 x 150	1.8
1624/20M	24 x 150	1.8