VALVE-REGULATED LEAD ACID BATTERIES: INDIVIDUAL DATA SHEET

LC-R067R2P



Specifications

| Nom | 6V | | |
|---------------------------------|-----------------------|-------------------------|--|
| Rated Capa | 7.2Ah | | |
| Dimensions | Length | 5.945 inches (151.0 mm) | |
| | Width | 1.339 inches (34.0 mm) | |
| | Height | 3.702 inches (94.0 mm) | |
| | Total Height* | 3.937 inches (100.0 mm) | |
| Арј | 2.78 lbs. (1.26 kg) | | |
| Standard Terminals and Resin | UL94HB Faston 187 | LC-R067R2P | |
| | UL94HB Faston 250 | LC-R067R2P1 | |
| Optional Terminals and Resin | UL94HB Faston 187/250 | ♦ LC-R067R2P2 | |

[♦] Please contact Panasonic for availability on optional items. Optional items may be subject to minimum order quantities.


Characteristics

| Capacity ^(note) 77°F (25°C) | | 20 hour rate (3650mA) 10 hour rate (680mA) 5 hour rate (1260mA) 1 hour rate (4900mA) | 7.2Ah 6.8Ah 6.3Ah 4.9Ah |
|---|---------------------------------|---|--------------------------------------|
| | | 1.5 hour rate discharge Cut-off voltage 5.25 V | 3.5A |
| Internal Resistance | | Fully charged battery 77°F (25°C) | Approx. 20mΩ |
| Temperature | | 104°F (40°C) | 102% |
| dependency | | 77°F (25°C) | 100% |
| of capacity | | 32°F (0°C) | 85% |
| (20 hour rate) | | 5°F (-15°C) | 65% |
| Self discharge 77°F (25°C) | | Residual capacity after standing 3 months | 91% |
| | | Residual capacity after standing 6 months | 82% |
| | | Residual capacity after standing 12 months | 64% |
| Charge Method (Constant Voltage) | Cycle use (Repeating use) | Initial current | 2.88 A or smaller |
| | | Control voltage | 7.25V to 7.45V (per 6V cell 25°C) |
| | Trickle use | Initial current | 1.08 A or smaller |
| | | Control voltage | 6.8V to 6.9V (per 6V cell 25°C) |


(Note) The above characteristics data are average values obtained within three charge/discharge. Cycles not the minimum values.

For main and standby power supplies. Expected trickle life: 3-5 years at 25°C, Approx. 5 years at 20°C.

Dimensions (mm)



Discharge characteristics 77°F (25°C) (Note)



Duration of discharge vs. Discharge current (Note)

