International Rectifier

30BQ060

SCHOTTKY RECTIFIER

3 Amp

 $I_{F(AV)} = 3.0 Amp$ $V_R = 60 V$


Major Ratings and Characteristics

| Characteristics | 30BQ060 | Units |
|---|-------------|-------|
| I _{F(AV)} Rectangular waveform | 3.0 | А |
| V_{RRM} | 60 | V |
| I _{FSM} @t _p =5μs sine | 1200 | А |
| V _F @3.0 Apk, T _J = 125°C | 0.52 | V |
| T _J range | - 55 to 150 | °C |

Description/ Features

The 30BQ060 surface-mount Schottky rectifier has been designed for applications requiring low forward drop and small foot prints on PC boards. Typical applications are in disk drives, switching power supplies, converters, free-wheeling diodes, battery charging, and reverse battery protection.

- Small foot print, surface mountable
- Very low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability





Voltage Ratings

| F | Part number | 30BQ060 |
|--|-----------------------------|---------|
| V _R N | Max. DC Reverse Voltage (V) | 60 |
| V _{RWM} Max. Working Peak Reverse Voltage (V) | | |

Absolute Maximum Ratings

| | Parameters | 30BQ | Units | Conditions | |
|--------------------|-------------------------------------|------|-------|---|--|
| I _{F(AV)} | Max. Average Forward Current | 3.0 | Α | A 50% duty cycle @ T _L = 123 °C, rectangular wave | |
| | | 4.0 | | 50% duty cycle @ $T_L = 113 ^{\circ}C$, | rectangular wave form |
| I _{FSM} | Max. Peak One Cycle Non-Repetitive | 1200 | Α | 5μs Sine or 3μs Rect. pulse | Following any rated load condition and |
| | Surge Current @ $T_C = 25^{\circ}C$ | 130 | | 10ms Sine or 6ms Rect. pulse | with rated V _{RRM} applied |
| E _{AS} | Non Repetitive Avalanche Energy | 5.0 | mJ | $T_J = 25 ^{\circ}\text{C}, I_{AS} = 1.0\text{A}, L = 10\text{mH}$ | |
| I _{AR} | Repetitive Avalanche Current | 1.0 | Α | Current decaying linearly to zer Frequency limited by T ₁ max. V | |

Electrical Specifications

| | Parameters | 30BQ | Units | Conditions | |
|-----------------|----------------------------------|-------|-------|---|---------------------------------------|
| V _{FM} | Max. Forward Voltage Drop (1) | 0.58 | V | @ 3A | T _J = 25 °C |
| | | 0.76 | V | @ 6A | |
| | | 0.52 | V | @ 3A | T _J = 125 °C |
| | | 0.66 | V | @ 6A | |
| I _{RM} | Max. Reverse Leakage Current (1) | 0.5 | mA | T _J = 25 °C | V _R = rated V _R |
| | | 20 | mA | T _J = 125 °C | |
| C _T | Max. Junction Capacitance | 180 | pF | V _R = 5V _{DC} (test signal range 100KHz to 1Mhz) 25°C | |
| L _s | Typical Series Inductance | 3.0 | nH | Measured lead to lead 5mm from package body | |
| dv/dt | Max. Voltage Rate of Change | 10000 | V/µs | (Rated V _R) | |


⁽¹⁾ Pulse Width < 300µs, Duty Cycle < 2%

Thermal-Mechanical Specifications

| | Parameters | 30BQ | Units | Conditions |
|-------------------|---|-------------|---------|---------------------|
| T _J | Max. Junction Temperature Range (*) | -55 to 150 | °C | |
| T _{stg} | Max. Storage Temperature Range | - 55 to 150 | °C | |
| R _{thJL} | Max. Thermal Resistance Junction to Lead (**) | 12 | °C/W | DC operation |
| R _{thJA} | Max. Thermal Resistance Junction to Ambient | 46 | °C/W | DC operation |
| wt | Approximate Weight | 0.24(0.008) | g (oz.) | |
| | Case Style | SMC | | Similar to DO-214AB |
| | Device Marking | IR3H | | |

 $[\]frac{\text{(*)}}{\text{dTj}} < \frac{\text{dPtot}}{\text{Rth(j-a)}} < \frac{1}{\text{Rth(j-a)}} \quad \text{thermal runaway condition for a diode on its own heatsink}$

^(**) Mounted 1 inch square PCB






Fig. 4 - Maximum Average Forward Current Vs. Allowable Lead Temperature






Fig. 5 - Maximum Average Forward Dissipation Vs. Average Forward Current




(Microsec)
Fig. 6 - Maximum Peak Surge Forward Current Vs. Pulse Duration

(2) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$; $Pd = Forward Power Loss = I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D) \text{ (see Fig. 6)}$; $Pd_{REV} = Inverse Power Loss = V_{R1} \times I_R (1 - D); I_R @ V_{R1} = 80\% \text{ rated } V_R$


Outline Table




Marking & Identification



Tape & Reel Information



Ordering Information Table



Data and specifications subject to change without notice. This product has been designed and qualified for Industrial Level.

Qualification Standards can be found on IR's Web site.



IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
Visit us at www.irf.com for sales contact information. 07/04