

## JCK30 Series



- 2:1 Input Range
- High Power Density
- Single and Dual Outputs
- High Efficiency – Up to 92%
- Remote On/Off
- 1600 VDC Isolation
- 3 Year Warranty

## Specification

## Input

Input Voltage Range	<ul style="list-style-type: none"> <li>• 12 V (9-18 VDC), 24 V (18-36 VDC), 48 V (36-75 VDC)</li> </ul>
Input Current	<ul style="list-style-type: none"> <li>• See table</li> </ul>
Undervoltage Lockout	<ul style="list-style-type: none"> <li>• 12 V models: ON 8.6 V, OFF 7.9 V typical</li> <li>• 24 V models: ON 17.8 V, OFF 16 V typical</li> <li>• 48 V models: ON 33.5 V, OFF 30.5 V typical</li> </ul>
Input Surge	<ul style="list-style-type: none"> <li>• 12 V models 25 VDC for 100 ms</li> <li>• 24 V models 50 VDC for 100 ms</li> <li>• 48 V models 100 VDC for 100 ms</li> </ul>

## Output

Output Voltage	<ul style="list-style-type: none"> <li>• See table</li> </ul>
Output Voltage Trim	<ul style="list-style-type: none"> <li>• <math>\pm 10\%</math> on single outputs models only</li> </ul>
Minimum Load	<ul style="list-style-type: none"> <li>• No minimum load required</li> </ul>
Line Regulation	<ul style="list-style-type: none"> <li>• <math>\pm 0.5\%</math> max</li> </ul>
Load Regulation	<ul style="list-style-type: none"> <li>• Single output models: <math>\pm 0.5\%</math> max</li> <li>• Dual output models: <math>\pm 1\%</math> max balanced outputs</li> </ul>
Cross Regulation	<ul style="list-style-type: none"> <li>• <math>\pm 5\%</math>, see note 2</li> </ul>
Setpoint Accuracy	<ul style="list-style-type: none"> <li>• <math>\pm 1\%</math></li> </ul>
Start Up Time	<ul style="list-style-type: none"> <li>• 30 ms typical</li> </ul>
Ripple & Noise	<ul style="list-style-type: none"> <li>• 100 mV or 1% pk-pk, whichever is greater, 20 MHz bandwidth, see note 3</li> </ul>
Transient Response	<ul style="list-style-type: none"> <li>• 3% max deviation, recovery to within 1% in <math>&lt; 250 \mu\text{s}</math> for a 25% load change</li> </ul>
Temperature Coefficient	<ul style="list-style-type: none"> <li>• <math>0.02\%/^{\circ}\text{C}</math></li> </ul>
Overvoltage Protection	<ul style="list-style-type: none"> <li>• 3.3 V models: 3.9 V typical</li> <li>• 5 V models: 6.2 V typical</li> <li>• 12 V models: 15 V typical</li> <li>• 15 V models: 18 V typical</li> <li>• <math>\pm 5</math> V models: <math>\pm 6.2</math> V typical</li> <li>• <math>\pm 12</math> V models: <math>\pm 15</math> V typical</li> <li>• <math>\pm 15</math> V models: <math>\pm 18</math> V typical</li> </ul>
Overload Protection	<ul style="list-style-type: none"> <li>• <math>&gt; 150\%</math></li> </ul>
Short Circuit Protection	<ul style="list-style-type: none"> <li>• Trip &amp; restart (Hiccup mode), auto recovery</li> </ul>
Remote On/Off	<ul style="list-style-type: none"> <li>• On = Logic High (<math>&gt; 3.0</math>) or Open</li> <li>• Off = Logic Low (<math>&lt; 1.2</math> V) or short pin 2 to 3</li> </ul>

## General

Efficiency	<ul style="list-style-type: none"> <li>• See table</li> </ul>
Isolation	<ul style="list-style-type: none"> <li>• 1600 VDC Input to Output</li> <li>• 1600 VDC Input to Case</li> <li>• 1600 VDC Output to Case</li> </ul>
Isolation Capacitance	<ul style="list-style-type: none"> <li>• 1500 pF typical</li> </ul>
Switching Frequency	<ul style="list-style-type: none"> <li>• 330 kHz typical</li> </ul>
MTBF	<ul style="list-style-type: none"> <li>• 430 kHrs min to MIL-HDBK-217F at <math>25^{\circ}\text{C}</math>, GB</li> </ul>

## Environmental

Operating Temperature	<ul style="list-style-type: none"> <li>• <math>-40^{\circ}\text{C}</math> to <math>+75^{\circ}\text{C}</math>, see derating curve</li> </ul>
Case Temperature	<ul style="list-style-type: none"> <li>• <math>+105^{\circ}\text{C}</math> max</li> </ul>
Cooling	<ul style="list-style-type: none"> <li>• Convection-cooled</li> </ul>
Operating Humidity	<ul style="list-style-type: none"> <li>• 5-95% RH, non-condensing</li> </ul>
Storage Temperature	<ul style="list-style-type: none"> <li>• <math>-40^{\circ}\text{C}</math> to <math>+125^{\circ}\text{C}</math></li> </ul>

## Models and Ratings


Input Voltage	Output Voltage	Output Current	Input Current <sup>(1)</sup>		Maximum Capacitive Load	Efficiency	Model Number
			No Load	Full Load			
9-18 VDC	3.3 V	8.00 A	80 mA	2426 mA	20000 µF	89%	JCK3012S3V3
	5.0 V	6.00 A	120 mA	2874 mA	14000 µF	91%	JCK3012S05
	5.1 V	6.00 A	110 mA	2874 mA	14000 µF	92%	JCK3012S5V1
	12.0 V	2.50 A	50 mA	2809 mA	2000 µF	91%	JCK3012S12
	15.0 V	2.00 A	50 mA	2809 mA	2000 µF	92%	JCK3012S15
	±5.0 V	±3.00 A	180 mA	2874 mA	±3000 µF	89%	JCK3012D05
	±12.0 V	±1.25 A	50 mA	2874 mA	±1300 µF	90%	JCK3012D12
	±15.0 V	±1.00 A	60 mA	2874 mA	±1300 µF	91%	JCK3012D15
18-36 VDC	3.3 V	8.00 A	60 mA	1185 mA	20000 µF	91%	JCK3024S3V3
	5.0 V	6.00 A	100 mA	1420 mA	14000 µF	92%	JCK3024S05
	5.1 V	6.00 A	90 mA	1448 mA	14000 µF	92%	JCK3024S5V1
	12.0 V	2.50 A	30 mA	1436 mA	2000 µF	92%	JCK3024S12
	15.0 V	2.00 A	30 mA	1420 mA	2000 µF	92%	JCK3024S15
	±5.0 V	±3.00 A	120 mA	1437 mA	±3000 µF	90%	JCK3024D05
	±12.0 V	±1.25 A	30 mA	1453 mA	±1300 µF	91%	JCK3024D12
	±15.0 V	±1.00 A	40 mA	1437 mA	±1300 µF	91%	JCK3024D15
36-75 VDC	3.3 V	8.00 A	50 mA	593 mA	20000 µF	90%	JCK3048S3V3
	5.0 V	6.00 A	60 mA	710 mA	14000 µF	91%	JCK3048S05
	5.1 V	6.00 A	60 mA	710 mA	14000 µF	91%	JCK3048S5V1
	12.0 V	2.50 A	30 mA	718 mA	2000 µF	91%	JCK3048S12
	15.0 V	2.00 A	30 mA	718 mA	2000 µF	91%	JCK3048S15
	±5.0 V	±3.00 A	70 mA	710 mA	±3000 µF	90%	JCK3048D05
	±12.0 V	±1.25 A	30 mA	718 mA	±1300 µF	90%	JCK3048D12
	±15.0 V	±1.00 A	40 mA	718 mA	±1300 µF	90%	JCK3048D15

### Notes

1. Input current specified at nominal input.
2. Cross regulation for duals is ±5% when one output is at 100% and the other is varied between 25% and 100%.
3. Measured with 1 µF ceramic capacitor across output rails.

## Mechanical Details

Weight: 0.07 lbs (30 g) approx




PIN CONNECTIONS		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	Com	Com
6	Trim	-Vout

### Notes

1. All dimensions are in inches (mm).
2. Pin diameter: 0.04 ±0.002 (1.0 ±0.05)
3. Pin pitch tolerance: ±0.014 (±0.35)
4. Case tolerance: ±0.02 (±0.5)

## Application Notes

### Derating Curve



### Remote On/Off Control

- Output On >3.0 VDC or open circuit
- Output Off <1.2 VDC or short circuit pins 2 & 3

### Input Filter

