

HAND CRIMPING TOOLS (WITH CONTROLLED CALIBRATING DEVICES)

The Davico range of hand crimping tools has been selected to comply with all variations to customer specification and have the added advantage of compressing other manufacturers terminals.



DHCR 10	Triple Jaw Ratchet Tool with controlled calibration suitable for crimping miniature insulated terminals 0.05 to 2.55 sq. mm.
DHCR 15	Triple Jaw Ratchet Indent Tool with controlled calibration suitable for crimping 0.25 to 6 sq. mm insulated terminals.
DHCR 1516	Four Jaw Ratchet Tool for with controlled calibration suitable for crimping 1.5 to 16 sq. mm Davico copper tube terminals.
DHCRF 15	Triple Jaw Ratchet Tool with controlled calibration suitable for crimping non insulated male/female disconnect terminals with 'F' crimp configuration.
DHCRF 025	Double Jaw Ratchet Tool with controlled calibration suitable for 'F' crimp type miniature terminals/pins 0.102 to 0.25 sq. mm.
DHCRF 05	Double Jaw Ratchet Tool with controlled calibration suitable for 'F' crimp type miniature terminals 0.12 to 0.5 sq. mm.
DCER 510	Six Jaw Ratchet Tool with controlled calibration suitable for crimping insulated and non insulated cord end terminals 0.5 to 10 sq. mm.
DCER 1635	Triple Jaw Ratchet Tool with controlled calibration suitable for crimping non insulated and insulated cord end terminals 16, 25 and 35 sq. mm.
DHCR - HS	Triple Jaw Ratchet Tool with controlled calibration suitable for crimping insulated heat shrink prior to application of heat gun. The compression ratio has no detrimental effect on the heatshrink insulation 0.25 to 6 sq. mm.
DHCR - FL	Double Jaw Ratchet Tool with controlled calibration suitable for crimping fully insulated nylon right angle flag terminals 0.25 to 2.5 sq. mm.
DHCR - CA	Ratchet Tool for co-axial cables with controlled calibration jaw sets RG58/RG59 but other sets are available.

THE ABOVE TOOLS CAN BE CALIBRATED MANUALLY AND PROVED IN ACCORDANCE WITH ALL INTERNATIONAL STANDARDS