

Professional Torque Wrench Model 5

The Model 5 is a torque wrench that offers high accuracy and the convenience of interchangeable 1/4 in. hexagon bits. (ISO 1173:1988 Form C drive bits).


- Accuracy of $\pm 3\%$ of reading exceeds all torque wrench standards.
- Traceable calibration certificate supplied, to satisfy ISO9000:2000 quality systems.
- Non Length dependent. The Model 5 remains accurate regardless of hand position.
- Supplied in a storage case. The case allows space for the storage of additional drive bits and optional stepless ratchet.



Production 'P' Types


The 'P' type version prevents unauthorised alteration of torque setting. No external calibration equipment is required to set the Model 5 'P' Type.

Coloured end seals are provided to identify the wrench to a particular operator, torque setting or calibration period.



Model 5 'P' Type

Adjustable Torque Wrenches



Model	Units	Square Drive	Part No.	Range	Length	Weight
		in			mm	kg
5	N.m	1/4	13001	1-5 N.m	170	0.12
5	lbf.in	1/4	13002	10-50 lbf.in	170	0.12
5	kgf.cm	1/4	13003	10-50 kgf.cm	170	0.12



Optional stepless ratchet (Part No. 13122)

'P' Type Torque Wrenches

Model	Units	Square Drive	Part No.	Range	Length	Weight
		in			mm	kg
5 'P'	N.m	1/4	13004	1-5 N.m	154	0.12
5 'P'	lbf.in	1/4	13005	10-50 lbf.in	154	0.12
5 'P'	kgf.cm	1/4	13006	10-50 kgf.cm	154	0.12