



ITEM NUMBER: 5702S

CIRCUIT PROTECTION

SENTRY

ENCLOSURES IP65 WEATHERPROOF ENCLOSURE

CARTON QUANTITY: 1

5702s
Weatherproof
Complete with neutral and
earth terminal block
Accepts up to 4 modules

These enclosures will accommodate two or four
module Sentry RCDs or a combination of Sentry
modules, excluding contactors.

Dimensions:
5702s: 200 x 123 x 112mm
(width x height x depth)

Degree of Protection to
BS EN 60529: 1992
5702s: IP65
Precautions must be taken to maintain the IP rating.
eg. correct use of cable glands and knockouts

IP65 enclosures to EN 60670

[Click here to view the Honeywell privacy statement](#)

Site designed & developed by viplondon



Skeleton Units

FOR MOUNTING IN A
MANTEL/CLIFTON TYPE
ENCLOSURE



6000s



6001s

Enclosures

IP65
WEATHERPROOF
ENCLOSURE



5702s



5502s



K5592s



5704s



5504s



5604s

IP30 ENCLOSURE

Switch
Disconnectors
Double Pole

TWO MODULE



5500s



5560s

MCBs
Single PoleTYPE B
ONE MODULE

5903s



5906s



5910s



5916s

6000s

ACCEPTS 14
ONE MODULE PRODUCTS
(1 INTEGRAL NEUTRAL BAR)

6001s

100A SWITCH DISCONNECTOR
AND 63A 30mA RCD.
ACCEPTS A FURTHER 10
ONE MODULE PRODUCTS
IN ANY CONFIGURATION OF
RCD PROTECTED
AND UNPROTECTED CIRCUITS
BETWEEN 2/8 AND 8/2

These units are suitable for use in
most Mantel and Clifton type
enclosures.

Factory assembled units are available
for specific installations.

DIMENSIONS:

	WIDTH	HEIGHT	DEPTH
6000s:	222 x	333 x	90mm
6001s:	222 x	333 x	90mm

Degree of Protection to
BS EN 60529: 1992 IP30

Precautions must be taken to maintain
the IP rating, eg. correct use of cable
glands and knockouts.

BS EN 60439-3: 1994

1**5702s**

WEATHERPROOF
COMPLETE WITH NEUTRAL AND
EARTH TERMINAL BLOCK
ACCEPTS UP TO 4 MODULES

1**5704s**

WEATHERPROOF
COMPLETE WITH NEUTRAL AND
EARTH TERMINAL BLOCK
ACCEPTS UP TO 8 MODULES

Typical applications for enclosures
are house extensions, garages and
small workshops.

These enclosures will accommodate
two or four module Sentry RCDs or
a combination of Sentry modules,
excluding contactors.

DIMENSIONS:

	WIDTH	HEIGHT	DEPTH
5702s:	200 x	123 x	112mm
5704s:	200 x	195 x	112mm
5502s:	149 x	76 x	76mm
5504s:	188 x	121 x	74mm
5604s:	160 x	85 x	68mm
K5592s:	185 x	119 x	66mm

Degree of Protection to
BS EN 60529: 1992

5702s: IP65
5704s: IP65
5502s: IP30
5504s: IP30
5604s: IP30
K5592s: IP30

1**5502s**

INSULATED COMPLETE WITH
MOUNTING RAIL, NEUTRAL
AND EARTH TERMINALS
TWO MODULE

1**K5592s**

RCBO ENCLOSURE – METAL
TWO AVAILABLE MODULES
SUITABLE FOR LIST NOS.
6932s, 6933s, 6934s, 6935s,
6936s, 6937s, 6938s
WITH MOUNTING RAIL,
EARTH TERMINALS AND
METAL FRONT PLATE

1**5504s**

METAL
WITH MOUNTING RAIL,
EARTH TERMINALS AND
MOULDED FRONT PLATE
FOUR MODULE

1**5604s**

INSULATED
WITH MOUNTING RAIL,
TWO INTEGRAL BLANKING PLATES
AND TAMPER-PROOFING
COMPONENTS
FOUR MODULE

1

K5592s suitable for Sentry Single
Module RCBO.

Precautions must be taken to
maintain the IP rating, eg. correct
use of cable glands and knockouts
IP65 enclosures to EN 60670

5500s
100A 230V

5560s
63A 230V

Suitable for installation in Sentry
Consumer Units and two or four
module enclosures. Accepts direct
to busbar or cable-in / cable-out
connection. Category of duty:
AC22A for switching of resistive
and inductive loads.

Positive contact status indication in
accordance with 16th Edition IEE
Wiring Regulations
(537-02-03 and 537-03-02)

DIMENSIONS:
81 x 36 x 76mm

CABLE CAPACITY:
50mm²

BS EN 60947-3: 1992

5

5903s
3A 230V

5

5906s
6A 230V

5910s
10A 230V

5916s
16A 230V

Suitable for installation in Sentry
Consumer Units and two or four
module enclosures.

Positive contact status indication in
accordance with 16th Edition IEE
Wiring Regulations
(537-02-03 and 537-03-02)

DIMENSIONS:
83 x 18 x 74mm

CABLE CAPACITY:
3, 6, 10, 16A: 35mm²

Short-circuit breaking capacity: 6KA

BS EN 60898: 1991

10**10****10****10**