


成型尺寸	公差
5mm 以下	±0.2
5~20mm	±0.3
20~40mm	±0.4
40~60mm	±0.5
60~100mm	±0.8
100mm 以上	±1.0

REVISIONS			
REV	DESCRIPTION	DATE	BY



PART NO	A
4-2	2.0
4-3	3.0
4-4	4.0
4-4.83	4.83
4-5	5.0
4-6	6.0
4-7	7.0
4-7.5	7.5
4-8	8.0
4-9	9.0
4-9.5	9.5
4-10	10.0
4-11	11.0
4-12	12.0
4-12.7	12.7
4-13	13.0
4-14	14.0
4-15	15.0

PART NO	A
4-16	16.0
4-17	17.0
4-18	18.0
4-19	19.0
4-20	20.0
4-21	21.0
4-22	22.0
4-23	23.0
4-24	24.0
4-25	25.0
4-26	26.0
4-27	27.0
4-28	28.0
4-28.7	28.7
4-29	29.0
4-30	30.0
4-40	40.0

QMF22 Component - Plastics
 E I DUPONT DE NEMOURS & CO INC
 ENGINEERING POLYMERS CHESTNUT RUN PLAZA PO BOX 80713 WILMINGTON DE 19880

Wednesday, September 15, 2004

B41938

Material Designation: 101(+)(X)(F), 101R(+)(X)(F), 101L(+)(X)(F), E101(+)(X)(F), E101L(F), 132P(+)(X)(F), 135P(+)(X)(F)
 Product Description: Polyamide 66 (PA66), designated "Zytel" furnished as pellets.

Color	Min. Thick. (mm)	Flame Class	HWI	HAI	RTI Elec	RTI Imp	RTI Str	IBC GWIT	IBC GWFI
ALL	0.71	V-2	4	0	130	75	85	725	960
	1.5	V-2	3	0	130	75	85	750	960
	3	V-2	2	0	130	75	85	800	960
	6	V-2	2	0	130	75	85	800	960
CTI: 0		HVTR: 0			D495: 6				

Dielectric Strength (kV/mm): 13
 ISO Tensile Strength (MPa):
 ISO Tensile Impact (kJ/m²):
 Volume Resistivity (10¹²ohm-cm): 14
 ISO Physical Strength (MPa):
 ISO Heat Deflection (°C):
 ISO Charpy Impact (kJ/m²):

(+) Virgin and regrind up to 50% by weight inclusive, have the same basic material characteristics.
 (F) Suitable for outdoor use with respect to exposure to Ultraviolet Light, Water Exposure and Immersion in accordance with UL 746C.

NOTE (1) Material designations that are color pigmented may be followed by suffix letters and numbers. (2) Material designations may be prefixed by "ZYT" or "MIN" or "ZEN" or "DEL" or "CRA" or "RYN".

Report Date: 7/29/1996

Underwriters Laboratories Inc®

UL 94 small-scale test data does not pertain to building materials, furnishings and related contents. UL 94 small-scale test data is intended solely for determining the flammability of plastic materials used in components and parts of end-product devices and appliances, where the acceptability of the combination is determined by ULI.

<p>康揚企業股份有限公司 KANG YANG HARDWARE ENTERPRISE CO., LTD. 東莞康揚塑膠五金電子廠 DONG GUAN KANG YANG PLASTIC HARDWARE COMPANY 康哲電腦配件(吳江)有限公司 KANG CHEE COMPUTER COMPONENTS(WUJIANG) CO.,LTD.</p>	TITLE 圓體間隔柱		產品規格圖面	
	MATERIAL NYLON 66 UL94V-2		DATE 2001.11.13	
	FINISH		DRAWN AMY	
	COLOR NATURAL		CHECK 陳明得	
PART NUMBER SEE ABOVE	DRAWING NUMBER 4-H		UNLESS OTHERWISE SPECIFIED TOLERANCE SEE ABOVE	
SIZE A4	SCALE NONE	UNIT mm	REV A	APPROVED Kang