


- Rated insulation voltage:  
AC 250V.
- Rated current: 16A
- Cable section: 2.5mm<sup>2</sup>
- Type of conductor:  
flexible only.
- Number of poles: 3



## General informations

ITW code:	Date:	<b>16/01/2006</b>
Type/model <b>PA 244 S</b>	P.D. (project development):	<b>4498</b>
Description: <b>Terminal Block - NEW PA244</b>		

## Technical data

Rated insulation voltage:	<b>AC V</b>	<b>250</b>
Rated current:	<b>A</b>	<b>10 - 25</b>
Wire size:	<b>mm<sup>2</sup></b>	<b>3x0,75 - 3x2,5</b>
Total poles:	<b>n°</b>	<b>3</b>
Male tabs:	<b>mm</b>	<b>6,3x0,8 (two for each pole)</b>
Working temperature:	<b>°C</b>	<b>110</b>
Type of wire / cable clamp capab.:		<b>flexible / 11 mm</b>
Glow wire test (GWFI)	<b>°C</b>	<b>850</b>
Traking test (PTI):	<b>V</b>	<b>&gt;250</b>
Protection degree:	<b>IP</b>	<b>30</b>
Kind of connection:		<b>Only for fixed usage</b>

## Possible raw materials used

Producer:	<b>BASF</b>	<b>EURONIL</b>	<b>RADICI</b>
Tradename:	<b>A3W</b>	<b>Nilamid AXP 156</b>	<b>RDF A AE 131 C</b>
Flame class (UL 94):	<b>V2</b>	<b>V2</b>	<b>V0</b>
Glow wire test (GWFI):	<b>850</b>	<b>850</b>	<b>850</b>
Glow wire test (GWIT):	<b>775 5 sec.</b>	<b>750 2 sec.</b>	<b>750 2 sec.</b>
CTI (sol. A):	<b>&gt;600</b>	<b>250-399</b>	<b>250-399</b>

## Similar products with homologation:

Type:	<b>PA 244</b>	<b>PA 244 N</b>
Licenze n°:	<b>121360 (VDE) - CA02.00715/EG912 (IMQ)</b>	
What does it change?	<b>Plastic box, contact geometry and screws.</b>	

## Image:

