

DM7408

Quad 2-Input AND Gates


General Description

This device contains four independent gates each of which performs the logic AND function.

Features

Alternate Military/Aerospace device (5408) is available.
 Contact a Fairchild Semiconductor Sales
 Office/Distributor for specifications.

Connection Diagram



Order Number 5408DMQB, 5408FMQB, DM5408J, DM5408W or DM7408N See Package Number J14A, N14A or W14B

Function Table

$$Y = AB$$

Inputs		Output		
Α	В	Y		
L	L	L		
L	Н	L		
Н	L	L		
н	Н	Н		

H = High Logic Level L = Low Logic Level **Absolute Maximum Ratings** (Note 1)

Supply Voltage 7V Input Voltage 5.5V

DM54 and 54 DM74 Storage Temperature Range -55°C to +125°C 0°C to +70°C -65°C to +150°C

Operating Free Air Temperature Range

Recommended Operating Conditions

Symbol	Parameter	DM5408			DM7408			Units
		Min	Nom	Max	Min	Nom	Max	
V _{cc}	Supply Voltage	4.5	5	5.5	4.75	5	5.25	V
V _{IH}	High Level Input Voltage	2			2			V
V _{IL}	Low Level Input Voltage			0.8			0.8	V
I _{OH}	High Level Output Current			-0.8			-0.8	mA
I _{OL}	Low Level Output Current			16			16	mA
T _A	Free Air Operating Temperature	-55		125	0		70	°C

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Electrical Characteristics

over recommended operating free air temperature range (unless otherwise noted)

Symbol	Parameter	Conditions		Min	Тур	Max	Units	
					(Note 2)			
V _I	Input Clamp Voltage	V _{CC} = Min, I _I =	–12 mA			-1.5	V	
V _{OH}	High Level Output	V _{CC} = Min, I _{OH} = Max		2.4	3.4		V	
	Voltage	V _{IL} = Max						
V _{OL}	Low Level Output	V _{CC} = Min, I _{OL} = Max			0.2	0.4	V	
	Voltage	V _{IH} = Min	V _{IH} = Min					
I _I	Input Current @ Max	V _{CC} = Max, V _I = 5.5V				1	mA	
	Input Voltage							
I _{IH}	High Level Input Current	V _{CC} = Max, V _I	V _{CC} = Max, V _I = 2.4V			40	μΑ	
I _{IL}	Low Level Input Current	V _{CC} = Max, V _I	$V_{CC} = Max, V_I = 0.4V$			-1.6	mA	
I _{os}	Short Circuit	V _{CC} = Max	DM54	-20		-55	mA	
	Output Current	(Note 3)	DM74	-18		-55		
I _{CCH}	Supply Current with	V _{CC} = Max	•		11	21	mA	
	Outputs High							
I _{CCL}	Supply Current with	V _{CC} = Max			20	33	mA	
	Outputs Low							


Switching Characteristics

at V_{CC} = 5V and T_A = 25°C (See Section 1 for Test Waveforms and Output Load)

Symbol	Parameter	Conditions	Min	Max	Units
t _{PLH}	Propagation Delay Time	C _L = 15 pF		27	ns
	Low to High Level Output	$R_L = 400\Omega$			
t _{PHL}	Propagation Delay Time			19	ns
	High to Low Level Output				


Note 2: All typicals are at $V_{CC} = 5V$, $T_A = 25^{\circ}C$.

Note 3: Not more than one output should be shorted at a time.



www.fairchildsemi.com

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



14-Lead Ceramic Flat Package (W) Order Number 5408FMQB or DM5408W Package Number W14B

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DE-VICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMI-CONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Fairchild Semiconductor Corporation Americas

Customer Response Center

Tel: 1-888-522-5372

Fairchild Semiconductor Europe

Fax: +49 (0) 1 80-530 85 86

Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 8 141-35-0
English Tel: +44 (0) 1 793-85-68-56
Italy Tel: +39 (0) 2 57 5631

Fairchild Semiconductor Hong Kong Ltd. 13th Floor, Straight Block, Ocean Centre, 5 Canton Rd. Tsimshatsui, Kowloon

Hong Kong Tel: +852 2737-7200 Fax: +852 2314-0061

National Semiconductor Japan Ltd. Tel: 81-3-5620-6175 Fax: 81-3-5620-6179

www.fairchildsemi.com