

PRODUCT SPECIFICATION

GP Powerbank Smart 2 Model: GPPB14BSSA

Revision History

Revision	Date	Initiator	Reason for Change
00	9 September 2003	Bonnie lau	New release
01	10 August 2007	Ivy So	New Smart 2 replace for existing one

Prepared By	Approved By
Ivy So	Iris Lai
Date: 10 Aug 07	Date: 10 Aug 07

GPI International Limited

Gold Peak Building, 8/F, 30 Kwai Wing Road, Kwai Chung, New Territories, Hong Kong. Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com


Website: http://www.gpbatteries.com




Product Specification

Model No.: GPPB14BSSA







NOTE: It is safe to charge GP NiMH batteries continuously with GP PowerBank Smart 2.

Product Name : GP PowerBank Smart 2

Description : One Hour Battery Charger (with external adaptor)

Input Voltage : AC100-240V 50/60Hz

Input Power : 18W Max.

Application : For charging 1 to 4 pcs NiMH batteries

(DO NOT mix AA and AAA size batteries in the same channel.)

Output Voltage : DC12V/1.5A

Charging Current : AA/NiMH 2000mA \pm 10% AAA/NiMH 1000mA \pm 10% Trickle Charge Current : AA/NiMH 160mA \pm 10% AAA/NiMH 60mA \pm 10%

Charging Time (1-4 pcs)

NiMH				
Size	Battery	Time(mins)		
AA	2500 series	~70		
AA	2300 series	~65		
AA	2100 series	~60		
AAA	950 series	~60		
AAA	850 mAh	~60		
AAA	750 mAh	~60		

Termination methods : $-\Delta V$ 0-5mV; Temperature cutoff 55°C ± 5°C; Safety timer 95 mins.

MTBF : 30000 hours (at ambient temperature 25°C)

Operating Temperature : 0°C to 45°C Storage Temperature : -20°C to 45°C


Charge Indicator : LED for each channel; Orange LED ON for charging in process; LED OFF for fully

charged; LED FLASH for primary or damaged batteries.

Dimensions : 115(L) X 80(W) X 31.5(T)mm

Approval : CE

Warranty Period : 12 months from ex-factory date



Unit: mm