

# SPECIAL ELECTRONIC PLIERS EUROline-Conductive

## CUTTING PLIERS

| ALL S |        |        |        | cuttin    | cutting capacity mm Ø |        |   |
|-------|--------|--------|--------|-----------|-----------------------|--------|---|
| No.   | Length | Finish | Medium | Hard      | Piano-                | Weight |   |
|       | mm     | inches |        | hard wire | wire                  | wire   | g |

#### Carbide mini side cutters EUROline-Conductive

for continuous heavy work, with inserted carbide cutting edges, only for tough nickel and electrode wires

| Omy for to | agirinokoi | aria oroc | otrodo wrios                                |             |     |     |    |
|------------|------------|-----------|---|-------------|-----|-----|----|
| 3-661-15   | 5 120      | 4 3/4     | with side face<br>very slim<br>rounded head | 1.2         | 1.0 | 0.6 | 60 |
| 3-663-15   | 120        | 4 3/4     | with side face<br>very slim pointed         | 0.6<br>head | 0.5 |     | 60 |
|            |            |           | with special flat co                        |             | е   |     |    |

#### Carbide oblique top cutters EUROline-Conductive

for continuous heavy work, with inserted carbide cutting edges, cutting plane 29° angular, for horizontal and vertical use, only for tough nickel and electrode wires

| 3-667-15 115 | 4 1/2 | without side face   | 0.6 | 0.5 | 0.3 | 65 |
|--------------|-------|---------------------|-----|-----|-----|----|
| 0 001 10     | , , – | With loat orde lace | 0.0 | 0.0 |     |    |

#### Glas fibre mini side cutters EUROline-Conductive

for continuous heavy work, with inserted carbide cutting edges, with special side face, for cutting glass fibre only, max. Ø 2.0 mm

4 3/4 3-665-15 120 very slim rounded head 60

## ROUND, FLAT, SNIPE MOSE PLIERS

| No. | Length    | Finish | Weight |
|-----|-----------|--------|--------|
|     | mm inches |        | g      |

#### Round nose pliers EUROline-Conductive

extremely slim

60 3-681-15 130 5 1/8 short plain jaws

### Flat nose pliers EUROline-Conductive

extremely slim

| 3-682-15 | 130 5 <sup>1</sup> / <sub>8</sub> | short plain jaws             | 60 |
|----------|-----------------------------------|------------------------------|----|
| 3-688-15 | 130 5 <sup>1</sup> / <sub>8</sub> | short, ultra slim plain jaws | 60 |

#### Snipe nose pliers EUROline-Conductive

extremely slim

| Criticity Cilit |     |                                      |   |    |
|-----------------|-----|--------------------------------------|---|----|
| 3-683-15        | 130 | 5 1/8                                | short plain jaws  | 55 |
| 3-685-15        | 140 | 5 1/2                                | long plain jaws   | 65 |
| 3-686-15        | 140 | 5 1/2                                | long serrated jaws  | 65 |
| 3-687-15        | 130 | 5 <sup>1</sup> / <sub>8</sub> for pr | short plain jaws, <b>ultra slim pointed</b> ecise handling of tiny components | 60 |

