


10mm Pitch **18 Pole** Rising Clamp Terminal


Features

- Unique 18 pole strip
- Easily cut to required number of poles
- Can be supplied pre-cut
- 1 pole in 10mm & 15mm length
- Moulded in grey UL94-V0 flame retardant Lexan
- Professional rising clamp terminals
- 4mm² cable entry
- cUL, UL, VDE, & CE approved
- Guided pin alignment
- Captive screws
- Anti solder wicking terminals



Type No.	Poles	Length
CTB8000/1	1	10mm
CTB8000/1/15	1	15mm
CTB8000/2	2	15mm
CTB8000/3	3	25mm
CTB8000/4	4	35mm
CTB8000/5	5	45mm
CTB8000/6	6	55mm
CTB8000/7	7	65mm
CTB8000/8	8	75mm
CTB8000/9	9	85mm
CTB8000/10	10	95mm
CTB8000/11	11	105mm
CTB8000/12	12	115mm
CTB8000/18	18	175mm

CTB8000 Series



Specification

Rating	17.5A/750V
Dielectric strength	≥ 2.5kV/60sec
Insulation resistance	≥ 5MΩ
Working temperature	-20°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant Lexan
Pin/terminal	5μ tinned, nickel plated brass
Rising clamp	Zinc plated steel
Screw/torque	M2.5 steel, 6μ zinc colour passivated and tropicalised/0.4Nm
Recommended PCB hole size	ø1.3mm

10mm Pitch **18 Pole 90°** Rising Clamp Terminal


Features

- Unique 18 pole strip
- Easily cut to required number of poles
- Can be supplied pre-cut
- 1 Pole in 10mm & 15mm length
- Moulded in grey UL94-V0 flame retardant Lexan
- Professional rising clamp terminals
- 4mm² cable entry
- cUL, UL, VDE, & CE approved
- Guided pin alignment
- Captive screws
- Anti solder wicking terminals



Type No.	Poles	Length
CTB8050/1	1	10mm
CTB8050/1/15	1	15mm
CTB8050/2	2	15mm
CTB8050/3	3	25mm
CTB8050/4	4	35mm
CTB8050/5	5	45mm
CTB8050/6	6	55mm
CTB8050/7	7	65mm
CTB8050/8	8	75mm
CTB8050/9	9	85mm
CTB8050/10	10	95mm
CTB8050/11	11	105mm
CTB8050/12	12	115mm
CTB8050/18	18	175mm

CTB8050 Series



Specification

Rating	17.5A/750V
Dielectric strength	≥ 2.5kV/60sec
Insulation resistance	≥ 5MΩ
Working temperature	-20°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant Lexan
Pin/terminal	5μ tinned, nickel plated brass
Rising clamp	Zinc plated steel
Screw/torque	M2.5 steel, 6μ zinc colour passivated and tropicalised/0.4Nm
Recommended PCB hole size	ø1.3mm