

Leak Detector Spray

Gas leak detection system in aerosol form.

Specially formulated fluid, designed specifically to identify even the smallest, positive pressure, gaseous leak. ROCOL Leak Detector Spray leaves a thin uniform film of surface-active agents that accurately identify any leaks or bleeding of joints.

Features

- Suitable for use with most gases.
- Low chlorine content to ensure maximum plastic compatibility.
- Compatible with most metals and plastics.
- Aerosol enables fast and easy application.
- Convenient and accurate in difficult to reach areas.
- No wastage or spillage.
- For use by CORGI registered Gas Installers.
- Meets the requirements of BS EN14291:2004 - (Foam producing solutions for leak detection on gas installations).
- Meets the product specification given in IGE/UP/1B Edition 2.
- Meets the oxygen compatibility requirements of MIL-PRF-25567E.

Directions for Use

- Shake can well before use.
- Spray from a distance of 25 to 30 cm onto the area to be tested.
- Bubbles in the applied film indicate the location of a leak.
- Test compatibility with painted or coated surfaces, plastics and rubbers prior to application.
- BS EN14291:2004 states that leak detection products should be rinsed off plastic and copper pipes after testing.

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Leak Detector Spray

Appearance	Clear liquid
Base type	Aqueous blend of surfactants
Viscosity range (Brookfield)	60 – 80 cPs
Chloride content	<3 ppm
Ammonia content	<1 ppm
Propellant	CO ₂
Flash point	None
Suitable for use with these common industrial gases	
	Natural & Town Gas
	Compressed air
	Butane / propane
	Acetylene
	Chlorine gas
	Hydrogen
	Oxygen
Storage	Storage area should be out of direct sunlight. Storage temperature should be kept below 50 °C.
Pack sizes	300ml - p/c 32030

T +44 (0) 113 232 2600
 F +44 (0) 113 232 2740
 E customer-service@rocol.com
 www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
 Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001
 Certificate No. FM 12448



BS EN ISO 14001
 Certificate No. EMS 67596



OHSAS 18001
 Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.