


# GP Batteries

## Data Sheet

Model No.: GP357


|                          |   |
|--------------------------|---|
| Description              | : Silver Oxide High Drain Button Cell   |
| Nominal Voltage          | : 1.55Volts   |
| Nominal Dimensions       | : Ø11.60mm×5.40mm   |
| Application              | : calculator, hearing aid, lighter, .<br>electronic toys, camera, etc.  |
| Average Weight           | : 2.3g  |
| Date Code                | : Unless otherwise specified, each cell<br>Will carry a numeric year code and an<br>alphabetical month code.  |
| Shelf Life               | : Not less than 90% of the service<br>capacity within first year. , not less<br>than 85% of the service capacity with<br>third year storage at 22 ± 3 °C<br>year storage at 22 ± 3 °C<br>40-80 %RH. |
| Close Circuit Voltage    | : 1.30 Volts (min.)(load resistor 100Ω<br>at 22 ± 3 °C for 0.1 to 2 seconds)  |
| Nominal Service Life     | : 165hrs (at 1.5kΩ load)<br>(to 1.2V at 22 ± 3 °C)      230days(at 50 kΩ load)  |
| Average Service Capacity | : 165mAh(at 6.2kΩ load)<br>(to 1.2V at 22 ± 3 °C)   |

### Typical Discharge characteristics at 22 ± 3 °C



### Cross References:

| IEC  | JIS  | Eveready | Panasonic | Sony   | Duracell | Varta |
|------|------|----------|-----------|--------|----------|-------|
| SR44 | SR44 | 357      | SP357     | SR44SW | D357     | V357  |



\* The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

