




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION FEB ,2004.  
 © COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
		C		ECR-06-021506	12OCT06	JMS	FWK

- NOTES:**
- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
  - 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
  - 3 Au PLATING
  - 4 Ni PLATING
  - 5 ELECTRICAL CHARACTERISTICS  
 FREQUENCY RANGE: 50 Ohm DC - 4 GHz  
 75 Ohm DC - 2 GHz  
 INSULATION RESISTANCE: 5000 MOhm  
 WORKING VOLTAGE: 500 Volts RMS at Sea Level  
 DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max  
 CONTACT RESISTANCE:  
 CENTRE CONTACT: 1.50 mOhm Max  
 OUTER CONTACT: 0.20 mOhm Max
  - 6 MECHANICAL CHARATERISTICS  
 MOUNT NUT RECOMMENDED TORQUE: 4N  
 DURABILITY: 50 Cycles Min
  - 7 ENVIRONMENTAL CHARACTERISTICS  
 OPERATING TEMPERATURE: -65 to +85 DegC
  - 8 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
  - 9 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



QTY	QTY	QTY	QTY	MATERIAL	DESCRIPTION	ITEM
1	1	1	1	PHOSPHER BRONZE	CONTACT	5
1	1	-	-	TPX	INSULATION	4
-	-	1	1	TPX	INSULATION	3
1	1	1	1	PTFE	INSULATION	2
1	1	1	1	ZINC ALLOY	BODY	1
5--3	5--2	5--1	5--0			
				MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 25FEB04	Tyco Electronics Corporation Bideford EX39 4HE	
DIMENSIONS: mm		CHK S.PARLOW 25FEB04		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F.WHEELER-KING 25FEB04	NAME BNC ELBOW BULKHEAD PCB SOCKET LOW PROFILE 50 & 75 OHMS - DIECAST	
0 PLC ± -		PRODUCT SPEC -	SIZE A3 CAGE CODE 00779 DRAWING NO C-1634556 RESTRICTED TO -	
1 PLC ± -		APPLICATION SPEC -	SCALE NTS SHEET 1 OF 1 REV C	
2 PLC ± -		WEIGHT -		
3 PLC ± -		CUSTOMER DRAWING		
4 PLC ± -				
ANGLES ± -				
FINISH -				