


CPWplus Industrial Scales



"The Affordable Choice"

CPWplus Industrial Scales

"The Affordable Choice"

The CPWplus is a multi-purpose industrial scale.

- Stainless steel weighing pan with remote indicator
- Large backlit LCD display
- Simple 4 button operation
- Portable with battery power
- Kg/lb/oz/lb:oz switchable
- Tare function
- Mains power adapter and wall mounting kit for display included as standard
- RS-232 bi-directional Interface

SPECIFICATIONS

Model	CPWplus 6	CPWplus 15	CPWplus 35	CPWplus 75	CPWplus 150	CPWplus 200
Maximum capacity	6000g	15kg	35kg	75kg	150kg	200kg
Readability	2g	5g	10g	20g	50g	
Tare range	Full					
Repeatability	2g	5g	10g	20g	50g	
Linearity (±)	4g	10g	20g	40g	100g	
Typical stabilisation time	2 Sec					
Units of measure	kg, lb, oz, lb:oz					
Interface	RS-232 bi-directional Interface					
Operating temperature	0° - 40°C / 32° - 104°F					
Power supply	6 AA size non-rechargeable batteries in a compartment located in the base or 12VAC 150mA from external adapter					
Calibration	Automatic External with user selectable calibration mass					
Display	LCD with minimum 25mm digits with weight legends for kg, lb, oz and low battery, stable, zero, net weight and hold symbols, as well as ability to display lb and oz together					
Housing	Indicator- Aluminium, Platform- Mild Steel base and stainless steel pan					
Pan size	300x300mm					
Overall dimensions (wxdxh)	300x300x50mm					
Net weight	4kg					



Optional Accessories:

- Carry Case
- Adam Printer



Adam Equipment have offices in the UK, USA, South Africa and China

www.adamequipment.com