


Customers:		Edition: A	Revision: 0	
Customer Part No.:		BCc Part No.: D561K20Y5PH63L2R		
Rated Voltage: 100 VDC	Test Voltage: 250 VDC	12NC:	Qualification: IEC	
Capacitance: 560.00pF	Tolerance: ± 10%	Cap.Range: 504.00pF To 616.00pF		
DF/Q: 2.5% MAX	At 1KHZ/1.0VRMS	Temp.chart./coefficient: Y5P	Operating Temp.: -30℃ to 125℃	
Coating: Phenolic	SPQ: 1000PCS	Insulation Resistance: 10G Ω MIN AT 100 VDC		
Marking: <div style="text-align: center;"> <u>561</u> </div>		Dimensions(mm)		
		D-Body Diameter: 5.00 MAX		
		T-Body Thickness: 3.50 MAX		
		F-Lead Spacing: 2.50±0.80		
		V-S Spacing: NA		
		L-Lead Length: 30.00±5.00		
		SH-Seat Height: NA		
		DR-Run Down: 1.50 MAX		
		ED-Disc Exposure: NA		
		K-Kink Off: NA		
Resistance to Soldering Heat: 260±5℃,10±1s		θ-Kink Angle: NA		
Packing: Bulk		Lead Style: L		
Taping Specifications(mm)				
Pitch between Components	P			
Feed-hole Pitch	P0			
Feed-hole Diameter	D0			
Height to Seating Plane	H0			
Top of Component Height	H1			
Carrier Tape Width	W			
Remarks/Customers specific requirements:				