

→ Millennium power supply

- With a switch mode power supply, regulated and protected against overloads and short-circuits, these new power supply units are easily integrated in switchboards and enclosures.
- The potentiometer can be used to set the output voltage between 100 and 120% to compensate for any voltage drops on the line.
- The LED continuously signals the presence of voltage at the output and, when flashing, triggering of the self-protection.



PS 24-60 W

Part numbers

Type	Nominal output voltage	Nominal power	Code
PS	12 V ~	22 W	88950300
	24 V ~	30 W	88950301
	24 V ~	60 W	88950302

General characteristics

Environmental characteristics

Conformity to standards

EN 50081-1
EN50082-1
IEC 950

Certifications

UL-CSA, TÜV

Electrical characteristics

Input voltage 100 → 240 V ~ single-phase

Supply frequency range 50/60 Hz (+4%/-6%), or 47→ 53 Hz/ 57→ 63Hz

Output voltage (V) Adjustable from 100 → 120%

Technology Primary switch mode electronic power supplies

Short-circuit protection Yes

Overload protection Yes

Primary protection 1 A gG fuse for 88950300 and 88950301
3 A gG fuse for 88950302

Reset after overload Automatic

Mechanical characteristics

Status indication LED at the output

Mounting DIN rail EN 50022

Dimensions (mm)

PS

