

DC925KB

129-3353



18 Volt 13 mm Heavy Duty Hammerdrill/Driver

Features

- Powerful 18 Volt combination tool for heavy duty hammerdrilling and screwdriving applications
- 22 position adjustable torque control for uniform results and optimised precision when screwdriving
- Up to 56 Nm of sustained torque for maximum performance
- 13 mm self-tightening chuck tightens throughout operation providing superior bit gripping strength
- Three speed settings for optimum performance in high torque, normal use and high speed applications.
- Ergonomically designed trigger and rubber grip
- Electronic brake for added control
- High performance fan cooled motor with replaceable brushes for maximum power and durability
- All metal gearing for efficient power transmission and longer tool life
- Modular design for easy access to key components and serviceability

Specifications Voltage	18 V
Chuck Capacity	1.5-13 mm
Battery	NiMH 2.6 Ah
Power Output	450 Watts
No Load Speed	0-450 / 0-1500 / 0-2000 rpm
Beats per Minute	0-7650 / 0-25500 / 0-34000 bpm
Max. Drilling Capacity [Wood]	50 mm
Max. Drilling Capacity [Metal]	13 mm
Max. Drilling Capacity [Masonry]	16 mm
Weight	2.8 kg
Length	270 mm
Height	245 mm

Standard

- 30 minute charger
- 2 batteries
- Multi position side handle
- Heavy duty carrying case