

DATA SHEET



PART NO: T 2593ST

ISSUE NO: 1

CATALOGUE NO: AD-0500300RBS


CUSTOMER NO: N/A

DESCRIPTION 5Vdc Regulated 300mA UK Plugtop Adaptor



INPUT VOLTS	230Vac
FREQUENCY	50Hz
MAG CURRENT (max.)	50mA
O/P VOLTS NO LOAD	
O/P VOLTS NO LOAD	5.1Vdc
O/P VOLTS	
O/P CURRENT	
O/P VOLTS	5Vdc
O/P CURRENT	300mA
FLASH TEST	3.75KV
OUTPUT CONNECTOR	6 Way
OUTPUT POLARITY	Either
LEAD LENGTH	1.8mtr
APPROVALS	N/A
LENGTH	78.6mm
DEPTH	43.9mm
WIDTH	52.7mm
WEIGHT	330 grams

LABELLING:




MATERIAL : PVC SHEET

BASE : BLACK COLOUR

WORDS : WHITE COLOUR

SIZE : 32.6 x 32.6mm

SCHEMATIC:



C1 = 1000uF 16V
 C2 = 22uF 16V
 C3 = 0.01uF 50V