

max. 13.5 m³/h

DC Axial Fans

Series 400 40 x 40 x 20 mm



Highlights:

- Compact fan with low power consumption.
- Some models suitable for use at high ambient temperatures.

General characteristics:

- Material: fiberglass-reinforced plastic. Impeller PA, housing PBT.
- Fully integrated electronic commutation.
- Protected against reverse polarity and blocking.
- Electrical connection via single leads AWG 28, TR 64. Stripped and tinned ends.
- Blowing over struts. Rotational direction CCW looking at rotor.
- Mass: 27 g.

Nominal Data		Air Flow	Air Flow	Nominal Voltage	Voltage Range	Noise	Sound Power	Sinter-Sleeve Bearings Ball Bearings	Power Input	Nominal Speed	Temperature Range	Service Life L ₁₀ (20 °C) ebm-papst Standard	Service Life (60 °C) ebm-papst Standard	Life expectancy L _{10Δ} (40 °C)	Curve	Specials
Type		m ³ /h	CFM	V DC	V DC	dB(A)	Bel	□/■	Watt	min ⁻¹	°C	Hours	Hours	Hours		
405		10.0	5.9	5	4.5...5.5	18	3.8	■	0.9	6 000	-20...+70	50 000 / 20 000	62 500	62 500	1	/2
412		10.0	5.9	12	10...14	18	3.8	■	0.9	6 000	-20...+70	50 000 / 20 000	62 500	62 500	1	/2;/39
412 H		13.5	7.9	12	10...14	29	4.7	■	1.6	8 100	-20...+60	45 000 / 15 000	47 500	47 500	2	/39
414		10.0	5.9	24	20...28	18	3.8	■	1.0	6 000	-20...+70	50 000 / 20 000	62 500	62 500	1	/2
414 H		13.5	7.9	24	20...26.5	29	4.7	■	1.6	8 100	-20...+60	45 000 / 15 000	47 500	47 500	2	/2
Model with Temperature range up to +85 °C.																
NEW 412-099		10.0	5.9	12	10...14	18	3.8	■	0.8	6 000	-20...+85	50 000 / 20 000	62 500	62 500	1	

