




ISS	ZONE	DESCRIPTION\PER REQUEST\DATE

1	2	3	4	5	6	7	8



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. BRASS PER QQ-B-613
3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
4. PHOSPHOR BRONZE PER QQ-B-750
5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
6. PTFE - MIL-P-19468

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DRAWING NO.
1	LOCK RING	NOTE 2	NOTE 3	1	B7700-4
2	CONTACT PIN	NOTE 4	NOTE 5	1	B7700-3
3	INSULATOR	NOTE 6	NATURAL	1	B7700-27-50-B
4	BODY	NOTE 1	NOTE 3	1	B7700-1-A

DIMENSIONS ARE IN MILLIMETERS		PART NO. B6251C1-NT3G-50	
UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVED	
0.5-6 = ±0.2	6-30 = ±0.4	DATE 10-11-01	
30-120 = ±0.6	120-315 = ±1	CHECKED	
315-1000 = ±1.6	1000-2000 = ±2.4	DATE 10-11-01	
SCALE 4/1		ISSUE A	
FILE NO.		DRAWN	
DATE 10-11-01		DATE 10-11-01	

TITLE	
BNC P.C. MOUNT RECEPT, JACK	
DRAWING NO. KU-B6251C1-NT3G-50	
ITEM NO.	

Amphenol

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DRAWING NO.
1	LOCK RING	NOTE 2	NOTE 3	1	B7700-4
2	CONTACT PIN	NOTE 4	NOTE 5	1	B7700-3
3	INSULATOR	NOTE 6	NATURAL	1	B7700-27-50-B
4	BODY	NOTE 1	NOTE 3	1	B7700-1-A

DIMENSIONS ARE IN MILLIMETERS		PART NO. B6251C1-NT3G-50	
UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVED	
0.5-6 = ±0.2	6-30 = ±0.4	DATE 10-11-01	
30-120 = ±0.6	120-315 = ±1	CHECKED	
315-1000 = ±1.6	1000-2000 = ±2.4	DATE 10-11-01	
SCALE 4/1		ISSUE A	
FILE NO.		DRAWN	
DATE 10-11-01		DATE 10-11-01	

TITLE	
BNC P.C. MOUNT RECEPT, JACK	
DRAWING NO. KU-B6251C1-NT3G-50	
ITEM NO.	

Amphenol