



WIRE SIZE	MAX INSULATION	"A" ±.012 ±0.30	"C" ±.012 ±0.30	"D" ±.005 ±0.13	"E" ±.012 ±0.30	"G" ±.005 ±0.13	"H" ±.012 ±0.30
20-24	.073/1.85	.090/2.29	.100/2.54	.030/0.76	.075/1.91	.025/0.64	.082/2.08
26-30	.050/1.27	.075/1.91	.083/2.10	.025/0.64	.058/1.47	.020/0.51	.065/1.65



MATERIAL NUMBER	PLATING	WIRE SIZE	FORM
43030-001	A	20-24	CHAIN
43030-002	B	20-24	CHAIN
43030-003	C	20-24	CHAIN
43030-004	A	26-30	CHAIN
43030-005	B	26-30	CHAIN
43030-006	C	26-30	CHAIN
43030-007	A	20-24	LOOSE
43030-008	B	20-24	LOOSE
43030-009	C	20-24	LOOSE
43030-010	A	26-30	LOOSE
43030-011	B	26-30	LOOSE
43030-012	C	26-30	LOOSE

NOTES

- 1) MATERIAL: PHOSPHOR BROMIDE
- 2) TERMINAL PLATING:
 - "A" - HOT TIN DIP: .00015/0.00038
 - "B" - .000015/0.00038
 - .000100/0.0025
 - ALL OVER .000100/0.0025
 - "C" - .000030/0.00038
 - .000100/0.0025
 - ALL OVER .000100/0.0025
- * THE PRIMARY MATERIAL IS COMPLIANT TO ROHS DIRECTIVE 2002/95/EC. ALL PRODUCTS OF DIRECTIVE 2000/53/EC. PRODUCT WITH TIN/LEAD IN THE FINISH.
- MATERIAL IS NOT PLATED.
- 3) PRODUCT NUMBER: 4300-001.
- 4) PACKAGING: 4300-001.
- 5) TERMINAL FOR USE IN A MICRO FIT RECEPTACLE #4133-****.
- TERMINAL ORIENTATION IN RECEPTACLE SEE DRAWING.