


Zener Diodes

Features

- Silicon Planar Power Zener Diodes
- For use in stabilizing and clipping circuits with high power rating
- The Zener voltages are graded according to the international E 24 standard. Smaller voltage tolerances are available upon request
- These diodes are also available in the DO41 case with the type designation ZPY3V9 to ZPY100
- Lead (Pb)-free component
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



18315

Mechanical Data

Case: MELF Glass case

Weight: approx. 135 mg

Cathode Band Color: black

Packaging Codes/Options:

GS18/ 5 k per 13" reel (12 mm tape), 10 k/box

GS08/ 1.5 k per 7" reel (12 mm tape), 12 k/box

Absolute Maximum Ratings

$T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit
Zener current (see Table "Characteristics")				
Power dissipation		P_{tot}	1.0 ¹⁾	W

¹⁾ Valid provided that electrodes are kept at ambient temperature.

Thermal Characteristics

$T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit
Thermal resistance junction to ambient air		R_{thJA}	170 ¹⁾	K/W
Thermal resistance junction to case		R_{thJC}	60	K/W
Junction temperature		T_j	175	$^{\circ}\text{C}$
Storage temperature		T_{stg}	- 55 to + 175	$^{\circ}\text{C}$

¹⁾ Valid provided that electrodes are kept at ambient temperature.

ZMY3V9 to ZMY100



Vishay Semiconductors

Electrical Characteristics

Partnumber	Zener Voltage (2)		Dynamic Resistance		Temperature Coefficient of Zener Voltage		Test Current	Reverse Voltage	Admissible Zener Current ¹⁾
	V_Z at I_{ZT}		r_{zj} at I_{ZT} , $f = 1$ kHz		α_{VZ} at I_{ZT}		I_{ZT}	V_R at $I_R = 0.5 \mu A$	I_Z at $T_{amb} = 25^\circ C$
	V		Ω		$10^{-4}/^\circ C$		mA	V	mA
	min	max		typ	min	max			
ZMY3V9	3.7	4.1	7	4	- 7	2	100	-	203
ZMY4V3	4	4.6	7	4	- 7	3	100	-	182
ZMY4V7	4.4	5	7	4	- 7	4	100	-	165
ZMY5V1	4.8	5.4	5	2	- 6	5	100	0.7	150
ZMY5V6	5.2	6	2	1	- 3	5	100	1.5	135
ZMY6V2	5.8	6.6	2	1	- 1	6	100	2	128
ZMY6V8	6.4	7.2	2	1	0	7	100	3	110
ZMY7V5	7	7.9	2	1	0	7	100	5	100
ZMY8V2	7.7	8.7	2	1	3	8	100	6	89
ZMY9V1	8.5	9.6	4	2	3	8	50	7	82
ZMY10	9.4	10.6	4	2	5	9	50	7.5	74
ZMY11	10.4	11.6	7	3	5	10	50	8.5	66
ZMY12	11.4	12.7	7	3	5	10	50	9	60
ZMY13	12.4	14.1	9	4	5	10	50	10	55
ZMY15	13.8	15.8	9	4	5	10	50	11	49
ZMY16	15.3	17.1	10	5	7	11	25	12	44
ZMY18	16.8	19.1	11	5	7	11	25	14	40
ZMY20	18.8	21.2	12	6	7	11	25	15	36
ZMY22	20.8	23.3	13	7	7	11	25	17	34
ZMY24	22.8	25.6	14	8	7	12	25	18	29
ZMY27	25.1	28.9	15	9	7	12	25	20	27
ZMY30	28	32	20	10	7	12	25	22.5	25
ZMY33	31	35	20	11	7	12	25	25	22
ZMY36	34	38	60	25	7	12	10	27	20
ZMY39	37	41	60	30	8	12	10	29	18
ZMY43	40	46	80	35	8	13	10	32	17
ZMY47	44	50	80	40	8	13	10	35	15
ZMY51	48	54	100	45	8	13	10	38	14
ZMY56	52	60	100	50	8	13	10	42	13
ZMY62	58	66	130	60	8	13	10	47	11
ZMY68	64	72	130	65	8	13	10	51	10
ZMY75	70	79	160	70	8	13	10	56	9
ZMY82	77	88	160	80	8	13	10	61	8
ZMY91	85	96	250	120	9	13	5	68	7.5
ZMY100	94	106	250	130	9	13	5	75	7

¹⁾ Valid provided that electrodes are kept at ambient temperature

²⁾ Tested with pulses $t_p = 5$ ms

Typical Characteristics

$T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified




Figure 1. Dynamic Resistance vs. Zener Current




Figure 4. Admissible Power Dissipation vs. Ambient Temperature




Figure 2. Dynamic Resistance vs. Zener Current




Figure 5. Pulse Thermal Resistance vs. Pulse Duration




Figure 3. Dynamic Resistance vs. Zener Current

ZMY3V9 to ZMY100

Vishay Semiconductors




Figure 6. Breakdown Characteristics




Figure 8. Breakdown Characteristics






Figure 7. Breakdown Characteristics

Package Dimensions of MELF Glass in mm (Inches): DO41



★ The gap between plug and glass can be either on cathode or anode side

foot print recommendation:



Document no.:S8-V-3453.02-001 (4)
 Rev. 3 - Date: 07.June.2006
 18317

Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design
and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.