



NOTE :
 1. DIMENSIONS SHOWN MILLIMETERS INCHES
 2. FOR OTHER PRODUCT SPEC'S. SEE PSX 10-39.
 3. THIS HOUSING USES KK TERM. No's. 2478, 2578 & 28



FOR VOID CKT. LOCATION SEE PAGE 2 OF 2



MAT'L: NYLON

CENTER RIB ONLY

10-01-1204	E-3001-20	3.800 ±.012	4.000 ^{+0.006} _{-0.016}	96.52 ±0.3	101.60 ^{+0.3} _{-0.4}
-1194	-19	3.600 ±.012	3.800 ^{+0.006} _{-0.016}	91.44 ±0.3	96.52 ^{+0.3} _{-0.4}
-1184	-18	3.400 ±.012	3.600 ^{+0.006} _{-0.016}	86.36 ±0.3	91.44 ^{+0.3} _{-0.4}
-1174	-17	3.200 ±.012	3.400 ^{+0.006} _{-0.016}	81.28 ±0.3	86.36 ^{+0.3} _{-0.4}
-1164	-16	3.000 ±.010	3.200 ^{+0.006} _{-0.016}	76.20 ±0.25	81.28 ^{+0.3} _{-0.4}
-1154	-15	2.800 ±.010	3.000 ^{+0.006} _{-0.016}	71.12 ±0.25	76.20 ^{+0.3} _{-0.4}
-1144	-14	2.600 ±.010	2.800 ^{+0.006} _{-0.016}	66.04 ±0.25	71.12 ^{+0.3} _{-0.4}
-1134	-13	2.400 ±.010	2.600 ^{+0.006} _{-0.016}	60.96 ±0.25	66.04 ^{+0.3} _{-0.4}
-1124	-12	2.200 ±.010	2.400 ^{+0.006} _{-0.016}	55.88 ±0.25	60.96 ^{+0.3} _{-0.4}
-1114	-11	2.000 ±.008	2.200 ^{+0.006} _{-0.012}	50.80 ±0.20	55.88 ^{+0.3} _{-0.4}
-1104	-10	1.800 ±.008	2.000 ^{+0.006} _{-0.008}	45.72 ±0.20	50.80 ^{+0.3} _{-0.4}
-1094	-9	1.600 ±.008	1.800 ^{+0.006} _{-0.008}	40.64 ±0.20	45.72 ^{+0.3} _{-0.4}
-1084	-8	1.400 ±.008	1.600 ^{+0.006} _{-0.008}	35.56 ±0.20	40.64 ^{+0.3} _{-0.4}
-1074	-7	1.200 ±.008	1.400 ^{+0.006} _{-0.008}	30.48 ±0.20	35.56 ^{+0.3} _{-0.4}
-1064	-6	1.000 ±.004	1.200 ^{+0.006} _{-0.008}	25.40 ±0.10	30.48 ^{+0.3} _{-0.4}
-1054	-5	.800 ±.004	1.000 ^{+0.006} _{-0.006}	20.32 ±0.10	25.40 ^{+0.3} _{-0.4}
-1044	-4	.600 ±.004	.800 ^{+0.006} _{-0.006}	15.24 ±0.10	20.32 ^{+0.3} _{-0.4}
-1034	-3	.400 ±.004	.600 ^{+0.006} _{-0.006}	10.16 ±0.10	15.24 ^{+0.3} _{-0.4}
-1024	-2	.200 ±.004	.400 ^{+0.006} _{-0.006}	5.08 ±0.10	10.16 ^{+0.3} _{-0.4}
10-01-1014	E-3001-1		.200 ^{+0.006} _{-0.006}		5.08 ^{+0.3} _{-0.4}
PART No.	ENG. No.	ENGLISH		METRIC	
		A	B	A	B

CORRECT TEXT LOC
 EC NO: E2007-0720
 DRWN: DWASZKI EMI CZ 2007/03/28
 CHKD: D. MOR ARTY 2007/03/29
 APPR: DENNEHY 2007/04/04

QUALITY SYMBOLS
 ▽=0
 ▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±.005	±.0002
3 PLACES	±.005	±.010
2 PLACES	±0.25	±.014
1 PLACE	±0.35	±.014

ANGULAR ±1/2°

DIMENSION STYLE
MM/IN

SCALE
7:1

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

DRAWN BY P. MOORE **DATE** 1998/09/15
CHECKED BY MGOONEY **DATE** 1999/03/12
APPROVED BY MWILHITE **DATE** 1999/03/12

TITLE 5.08MM KK CRP TERM HSG

MATERIAL NO. SEE CHART **DOCUMENT NO.** SDE-3001-N-* **SHEET NO.** 1 OF 1

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

SIZE A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

PART NO. SEE CHART
 DWG. NO. SDE-3001-N*

FOR MANUFACTURE IN SINGAPORE ONLY

FOR DIMENSIONS SEE SHEET No.1

11	97-00-0919	E-3001-12-11	12
2	NOT TOOLED	E-3001-7-2	7
3	I 10-01-1080	-8-3	8
5	I -3085	-8-5	8
4	I -3044	-4-4	4
3	I -1030	-3-3	3
2	-1049	-4-2	4
2	-1109	-10-2	10
2	-1099	-9-2	9
5	10-01-1069	E-3001-6-5	6
VOID CKT. LOCATION	PART No.	ENG. No.	NO OF CKTS.

REDRAWN ON CAD EC NO. E90109 DRWN: P. MOORE 98/09/19 CHK: / / / / APPR: / / / /	DESCRIPTION MAJOR = CRITICAL = C =	QUALITY SYMBOLS		GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE :	DESIGN UNITS <input type="checkbox"/> mm <input type="checkbox"/> INCH	DIMENSIONS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH <input type="checkbox"/> mm ONLY		SHT	REV		
		4 PLACES ±0. ±.		DRAWN BY & DATE P. MOORE 98/09/19		CHECKED BY & DATE MGOONEY 12/03/99		TITLE: HOUSING, CONNECTOR, KK (5.08)/.200 CRIMP STYLE TERM.					
		3 PLACES ±0. ±.		APPROVED BY & DATE MWILHITE 12/03/99		MOLEX INCORPORATED							
		2 PLACES ±0. ±.		CAD FILENAME PM19.DGN		MATERIAL NO. SEE CHART		DRAWING NO. SDE-3001-N-*		SHEET NO. 2 OF			
1 PLACE ±0. ±.		ANGULAR: ± 1/2 °		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B											