



PHYSICAL

Conductors: 26 AWG 7/34 Tinned Copper
 Insulation: .010" PVC
 Color Code: Brn,Red,Org,Yel,Grn,Blu,Vio,Gry, Wht,Blk, and repeat
 Laminate: (2) .005" Clr PVC
 Temperature: 105°C

ELECTRICAL

Impedance: 140 ohms
 Capacitance: 10 pF/ft @1MHz
 Prop Delay: 1.4 ns/ft
 Current Rating: 1.7 A
 Insulation Res: 10¹⁰ ohms – 10 ft minimum

Above Values Estimated in the Ground-Signal-Ground Configuration

PRELIMINARY

Approvals:

UL Style 20130 and 300 V

Part Number	Count	A-Span, Nominal		B-Span	
		Inches	(mm)	Inches	(mm)
135-2607-304	4	0.40	10,16	0.300 ±.015	7,62 ±.38
135-2607-306	6	0.60	15,24	0.500 ±.015	12,70 ±.38
135-2607-308	8	0.80	20,32	0.700 ±.015	17,78 ±.38
135-2607-310	10	1.00	25,4	0.900 ±.015	22,86 ±.38
135-2607-312	12	1.20	30,48	1.100 ±.015	27,94 ±.38
135-2607-314	14	1.40	35,56	1.300 ±.015	33,02 ±.38
135-2607-316	16	1.80	45,72	1.700 ±.015	43,18 ±.38
135-2607-320	20	2.00	50,8	1.900 ±.020	48,26 ±.51

REVISION	CHANGES
1	PRELIMINARY
2	CORRECT DIM LINE

DRAWN	PROD ENG	QA	MKT	P/ECN#	DRAWING NO. 135-2607-3XX	AMPHENOL SPECTRA-STRIP 720 SHERMAN AVE TEL (203) 281-3200 HAMDEN CT 06514 FAX (203) 281-5872	Rev 2
FTTS 9/12/06	11/20/06				TITLE: 3C Color Coded Planar Cable, .100" Pitch		SHEET 1 of 1