
Noise Suppression Products/EMI Suppression Filters > Chip Common Mode Choke Coils > Film Type

Data Sheet


# Chip Common Mode Choke Coils Film Type

## DLP31S Series (1206 Size)

#### Dimension



#### Equivalent Circuit



#### ■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	Operating Temperature Range	Number of Circuit
DLP31SN121ML2	120ohm±20%	100mA	16Vdc	100M ohm	40Vdc	2.0ohmmax.	-40°C to 85°C	1
DLP31SN221ML2	220ohm±20%	100mA	16Vdc	100M ohm	40Vdc	2.5ohmmax.	-40°C to 85°C	1
DLP31SN551ML2	550ohm±20%	100mA	16Vdc	100M ohm	40Vdc	3.6ohmmax.	-40°C to 85°C	1

#### ■ ①Caution/Notice

#### Notice

Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin melting point is used. Please confirm the solderability of Tin plating termination chip before use.

• This data sheet is applied for CHIP COMMON MODE CHOKE COIL used for General Electronics equipment for your design.


#### A Note:

1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



### ■ Impedance-Frequency Characteristics



1

#### Packaging

Code	Packaging	Minimum Quantity		
L	180mm Embossed Tape	3000		
В	Bulk(Bag)	500		