

Customer: ALPS EUROPE DISTRIBUTION

No. 12E2006-3025

Date: Nov. 06, 2006

Attention:

Your ref. No.:

Your Part No.: EC12E1220401

## SPECIFICATIONS

ALPS' ;

MODEL: EC12E1220401

Spec. No.:

Sample No.: F 3 5 1 7 2 2 1 M

RECEIPT STATUS

RECEIVED

By Date

Signature

Name

Title

**ALPS**<sup>®</sup>  
ALPS ELECTRIC CO., LTD.

Head Office

1-7, Yukigaya-otsuka-cho, Ota-ku, Tokyo, 145-8501 Japan  
Phone, +81(3)3726-1211

DSG'D

*M. Sato*

APP'D

*S. Sato*

ENG. DEPT. DIVISION

Sales

B6523

Q1003#03A (EA)

# S P E C I F I C A T I O N S

1. THIS SPECIFICATIONS APPLY TO EC12E1220401 ROTARY ENCODERS.

2. CONTENTS OF THIS SPECIFICATIONS.

F3517221M

LE2120N

3. MARKING

- MARKING ON ALL UNITS  
DATE CODE

• CAUTION

Regardless of the suggested applications of these products being introduced in the specifications, when using them for equipment and devices requiring a high degree of safety, respective manufacturers will please preserve safety of the planned equipment and devices by providing necessary protective circuits and redundancy circuits and reconfirm if safety is being duly preserved.

Products being introduced in the specifications have been designed and manufactured for applications to ordinary electronic equipment and devices such as the AV equipment, electric home appliances, office machines and communications equipment. Consequently, when employing these products for applications requiring a high degree of safety and reliability such as the medical equipment, aviation and aircraft equipment, space equipment and burglar alarm equipment, the using manufacturers will please thoroughly study the proprieties of these products for the planned applications.

Although we are exerting our best efforts to maintain the quality of these products, we cannot guarantee that they will never cause short circuiting and open circuitry. Therefore, when designing an equipment or device with which the priority is given to the safety, you will please carefully study the influences to the whole equipment of a single function failure of Potentiometers and Encoders in advance to make out a fail-safe design providing.



5. 機械的性質 Mechanical characteristics


項目 Item	条件 Conditions	規格 Specifications
5-1 全回転角度 Total rotational angle		360° (エンドレス) 360° (Endless)
5-2 クリックトルク Click torque	(クリック特定の測定) (Applied for with-detent type)	3~20mN・m
5-3 クリック位置及び位置 Number and position of detents		12本クリック 12 detents (ステップ角: 30° ± 3°) (step angle: 30° ± 3°)
5-4 軸の押し引き強度 Push-pull strength of shaft	軸の押し引き強度は80Nの標準値を1.0倍測定する。(PCB実用値) Push and pull static load of 80N shall be applied to the shaft in the axial direction for 10S. (After soldering of the PC board)	軸の押し引き強度は、押し引き方向、及び軸の押し引き強度(電圧降下)を測定する。No excessive play in shaft. No excessive abnormality in rotational feeling. And electrical characteristics shall be satisfied.
5-5 端子強度 Terminal strength	端子強度は任意の方向に3Nの標準値を1.0倍測定する。 A static load of 3N shall be applied to the tip of terminals for 10S in any direction.	押し引き及び捻回強度を測定する。Without excessive play in terminals or poor contact.
5-6 軸の揺れ Shaft wobble	軸の揺れは5mmの位置で50mN・mの軸荷を印加する。 A momentary load of 50mN-m shall be applied at the point 5mm from the tip of the shaft in a direction perpendicular to the axis of shaft.	0.7xL/30mm-p以内 0.7xL/30mm-p MAX (Lは軸長(軸長測定位置、) (L: Shaft length)
5-7 軸の歪み Shaft play in axial direction	軸の歪みは任意の方向に3Nの標準値を1.0倍測定する。 Push and pull static load of 3N shall be applied to the shaft in the axial directions.	0.4mm-p以内 0.4mm-p MAX
5-8 軸の歪み強度 Side thrust strength of shaft	軸の歪みは55mmの位置で20Nの標準値を1.0倍測定する。(PCB実用値) A load of 20N shall be applied at the point 55mm from the tip of the shaft in a direction perpendicular to the axis of shaft. (After soldering of the PC board)	押し引き及び、軸の歪み強度を測定する。Without excessive play or bending in shaft. No mechanical abnormality.
5-9 軸の回転方向の揺れ Shaft play in rotational wobble	角度計で測定する。 Measure with Jig for rotational angle	3° 以内 3° MAX

**ALPS ELECTRIC CO., LTD.**

APPD.	CHKD.	DSGD.	TITLE
Apr. 22, '99	Apr. 22, '99	Apr. 22, '99	12 形回転编码器 12mm Size Rotary encoder
K. ITO Y. KANZAKI H. MIURA			DOCUMENT NO.
			F 3517221M

6. 電気的性質 Electrical characteristics

項目 Item	条件 Conditions	規格 Specifications
2) 滑動ノイズ (Sliding noise)	3-VONの電圧の1.5V以上の電圧変動を抑制し、チップ出力1.1mA以下の電圧変動を抑制する。また、電源ノイズは1.5V以下の電圧変動を抑制する。 Specified by the time of voltage change exceed 1.5V in code-ON area. When the bounce has code-ON time less than 1ms between chatterings ( $t_1$ or $t_2$ ), the voltage change shall be regarded as a part of chattering. When the code-ON time between 2 bounces is less than 1ms, they are regarded as 1 linked bounce.	$t_2 \leq 2ms$
3) 滑動ノイズ (Sliding noise)	3-VOFFの電圧変動を抑制する。 The voltage change in code-OFF area.	3.5V以上 3.5V MIN
4-4 絶縁強度 (Dielectric strength)	端子-接地間電圧: C. 50V/1分間維持する。(リーク電流1mA) A voltage of 50V.A.C. shall be applied for 1min between individual terminals and bracket. (Leak current 1mA)	絶縁強度の劣化なく Without arcing or breakdown
4-5 絶縁抵抗 (Insulation resistance)	端子-接地間電圧: D. C. 50Vの電圧を印加する。 Measurement shall be made under the condition which a voltage of 50V.D.C. is applied between individual terminals and bracket.	端子-接地間電圧10MΩ以上 Between individual terminals and bracket: 10MΩ MIN
4-6 位相差 (Phase-difference)	規定の動作条件で測定する。 Measurement shall be made under the condition which the shaft is rotated in constant speed. <Fig. 4> 図4 順方向 CW 図5 逆方向 CCW	$\Delta T = 0.08T$ 以上 MIN




**ALPS ELECTRIC CO., LTD.**

APPD.	CHKD.	DSGD.	TITLE
Apr. 22, '99	Apr. 22, '99	Apr. 22, '99	12 形回転编码器 12mm Size Rotary encoder
K. ITO Y. KANZAKI H. MIURA			DOCUMENT NO.
			F 3517221M



9. その前、取扱い上の注意 PRECAUTIONS IN USE

- 9-1. 保管は高温、多湿の気候及び風食性カスに含まれて下さい。  
During operation, storage in high temperature and humidity, and in corrosive gas, should be avoided.
- 9-2. エンコーダ - のハ、カスカウント装置の電源は必ず「動作スピード」、サブ「リング」タイム、マスキング、タイム等注意し、実装回路の上層を参照して下さい。  
In case of pulse count process design, operational speed, sampling time, and masking time etc should be taken into the consideration.  
Please check above matter at first on your circuit for the secure reason.
- 9-3. 本製品はクリック位置でA相はOFF状態で空走を繰り返すので、ソフト起動時A相基準で調整が必要です。  
A phase should be design criterion prior to B phase.  
Because A phase has steady off signal at detent position.
- 9-4. エンコーダ - のハ、カスカウント装置の回路は下記のフィルムをいれることを推奨します。  
For your pulse count design, it should be considered to add C/R filter on your circuit shown as below.



- 9-5. 本製品の本体に直接水分が付きまると、ハ、カスカウント装置が異常が発生する可能性がありますので、製品に直接水分が付きまらぬよう配慮して下さい。  
Care must be taken not to expose this product to water or dew to prevent possible problem in pulse output wave form.
- 9-6. 医療用器械、器具へ本製品の御使用は避けて下さい。  
Please avoid to medical instrument because this encoder is audio use.

<b>ALPS ELECTRIC CO., LTD.</b>	
APPD.	CHKD.
APR. 22, '99	APR. 22, '99
K. ITO Y. KANZAKI H. MIURA	
F 351 7221 M	
(8/8)	

7. はんだ付け条件 Soldering conditions

7-1 手はんだの場合 Manual soldering

温度350°C以下、時間3分以内  
Bit temperature of soldering iron : 350°C or less.  
Application time of soldering iron : within 3s.

7-2 ディップはんだの場合 Dip soldering

使用溶剤 : 1:1. 6片両面塗布  
Printed wiring board: Single-sided copper clad laminate board with thickness of 1.6mm.  
フラックス : 比重0.82以上のフラックスを用いた液式フラックスにて塗布後は、各接点の半量を回収し、かつ基板表面にフラックスの残りが無いこと。  
Flux:

- Specific gravity: 0.82 or more.
- Flux shall be applied to the board using a bubble foaming type fluxer.
- The board shall be soaked in the flux bubble only to the middle of its thickness.
- Flux shall not come into contact with the component side surface.

プリヒート : 各接点温度100°C以下、時間1分以内  
Preheating:

- Surface temperature of board: 100°C or less.
- Preheating time: within 1 min.


はんだ : 温度260°C±5°C、時間3秒±1秒以内  
Soldering:

- Solder temperature: 260°C ±5°C.
- Immersion time: within 3s.

以上の工程を1回または2回繰り返す。  
Apply the above soldering process for 1 or 2 times.


8. はんだ付け時の注意事項 Note for soldering method.

- 8-1 下部のようP.C.B.の上層にはんだ付けをする配線は、お避け下さい。  
Please avoid soldering on upper surface (the component side surface) of the PC board as shown below.




- 8-2 蒸留水、エタノール等の洗浄液はエンコーダ - 内にフラックスが流入する場合があります。蒸留水不純物等により、P.C.B.の上層にばんだ付けをする配線は、お避け下さい。  
Please avoid cleaning of PCB board because the flux used during the dip soldering process may enter the encoder and cause poor contact.

<b>ALPS ELECTRIC CO., LTD.</b>	
APPD.	CHKD.
APR. 22, '99	APR. 22, '99
K. ITO Y. KANZAKI H. MIURA	
F 351 7221 M	
(7/8)	




商標の位置は任意  
THE DIRECTION OF  
TRADE MARK IS OPTIONAL



取付穴寸法図 (許容差±0.1)


\*挿入側より見た図  
P.W.B. MOUNTING DETAIL  
(TOLERANCE±0.1)  
VIEWED FROM MOUNTING SIDE



基板板厚  $t = 1.6\text{mm}$   
P.C.B.

端子先端詳細図 (10:1)

△ DETAIL OF TERMINALS



指定なき部分の許容差 TOLERANCES UNLESS OTHERWISE SPEC	
$L \leq 10$	$\pm 0.3$
$10 < L < 100$	$\pm 0.5$
$100 \leq L$	$\pm 0.8$
角度 ANGULAR DIMENSION	$\pm 5^\circ$

				12ハズ 12PLUSE SHAFT COLOR:GRAY		L=20 伏形 クリック付き	
PART NO.	NAME	MATERIAL NAME / CODE		FINISH			
				<b>ALPS ELECTRIC CO., LTD.</b>			
				DSGD. ツツケ11-8501351 H. Shimomura98-01-29		SCALE 2:1	NO.
△ 1	2001/09/13	S.M.	H. OY. F	CHKD.		TITLE 12形薄形インコター	
△ 1	99/12/14	K. IY. KH. O	S. Inoue	98-02-02			
△ 2	99/8/23	K. KK. IY. K	APPD.		UNIT mm	DOCUMENT NO. LE2120N	
SYMB	DATE	APPD	CHKD	DSGD	K. Kawasaki 98-02-02	2001.9.18	