## **GP** Batteries

Data Sheet Model No.: GP17R8H

Type : High Voltage Nickel Metal Hydride Rechargeable Battery

Nominal Dimension : 15.7 mm (I)x 26.5 mm(w) x 48.4 mm(h)

Applications : Recommended discharge current 17mA to 510mA

Nominal Voltage : 8.4V

Capacity : Minimum: 170mAh Typical: 175mAh

when discharged at 0.2C to 1.0V at 20°C

Charging Condition : 17mA for 14 hrs at  $20^{\circ}C$ 

Fast Charge : 85 mA to 170mA (0.5 to 1C)

charge termination control recommended

control parameters: -ΔV : 0 - 35mV

DT/dt : 0.8°C/min (0.5 to 0.9C)

: 0.8 - 1°C/min (1C)

TCO: 45 - 50°C Timer: 105% nominal input

Service Life : >500 cycles (IEC standard)

Continuous : 17 mA maximum current for 1 year

Overcharge No conspicuous deformation

and/or leakage

Weight : 32 g

Internal Resistance : Maximum 2000 m $\Omega$  upon fully charged


at 1000Hz

Storage


Max. Charging Voltage: 10.5 V at 17 mA charging

Ambient Temperature Range


Standard Charging Fast Charging Discharging 0 to 45°C 10 to 45°C -20 to 50°C -20 to 35°C




## Fast Charge (Charge control required)



## Low Rate Discharge



## **High Rate Discharge**



\* The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.