


## AC and Pulse Metallized Polypropylene Film Capacitors MKP Axial Type



**APPLICATIONS**

High current and high pulse operations

**REFERENCE STANDARDS**

IEC 60384-17

**MARKING**

Manufacturer's logo; code for dielectric material; manufacturer's type designation; C-code; rated voltage-code; tolerance-code; special n °C-value; tolerance; rated voltage; year and week; manufacturer's location

**DIELECTRIC**

Polypropylene film

**ELECTRODES**

Metallized

**CONSTRUCTION**

Series construction

**RATED (DC) VOLTAGE**

630 V, 850 V, 1250 V, 1600 V

**RATED (AC) VOLTAGE**

300 V, 400 V, 450 V, 600 V

**FEATURES**

Supplied loose in box, taped on ammopack or reel available on request

RoHS compliant



**RoHS**  
COMPLIANT

**ENCAPSULATION**

Plastic-wrapped, epoxy resin sealed. Flame retardant.

**CLIMATIC TESTING CLASS ACC. TO IEC 60068-1**

55/110/56

**CAPACITANCE RANGE (E12 SERIES)**

0.1 µF to 3.3 µF

**CAPACITANCE TOLERANCE**

± 5 %

**LEADS**

Tinned wire

**RATED TEMPERATURE**

85 °C

**MAXIMUM APPLICATION TEMPERATURE**

At 85 °C:  $U_C = 1.0 U_R$   
at 110 °C:  $U_C = 0.7 U_R$

**PULL TEST ON LEADS**

≥ 20 N in direction of leads according to IEC 60068-2-21

**BENT TEST ON LEADS**

2 bends trough 90° with half of the force used in pull test

**RELIABILITY**


Operation life > 300 000 h  
Failure rate < 5 FIT (40 °C and 0.5 x  $U_R$ )

**DETAIL SPECIFICATION**

For more detailed data and test requirements contact:  
[dc-film@vishay.com](mailto:dc-film@vishay.com)



**COMPOSITION OF CATALOG NUMBER**



**Notes**

(1) For detailed tape specifications refer to "Packaging Information": [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139) or end of catalog

**SPECIFIC REFERENCE DATA**

DESCRIPTION	VALUE			
	at 1 kHz	at 10 kHz	at 100 kHz	
Tangent of loss angle:				
0.1 μF < C ≤ 0.47 μF	≤ 3 x 10 <sup>-4</sup>	≤ 5 x 10 <sup>-4</sup>	≤ 35 x 10 <sup>-4</sup>	
0.47 μF < C ≤ 1 μF	≤ 3 x 10 <sup>-4</sup>	≤ 8 x 10 <sup>-4</sup>	≤ 50 x 10 <sup>-4</sup>	
1 μF < C ≤ 0.33 μF	≤ 3 x 10 <sup>-4</sup>	≤ 10 x 10 <sup>-4</sup>	≤ 60 x 10 <sup>-4</sup>	
Rated voltage pulse slope (dU/dt) <sub>R</sub> at U <sub>Rdc</sub>	630 Vdc	850 Vdc	1250 Vdc	1600 Vdc
	500 V/μs	1000 V/μs	1000 V/μs	1000 V/μs
U <sub>p-p</sub> peak-to-peak voltage	700 V	1130 V	1400 V	1600 V
R between leads, for C ≤ 0.33 μF at 500 V; 1 min	> 100 GΩ			
RC between leads, for C > 0.33 μF at 500 V; 1 min	> 30 000 s			
R between interconnecting and wrapped film at 500 V; 1 min	> 100 GΩ			
Withstanding (DC) voltage (cut off current 10 mA); rise time 100 V/s	1008 V	1360 V	2000 V	2560 V
	1 min			
Withstanding (DC) voltage between leads and wrapped film (1.4 x U <sub>Rac</sub> + 2000)	2840 V; 1 min			
Maximum application temperature	110 °C			

# MKP 1839 HQ



Vishay Roederstein AC and Pulse Metallized Polypropylene Film Capacitors  
MKP Axial Type

Capacitance	VOLTAGE CODE 63 630 Vdc/300 Vac					VOLTAGE CODE 08 850 Vdc/400 Vac				
	Dimensions max. (mm)		Mass	d <sub>t</sub> ± 0.08 mm	SPQ <sup>(1)</sup>	Dimensions max. (mm)		Mass	d <sub>t</sub> ± 0.08 mm	SPQ <sup>(1)</sup>
	D	L	(g)	(mm)	Pieces	D	L	(g)	(mm)	Pieces
(μF)										
0.1	7	26.5	0.9	0.8	2000	8.5	31.5	1.6	0.8	1500
0.15	8	26.5	1.2	0.8	1750	10	31.5	2.3	0.8	1000
0.18	8.5	26.5	1.4	0.8	1500	11	31.5	2.7	0.8	850
0.22	9.5	26.5	1.6	0.8	1250	11.5	31.5	3.2	0.8	750
0.27	10	26.5	1.9	0.8	1000	13	31.5	3.9	0.8	600
0.33	11	26.5	2.3	0.8	900	14	31.5	4.6	0.8	500
0.39	10.5	31.5	2.6	0.8	900	15	31.5	5.4	0.8	1000
0.47	11	31.5	3.0	0.8	750	16.5	31.5	6.5	0.8	900
0.56	12	31.5	3.5	0.8	650	15	31.5	5.4	0.8	1000
0.68	13	31.5	4.2	0.8	500	16.5	31.5	6.5	0.8	850
0.82	14	31.5	5.1	0.8	1000	18	31.5	7.8	1.0	750
1	16	31.5	6.1	0.8	900	19.5	31.5	9.4	1.0	600
1.5	19	31.5	9.0	1.0	600	24	31.5	13.9	1.0	400
2.2	23	31.5	13.1	1.0	450	-	-	-	-	-
3.3	28	31.5	19.5	1.0	300	-	-	-	-	-

Capacitance	VOLTAGE CODE 12 1250 Vdc/450 Vac					VOLTAGE CODE 13 1600 Vdc/600 Vac				
	Dimensions max. (mm)		Mass	d <sub>t</sub> ± 0.08 mm	SPQ <sup>(1)</sup>	Dimensions max. (mm)		Mass	d <sub>t</sub> ± 0.08 mm	SPQ <sup>(1)</sup>
	D	L	(g)	(mm)	Pieces	D	L	(g)	(mm)	Pieces
(μF)										
0.1	8.5	31.5	1.6	0.8	1500	10.5	31.5	2.7	0.8	1000
0.15	10	31.5	2.3	0.8	1000	12.5	31.5	3.9	0.8	600
0.18	11	31.5	2.7	0.8	1000	13.5	31.5	4.6	0.8	500
0.22	11.5	31.5	3.2	0.8	800	15	31.5	5.5	0.8	500
0.27	13	31.5	3.9	0.8	650	16.5	31.5	6.7	0.8	900
0.33	14	31.5	4.6	0.8	500	18	31.5	8.1	1.0	750
0.39	15	31.5	5.4	0.8	1000	19.5	31.5	9.5	1.0	600
0.47	16.5	31.5	6.5	0.8	900	21.5	31.5	11.3	1.0	500
0.56	18	31.5	7.7	1.0	750	23.5	31.5	13.4	1.0	400
0.68	20	31.5	9.2	1.0	600	25.5	31.5	16.2	1.0	350
0.82	21.5	31.5	11.1	1.0	500	-	-	-	-	-
1	23.5	31.5	13.4	1.0	400	-	-	-	-	-
1.5	-	-	-	-	-	-	-	-	-	-
2.2	-	-	-	-	-	-	-	-	-	-
3.3	-	-	-	-	-	-	-	-	-	-

**Note**

<sup>(1)</sup> SPQ = Standard Packaging Quantity


**MOUNTING****Normal Use**

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

**Specific Method of Mounting to Withstand Vibration and Shock**

In order to withstand vibration and shock tests, it must be ensured that the capacitor body is in good contact with the printed-circuit board.

- For  $L \leq 19$  mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped
- The maximum diameter and length of the capacitors are specified in the dimensions table
- Eccentricity as shown in the drawing below:

**Storage Temperature**

- Storage temperature:  $T_{stg} = -25$  °C to  $+40$  °C with RH maximum 80 % without condensation


**Ratings and Characteristics Reference Conditions**

Unless otherwise specified, all electrical values apply to an ambient free air temperature of  $23 \pm 1$  °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of  $50 \pm 2$  %.


For reference testing, a conditioning period shall be applied over  $96 \pm 4$  h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.

## CHARACTERISTICS


Capacitance as a function of ambient temperature (typical curve)




Tangent of loss angle as a function of frequency (typical curve)




Impedance as a function of frequency (typical curve)




Max. DC and AC voltage as a function of temperature



Max. RMS Voltage (sinewave) as a function of frequency




Max. RMS Voltage (sinewave) as a function of frequency






## AC and Pulse Metallized Polypropylene Film Capacitors Vishay Roederstein MKP Axial Type


Max. RMS Voltage (sinewave) as a function of frequency




Max. RMS Voltage (sinewave) as a function of frequency




Max. RMS Voltage (sinewave) as a function of frequency




Max. RMS Voltage (sinewave) as a function of frequency




Max. RMS Voltage (sinewave) as a function of frequency




Max. RMS Voltage (sinewave) as a function of frequency



Insulation resistance as a function of ambient temperature  
(typical curve)



Max. allowed component rise ( $\Delta T$ ) as a function of the ambient temperature ( $T_{amb}$ )



**HEAT CONDUCTIVITY (G) AS A FUNCTION OF CAPACITOR BODY THICKNESS IN mW/°C**

DIAMETER (mm)	HEAT CONDUCTIVITY (mW/°C)	
	PITCH 26.5 mm	PITCH 31.5 mm
7.0	8	-
8.0	10	-
8.5	11	12
9.5	12	-
10.0	13	15
10.5	-	16
11.0	15	17
11.5	-	18
12.0	-	19
12.5	-	20
13.0	-	21
13.5	-	22
14.0	-	23
15.0	-	25
16.0	-	28
16.5	-	29
18.0	-	32
19.0	-	34
19.5	-	36
20.0	-	37
21.5	-	40
23.0	-	44
23.5	-	45
24.0	-	47
25.5	-	51
28.0	-	57

### POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free air ambient temperature.


The power dissipation can be calculated according type detail specification “HQN-384-01/101: Technical information film capacitors with the typical tgδ of the curves”.

The component temperature rise ( $\Delta T$ ) can be measured (see section “Measuring the component temperature” for more details) or calculated by  $\Delta T = P/G$ :

- $\Delta T$  = Component temperature rise ( $^{\circ}\text{C}$ )
- $P$  = Power dissipation of the component (mW)
- $G$  = Heat conductivity of the component (mW/ $^{\circ}\text{C}$ )

### MEASURING THE COMPONENT TEMPERATURE

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded ( $T_{\text{amb}}$ ) and maximum loaded condition ( $T_{\text{C}}$ ).

The temperature rise is given by  $\Delta T = T_{\text{C}} - T_{\text{amb}}$ .

To avoid radiation or convection, the capacitor should be tested in a wind-free.

### APPLICATION NOTE AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as cross-the-line capacitors without additional protection, as described hereunder. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

To select the capacitor for a certain application, the following conditions must be checked:

1. The peak voltage ( $U_{\text{P}}$ ) shall not be greater than the rated DC voltage ( $U_{\text{Rdc}}$ )
2. The peak-to-peak voltage ( $U_{\text{P-P}}$ ) shall not be greater than the maximum ( $U_{\text{P-P}}$ ) to avoid the ionisation inception level
3. The voltage pulse slope ( $dU/dt$ ) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by  $U_{\text{Rdc}}$  and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_0^T \left( \frac{dU}{dt} \right)^2 \times dt < U_{\text{Rdc}} \times \left( \frac{dU}{dt} \right)_{\text{rated}}$$

$T$  is the pulse duration.

4. The maximum component surface temperature rise must be lower than the limits (see figure max. allowed component temperature rise).
5. Since in circuits used at voltages over 280 V peak-to-peak the risk for an intrinsically active flammability after a capacitor breakdown (short circuit) increases, it is recommended that the power to the component is limited to 100 times the values mentioned in the table “Heat conductivity”.
6. When using these capacitors as across-the-line capacitor in the input filter for mains applications or as series connected with an impedance to the mains the applicant must guarantee that the following conditions are fulfilled in any case (spikes and surge voltages from the mains included).

### Voltage Conditions for 6 Above

ALLOWED VOLTAGES	$T_{amb} \leq 85\text{ }^{\circ}\text{C}$	$85\text{ }^{\circ}\text{C} < T_{amb} \leq 110\text{ }^{\circ}\text{C}$
Maximum continuous RMS voltage	$U_{Rac}$	See "Maximum AC voltage as a function of temperature par. characteristics"
Maximum temporary RMS-overvoltage (< 24 h)	$1.25 \times U_{Rac}$	$0.875 \times U_{Rac}$
Maximum peak voltage ( $V_{O-P}$ ) (< 2 s)	$1.6 \times U_{Rdc}$	$1.1 \times U_{Rdc}$

### INSPECTION REQUIREMENTS

#### General Notes:

Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-17 and Specific Reference Data".

#### Group C Inspection Requirements

SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
<b>SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1</b>		
4.1 Dimensions (detail)		As specified in chapter "General Data" of this specification
4.3.1 Initial measurements	Capacitance Tangent of loss angle at 100 kHz	
4.3 Robustness of terminations	Tensile: Load 30 N; 10 s Bending: Load 15 N; 90°	No visible damage
4.4 Resistance to soldering heat	No pre-drying Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s	
4.4.2 Final measurements	Visual examination  Capacitance Tangent of loss angle	No visible damage Legible marking  $ \Delta C/C  \leq 2\%$ of the value measured initially  Increase of tan $\delta$ : For $C \leq 470\text{ nF} \leq 0.001 (10 \times 10^{-4})$ For $C > 470\text{ nF} \leq 0.0015 (15 \times 10^{-4})$ Compared to values measured initially
4.14 Solvent resistance of the marking	Isopropylalcohol at room temperature Method: 1 Rubbing material: Cotton wool Immersion time: 5 ± 0.5 min	≥ 50 % of values specified in section "Insulation Resistance" of this specification  No visible damage Legible marking
<b>SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1</b>		
4.6.1 Initial measurements	Capacitance Tangent of loss angle at 100 kHz	
4.6 Rapid change of temperature	$\theta A = -55\text{ }^{\circ}\text{C}$ $\theta B = +110\text{ }^{\circ}\text{C}$ 5 cycles Duration $t = 30\text{ min}$ Visual examination	No visible damage



**AC and Pulse Metallized Polypropylene Film Capacitors Vishay Roederstein  
MKP Axial Type**

SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
4.7 Vibration  4.7.2 Final inspection 4.9 Shock  4.9.3 Final measurements	Mounting: See section "Mounting" of this specification Procedure B4 Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s <sup>2</sup> (whichever is less severe) Total duration 6 h  Visual examination  Mounting: See section "Mounting" for more information Pulse shape: Half sine Acceleration: 490 m/s <sup>2</sup> Duration of pulse: 11 ms  Visual examination Capacitance Tangent of loss angle   Insulation resistance	No visible damage   No visible damage $ \Delta C/C  \leq 2\%$ of the value measured initially Increase of tan $\delta$ : For $C \leq 470 \text{ nF} \leq 0.001 (10 \times 10^{-4})$ For $C > 470 \text{ nF} \leq 0.0015 (15 \times 10^{-4})$ Compared to values measured initially $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification
<b>SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B</b>		
4.10 Climatic sequence 4.10.2 Dry heat  4.10.3 Damp heat cyclic Test Db, first cycle 4.10.4 Cold  4.10.6 Damp heat cyclic Test Db, remaining cycles 4.10.6.2 Final measurements	Temperature: 110 °C Duration: 16 h  Temperature: - 55 °C Duration: 2 h  Voltage proof = $U_{Rdc}$ for 1 min within 15 min after removal from testchambers Visual examination  Capacitance Tangent of loss angle   Insulation resistance	No breakdown or flashover  No visible damage Legible marking $ \Delta C/C  \leq 3\%$ of the value measured initially Increase of tan $\delta$ : For $C \leq 470 \text{ nF} \leq 0.001 (10 \times 10^{-4})$ For $C > 470 \text{ nF} \leq 0.0015 (15 \times 10^{-4})$ Compared to values measured in 4.3.1 or 4.6.1 as applicable $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification
<b>SUB-GROUP C2</b>		
4.11 Damp heat steady state 4.11.1 Initial measurements  4.11.3 Final measurements	Capacitance Tangent of loss angle at 1 kHz Visual examination  Voltage proof = $U_{Rdc}$ for 1 min within 15 min after removal from testchamber Capacitance  Tangent of loss angle   Insulation resistance	No visible damage Legible marking No breakdown or flashover  $ \Delta C/C  \leq 3\%$ of the value measured in 4.11.1. Increase of tan $\delta$ : For $C \leq 470 \text{ nF} \leq 0.001 (10 \times 10^{-4})$ For $C > 470 \text{ nF} \leq 0.0015 (15 \times 10^{-4})$ Compared to values measured in 4.11.1 $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification

SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
<b>SUB-GROUP C3 A</b>		
4.12.1 Endurance test at 50 Hz alternative voltage  4.12.1.1 Initial measurements  4.12.1.3 Final measurements	Duration: 2000 h x U <sub>Rdc</sub> at 85 °C 0.875 x U <sub>Rdc</sub> at 110 °C  Capacitance Tangent of loss angle at 100 kHz  Visual examination  Capacitance  Tangent of loss angle  Insulation resistance	No visible damage Legible marking  $ \Delta C/C  \leq 5\%$ compared to values measured in 4.12.1.1  Increase of tan $\delta$ : For C $\leq$ 470 nF $\leq$ 0.001 (10 x 10 <sup>-4</sup> ) For C > 470 nF $\leq$ 0.0015 (15 x 10 <sup>-4</sup> ) Compared to values measured in 4.12.1.1 $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification
<b>SUB-GROUP C4</b>		
4.2.6 Temperature characteristics Initial measurement Intermediate measurements  4.13 Charge and discharge  4.13.1 Initial measurements  4.13.3 Final measurements	Capacitance Capacitance at - 55 °C Capacitance at 20 °C Capacitance at 110 °C  10 000 cycles Charged to U <sub>Rdc</sub> Discharge resistance:  $R = \frac{U_n(\text{Vdc})}{2.5 \times C(dU/dt)}$  Capacitance Tangent of loss angle at 100 kHz  Capacitance Tangent of loss angle  Insulation resistance	For - 55 °C to 20 °C $0\% \leq  \Delta C/C  \leq 2.75\%$ or for 20 °C to 110 °C: $- 5.5\% \leq  \Delta C/C  \leq 0\%$ As specified in section "Capacitance" of this specification  $ \Delta C/C  \leq 3\%$ of the value measured in 4.13.1  Increase of tan $\delta$ : For C $\leq$ 470 nF $\leq$ 0.001 (10 x 10 <sup>-4</sup> ) For C > 470 nF $\leq$ 0.0015 (15 x 10 <sup>-4</sup> ) Compared to values measured in 4.13.1 $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.