

35W TO-220 HIGH POWER RESISTORS

Features


- Non-inductive, thin film technology.
- Thermally enhanced Industry standard TO220 package.
- RoHS compliant.
- Low thermal resistance, 3.3 °C/W resistor hot spot to metal tab.
- Complete thermal flow design available for easy implementation.
- Superior vibration durability.
- Small thin package for high density PCB installation.

Applications

- High frequency circuits and high speed pulse designs.
- Switch mode power supplies.
- Motor control and drive circuits.
- Automotive.
- Industrial computing and measurement systems.



Specification







A	B	C	D	E	F	G	H	J	K	L	M	N
10.6	15.0	4.5	1.5	2.7	5.08	0.75	0.5	1.5	19.0	2.7	3.6	15.0

Specification

Item	Specifications				Test Conditions
Power Rating	35 Watt				-55 to 25 °C flange temperature
Power Rating	2.25 Watt				Free air.
Thermal Resistance	3.3 °C/W				Hot spot to Tab
Resistance Range	0.01-0.09 Ω	0.1-9.1 Ω	10-220 Ω		Up to 51 KΩ also available
Nominal Resistance Series	E6	E12	E24		2.5 Ω and 5.0 Ω also available
TCR	250 ppm/°C	100 ppm/°C	50 ppm/°C		-55 to +155 °C
Tolerance	+/- 5% (J)	+/-1% (F) & 5% (J)	+/-1% (F)		
Operation Temp. Range	-55°C to +155°C				
Max. Operating Volt.	500V or $\sqrt{P \cdot R}$				
Dielectric Withstanding Voltage	2000 Volts DC				60 seconds.
Load Life	ΔR +/- (1.0 % + 0.05 Ω)				25°C, 90 min.ON, 30 min.OFF, 1000 hours.
Humidity	ΔR +/- (1.0 % + 0.05 Ω)				40°C, 90-95%RH, DC 0.1W, 1000 hours.
Temp. Cycle	ΔR +/- (0.25 % + 0.05 Ω)				-55 °C, 30 min., +155 °C, 30 min., 5 cycles
Soldering Heat (Max)	ΔR +/- (0.1 % + 0.05 Ω)				250 +/- 5 °C, 3 seconds,
Solderability	Over 95% of surface				230 +/- 5 °C, 3 seconds.
Insulation Resistance	Over 1,000 MΩ				Between terminals and tab.
Vibration	ΔR +/- (0.25 % + 0.05 Ω)				

Note:
For resistances from 220Ω to 51k Ω the power rating shall be restricted to 20W.

Specifications subject to change without notice.



Notes:

- (1) Electrically isolated metal tab.
- (2) Recommend the use of thermal grease between metal tab and heat sink.
- (3) Thermal design should account for a thermal resistance between resistor and tab of 3.3°C/W and a maximum resistor temperature of 155°C.
- (4) Resistances greater than 220Ω are available, please call factory.
- (5) Surface mount package also available, please call factory.
- (6) Current rating: 25A maximum

Ordering Information

