




注記

1. ウエハーのそりは、長さ25.4に対して0.24MAX.

50.72	47.52	09-65-2129	5277-12A	I2
46.76	43.56	▲ -2119	▲ -11A	11
42.8	39.6	-2109	-10A	10
38.84	35.64	-2099	-09A	9
34.88	31.68	-2089	-08A	8
30.92	27.72	-2079	-07A	7
26.96	23.76	-2069	-06A	6
23	19.8	-2059	-05A	5
19.04	15.84	-2049	-04A	4
15.08	11.88	▼ -2039	▼ -03A	3
11.12	7.92	09-65-2029	5277-02A	2
B	A	EDP NO.	ENG. NO.	極数

REVISED EC NO: J2006-1540 2005/11/10 DRWN: NABEI 2005/11/11 CHKD: KTOYODA 2005/11/15 APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY H. HIRAMOTO		DATE '88/09/29	TITLE KK 3.96/7.92 WAFER ASSY WITH LOCK			
		10 OVER 30 UNDER	± 0.25	CHECKED BY M. FUKUSHIMA		DATE '91/06/26				
		30 OVER	± 0.3	APPROVED BY M. ENOMOTO		DATE '91/06/26	MOLEX MOLEX INCORPORATED			
		ANGULAR	± 3 °	MATERIAL NO.		DOCUMENT NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-5277-001		1 OF 1		
	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								