

Pluggable Input / Output Solutions









Table of Contents

Introduction
Small Form-factor Pluggable (SFP) System - Single Port
Ganged (Single Row) SFP System
Stacked (Dual Row) SFP System
Ganged SFP Cage with Integrated Electrical Connector
SFP with Enhanced EMI Gaskets11
SFP Direct Attach Cable Assemblies 12, 13
10 Gigabit Serial Pluggable Solution (XFP)14
XFP Cable Assemblies
X2 Guide Rail
Dense Wavelength Division Multiplexing (DWDM) SFP System
Part Number Index
Tyco Electronics Global Locations

Disclaimer

While Tyco Electronics Corporation and its affiliates referenced herein ("Tyco Electronics") have made every reasonable effort to ensure the accuracy of the information in this catalog, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current.

Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. Tyco Electronics' only obligations are those in the Tyco Electronics Standard Terms and Conditions of Sale, and in no case will Tyco Electronics be responsible for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products. Users should independently evaluate the suitability of, and test each product for, their application.

The dimensions, specifications, designs, construction, materials and processes in this catalog are for reference purposes only and are subject to change without notice. Please consult Tyco Electronics for the most current product information.

The export of certain Tyco Electronics products is restricted by the Arms Export Control Act (Title 22, U.S.C. Sec 2751, et seq.) or the Export Administration Act of 1979, as amended (Title 50, U.S.C., App. 2401 et seq.). Orders may be subject to export approval by the U.S. Government. Buyer must comply with all applicable export laws of all applicable jurisdictions.

© Copyright 2006, and 2004 by Tyco Electronics Corporation. All International Rights Reserved. AMP and TYCO are trademarks.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners

See inside back cover for Global Contacts and phone numbers.

Restriction on the use of Hazardous Substances (RoHS)

At Tyco Electronics, we're ready to support your RoHS requirements. We've assessed more than 1.5 million end items/components for RoHS compliance, and issued new part numbers where any change was required to eliminate the restricted materials. Part numbers in this catalog are identified as:

RoHS Compliant — Part numbers in this catalog are RoHS Compliant, unless marked otherwise. These products comply with European Union Directive 2002/95/EC as amended 1 January 2006 that restricts the use of lead, mercury, cadmium, hexavalent chromium, PBB, and PBDE in certain electrical and electronic products sold into the EU as of 1 July 2006.

NOTE: For purposes of this Catalog, included within the definition of RoHS Compliant are products that are clearly "Out of Scope" of the RoHS Directive such as hand tools and other non-electrical accessories.

NOTE: Information regarding RoHS compliance is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information provided by our suppliers. This information is subject to change. For latest compliance status, refer to our website referenced at right.

Getting the Information You Need

Our comprehensive on-line RoHS Customer Support Center provides a forum to answer your questions and support your RoHS needs. A RoHS FAQ (Frequently Asked Questions) is available with links to more detailed information. You can also submit RoHS questions and receive a response within 24 hours during a normal work week. The Support Center also provides:

- Cross-Reference from Non-compliant to Compliant Products
- Ability to browse RoHS Compliant Products in our on-line catalog
- Downloadable Technical Data Customer Information Presentation
- More detailed information regarding the definitions used above
 - So whatever your questions when it comes to RoHS, we've got the answers at www.tycoelectronics.com/ leadfree



Catalog 1773408-1 Revised 8-06

2


www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444





Introduction



As a founding member of the Small Form-factor Pluggable (SFP) Multi-Source Agreement (MSA), Tyco Electronics supports the market with a full range of SFP products, including single port and high density SFP products in single row and stacked configurations.

As the market's demand for increased functionality and higher data rates continues to grow, Tyco Electronics responds. Products introduced to support the rapidly expanding product line include: single cage press fit designs, integrated light pipes for port indicators, modified connector contact formation for improved signal integrity,

enhanced spring finger designs for increased EMI suppression, and riding heat sinks for improved thermal management.

Light Pipes:

Tyco Electronics provides a complete line of light pipes for single cages, ganged (single row), and stacked (double row) SFP products.

Enhanced EMI fingers: As the data rates using the SFP form factor increase, the need for increased EMI suppression becomes imperative. Addressing both cabinet and modulegenerated noise, tests suggest Tyco Electronics' enhanced EMI fingers on the SFP cages can add up to 20dB of margin.

Riding Heat Sinks:

As the SFP form factor is adopted across multiple platforms, Tyco Electronics addresses the need for increased thermal dissipation by incorporating riding heat sinks. The riding heat sinks use direct contact to the pluggable module to draw heat away from its source.

As increased functionality and data rates exceeded 10 Gigabits per second, Tyco Electronics actively participated in the 10 Gigabit Serial (XFP) standard, and the X2 MSA, the Xaui based 10 Gigabit solution.

millimeters unless otherwise specified. Values in brackets www.tycoelectronics.com are metric equivalents.

Dimensions are in inches and

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



- RoHS Compliant
- Used in conjunction with 20 pin SMT SFP Connector
- Offers full metal housing for superior grounding and EMI suppression
- Solder, SMT, and Press Fit configurations available
- Single piece and two piece available
- Hot Swappable
- Compatible with SFP MSA **Compliant Modules**
- UL/CSA Report File E28476
- Connector supports data rates beyond 10 Gb/s
- Chassis grounds for pass through EMI protection to 12.5 Gb/s

Applications

- Fiber Channel
- Fast/Gigabit Ethernet
- ATM/SONET/SDH
- InfiniBand (IB)

Technical Documents

Instruction Sheet

408-8495 SFP Connector and Cage Assembly

Application Specification

114-13017 SFP Connector a SMT Cage Assembly 114-13120 SFP Connector and Press Fit Cage Assy

Product Specifications


108-1949 SFP Connector 108-1950 SFP Cage

SFP Documentation

INF-8074

4





Tyco Electronics, continuing to support the OEM market with high speed I/O product, offers a full line of Small Form-factor Pluggable (SFP) products, including SFP cages, connectors, dust caps, and


SFP direct attach cable assemblies. The SFP system can be used with any SFP MSA compliant optic or copper module. The cage system is a copper alloy with nickel subplate with a matte tin finish. The SFP system is part of the Tyco Electronics family of Pluggable I/O solutions.


Part Number	Description	Belly-to-Belly Applications
6367034-1	SFP Bottom Cage (2 pc SMT)	Yes
6367035-1	SFP Top Cage (2 pc)	Yes
1489669-1	One Piece Press Fit	Yes
1489779-1	One Piece Press Fit	No
1489962-1	One Piece SMT or Wave Solder	No
1367629-1	One Piece Press Fit w/Light Pipes	No


Related Products

Part Number	Description
1367073-1	20 pin, surface mount connector; 15µm gold plating
1367073-2	20 pin, surface mount connector; 30µm gold plating
1658197-1	20 pin, surface mount connector; 30µm gold plating with contact surface treatment
1888247-1	20 pin, surface mount connector; enhanced contact formation
1367147-1	SFP Dust Cap with AMP logo
1367147-3	SFP Dust Cap without AMP logo

Note: For a listing of SFP Direct Attach Cable Assemblies, refer to page 12.







Catalog 1773408-1 Revised 8-06

millimeters unless otherwise specified. Values in brackets www.tycoelectronics.com are metric equivalents.

Dimensions are in inches and

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444






Small Form-factor Pluggable (SFP) System - Single Port (Continued)

SFP Top Plate Part Number 6367035-1 2 Pc Cage System



SFP Bottom Plate Part Number 6367034-1

SFP Press Fit Cage Assembly Part Number 1489669-1



SFP Press Fit Cage Assembly with Light Pipe Assembly Part Number 1367629-1



Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



Used in conjunction with

Offers full metal housing

Compatible with SFP MSA **Compliant Modules**

Connector supports data rates beyond 10 Gb/s

Application tooling avail-

able for press fit SFP cages

Product Facts

RoHS Compliant

EMI reduction Solder and Press Fit configurations available

Hot Swappable

Applications

Fiber Channel

Fast/Gigabit Ethernet

ATM/SONET/SDH InfiniBand (IB)

Technical Documents Instruction Sheet 408-8848

Application Specification 114-13017 SFP Connector and


408-8849

SFP Cage Assembly Seating Tool

SFP Cage Assembly Extraction Tool

SMT Cage Assembly

Ganged (Single Row) SFP System



The Ganged SFP product line allows for single row, high density port designs to maximize the horizontal I/O space. The design allows for belly-to-belly orientation to maximize port density. The lateral port-to-port

spacing is minimized to 14.25mm. The entire product family is compliant to RoHS by using a matte tin, pre-plated copper alloy. Port configurations include 1x2, 1x4 and 1x6, with options including:

- Light Pipe Assembly Enhanced EMI contact finger (page 11).
- Application tooling is required for press fit configurations.

Part Number	Port Configuration	PCB Attachment	Light Pipes Included	Special Attributes
1761014-1	1x2	Press Fit	No	
1761007-1	1x2	Press Fit	Yes	
1658744-1	1x4	Press Fit	No	
1888038-1	1x4	Solder Tail	No	No Vent Holes
1658723-1	1x4	Solder Tail	No	
1761008-1	1x4	Press Fit	Yes	
1761015-1	1x6	Press Fit	No	
1658939-1	1x6	Press Fit	Yes	

114-13120 SFP Connector and Press Fit Cage Assy

	-	-
Product S	pecifications	
108-1949	SEP Connector	

108-1950 SFP Cage

Related Products

Part Number	Description
1367073-1	20 pin, surface mount connector; 15µm gold plating
1367073-2	20 pin, surface mount connector; 30µm gold plating
1658197-1	20 pin, surface mount connector; 30µm gold plating with contact surface treatment
1888247-1	20 pin, surface mount connector; enhanced contact formation
1761394-1	SFP Dust Cap

Note: For a complete listing of SFP Direct Attach Cable Assemblies, refer to page 12.

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

6

millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are in inches and

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444






Ganged (Single Row) SFP System (Continued)

Ganged 1x4 Configuration View Part Number 1658744-1



Ganged 1x4 w/Light Pipes Configuration View Part Number 1761008-1



Nominal Dimensions

Part Number	Description	X Dim	Y Dim	Z Dim
1761014-1	1x2 SFP Cage	28.75 [1.132]	9.70 [.382]	50.00 [1.969]
1761007-1	1x2 SFP Cage w/Light Pipes	28.75 [1.132]	13.00 [.512]	55.63 [2.190]
1658744-1	1x4 SFP Cage	57.25 [2.254]	9.70 [.382]	50.00 [1.969]
1761008-1	1x4 SFP Cage w/Light Pipes	57.25 [2.254]	13.00 [.512]	55.63 [2.190]
1761015-1	1x6 SFP Cage	85.75 [3.376]	9.70 [.382]	50.00 [1.969]
1658939-1	1x6 SFP Cage w/Light Pipes	85.75 [3.376]	13.00 [.512]	55.63 [2.190]

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



- RoHS Compliant
- Utilizes fully integrated stacked connector
- Offers full metal housing for superior grounding and EMI reduction
- Incorporates press fit eyeof-the-needle contacts for both mechanical cages and electrical connector
- Connector contacts 30um gold plating w/contact surface treatment
- Hot Swappable
- Compatible with SFP MSA Compliant Modules
- Connector supports data rates beyond 10 Gb/s
- Application tooling available

Applications

- Switches/Routers
- Fiber Channel
- Fast/Gigabit Ethernet
- ATM/SONET/SDH
- InfiniBand (IB)

Technical	Documents
Instruction	Sheet
408-8848	SFP Cage Assembly
	Seating Tool
408-8849	SFP Cage Assembly
	Extraction Tool
408-8850	Stacked SFP Connector Extraction Tool


Application Specification

114-13103 Stacked SFP Connector & Cage Assembly

Product Specifications

108-2161 SFP Connector & Cage Assemblies





The Stacked SFP configuration allows original equipment manufacturers and designers the ability to maximize port density by decreasing the horizontal port spacing from 16.25mm, in the original SFP MSA, to 14.25mm allowing a common wall to support two side by side ports:

- Minimizing height requirements
- Decreasing horizontal port spacing

Tyco Electronics supports 2x1, 2x4 and 2x6 configurations.

For increased flexibility, Tyco Electronics also offers a single row SFP cage with integrated connector, which is footprint compatible with its stacked SFP cages. See page 10 for details.

Part Number	Port Configuration	Height Profile	Light Pipes Included	Press Fit Exemption Tin-Lead on I/O Contacts
1658391-1	2x1	Standard	No	1761937-1
1658628-1	2x1	Low Profile	No	1888126-1
1658859-1	2x1	Low Profile	Yes	
1658390-1	2x4	Standard	No	1761938-1
1658629-1	2x4	Low Profile	No	
1658758-1	2x4	Low Profile	Yes	
1761327-1	2x6	Standard	No	1761939-1
1658894-1	2x6	Low Profile	No	
1658895-1	2x6	Low Profile	Yes	

Note: Tyco Electronics Light Pipe assemblies are sold with the SFP cage assembly. The Light Pipes attach to the top of the SFP cage for clear visibility in a high density application.

Related Products

Part Number	Description
1761394-1	SFP Dust Cap
Note: For a compl Direct Attac	h Cable Assemblies,

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

8


Dimensions are in inches and millimeters unless otherwise specified. Values in brackets n are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444






Stacked (Dual Row) SFP System (Continued)


Standard Profile 2x4 Configuration View Part Number 1658390-1





Low Profile 2x4 with Light Pipe Configuration View Part Number 1658758-1

Low Profile 2x4 Configuration View Part Number 1658629-1



Nominal Dimensions

Part Number	Description	X Dim	Y Dim	Z Dim
1658391-1	2x1 SFP Cage	14.50 [.571]	25.50 [1.004]	63.25 [2.490]
1658628-1	2x1 Low Profile SFP Cage	14.50 [.571]	22.55 [.888]	63.25 [2.490]
1658859-1	2x1 Low Profile SFP Cage w/Light Pipes	14.50 [.571]	28.35 [1.116]	68.75 [2.707]
1658390-1	2x4 SFP Cage	57.25 [2.254]	25.50 [1.004]	63.25 [2.490]
1658629-1	2x4 Low Profile SFP Cage	57.25 [2.254]	22.55 [.888]	63.25 [2.490]
1658758-1	2x4 Low Profile SFP Cage w/Light Pipes	57.25 [2.254]	28.35 [1.116]	68.75 [2.707]
1761327-1	2x6 SFP Cage	85.75 [3.376]	25.50 [1.004]	63.25 [2.490]
1658894-1	2x6 Low Profile SFP Cage	85.75 [3.376]	22.55 [.888]	63.25 [2.490]
1658895-1	2x6 Low Profile SFP Cage w/Light Pipes	85.75 [3.376]	28.35 [1.116]	68.75 [2.707]

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-208-420-8341



Utilizes fully integrated 20 position SFP connector
Offers full metal housing for superior grounding and

 Incorporates press fit eyeof-the-needle contacts for both mechanical cages and electrical connector
Connector contacts 30um gold plating w/contact sur-

Compatible with SFP MSA

Compliant Modules

 Application tooling available

Technical Documents Instruction Sheet 408-8848 SFP Cage Asse

408-8849

408-8850

SFP Cage Assembly Seating Tool SFP Cage Assembly

Extraction Tool Stacked SFP Connector

Extraction Tool

Application Specification 114-13121 SFP Ganged Press Fit Connector & Cage Assembly

Product Specifications 108-2161 SFP Connector & Cage Assembly

Applications Switches/Routers Fiber Channel Fast/Gigabit Ethernet ATM/SONET/SDH InfiniBand (IB)


Connector supports data rates beyond 10 Gb/s

Product Facts RoHS Compliant

EMI reduction

face treatment Hot Swappable AMP


Ganged SFP Cage with Integrated Electrical Connector




compatible with its Stacked SFP product line. The SFP cages are fully RoHS compliant with a Tin finish over Nickel subplate. The connector uses the same press fit technology as was incorporated into the stacked SFP connector system. Products currently offered are in 1x4 and 1x6 configurations.

For increased flexibility with Original Equipment Manufacturers', Tyco Electronics has developed a line of Ganged (Single Row) SFP products that are footprint

Part Number 1658706-1



Part Number 1761322-1



Part Number	Port Configuration	Footprint Compatible with Stacked SFP	Light Pipes Available	Press Fit Exemption Tin Lead on I/O Contacts
1658706-1	1x4	1658390-1 1658629-1	No	No
1761322-1	1x6	1761327-1 1658894-1	No	No
1761967-1	1x6	1761327-1 1658894-1	No	Yes

Related Products

Part Number	Description	
1761394-1	SFP Dust Cap	

Note: For a complete listing of SFP Direct Attach Cable Assemblies,

refer to page 12.

Note: All part numbers are RoHS compliant.

10

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444






SFP with Enhanced EMI Gaskets

Product Facts

- RoHS Complaint
- Used in conjunction with 20 pin SMT SFP connector
- Offers full metal housing for superior grounding and EMI reduction
- Available in 1x1, 1x2, and 1x4 configurations
- Compatible with existing SFP MSA compliant modules
- Hot Swappable
- Enhanced EMI gasket, increasing the contact points between EMI contact fingers on bezel opening
- Double-sided EMI contacts
- 20dB EMI suppression improvement possible
- Connector supports data rates beyond 10 Gb/s

Applications

- Servers
- Storage
- Networking Equipment
- Switching (Telephone)
- SFP+



As data rates exceed 2.5 Gb/s, there is a greater need for higher EMI suppression. Enhanced EMI gaskets are added to the existing SFP product line to meet the increased EMI requirements at higher data rates.

The SFP Cages with enhanced EMI Gaskets are

compatible with the existing SFP MSA panel cutout. The enhanced EMI gaskets offer increased surface area for improved EMI suppression.

EMI gaskets are double sided to reduce emissions between both cage and panel, as well as cage and module. Testing suggests a 20dB improvement on EMI suppression can be achieved.

Initial product will focus on single port, ganged 1x2 and ganged 1x4 configurations.

Part Number	Description
1761783-1	Cage Assy, Enhanced EMI, II Press Fit
1761896-1	Cage Assy, 8 Press Fit, SFP
1761497-1	Cage Assy, 20 Press Fit, Enhanced EMI SFP
1888424-1	Cage Assy, 1x2 Press Fit
1888425-1	Cage Assy, 1x4 Press Fit

Technical Documents

Application Specification 114-13017 SFP Connector and

Cage Assembly Product Specification

108-1950 SFP Cage

Related Products

Part Number	Description
1367073-1	20 pin, surface mount connector; 15µm gold plating
1367073-2	20 pin, surface mount connector; 30µm gold plating
1658197-1	20 pin, surface mount connector; 30µm gold plating with contact surface treatment
1888247-1	20 pin, surface mount connector; enhanced contact formation
1367147-1	SFP Dust Cap with AMP logo
1367147-3	SFP Dust Cap without AMP logo

Note: For a complete listing of SFP Direct Attach Cable Assemblies, refer to page 12.

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06

www.tycoelectronics.com are r

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



10 Gb/s

Ethernet

(1-5 meters)

Applications Servers ■ Storage

■ Supports SFP & SFP+ applications ■ SFP+ active cable assemblies support data rates of 500 Mhz to

Broadband — will work at all frequencies up to and including 8.5 Gb/s Fibre Channel and 10 Gb/s

Low cost solution for short reach applications

Compatible with MSA **Compliant SFP cages**


■ Three stage sequencing — GND, VDD, Signal —

pads engage the connector

Any 8.5 Gb/s Fibre Channel and 10 Gb/s Ethernet applications



SFP Direct Attach Cable Assemblies



Cable Assembly Part Numbers

Description	.5 meter	1 meter	2 meters	3 meters	4 meters	5 meters
2 Gb/s Passive	1902495-1	1902495-2	1902495-3	1902495-4	1902495-5	1902495-6
4 Gb/s Passive	1948134-1	1948134-2	1948134-3	1948134-4	1948134-5	1948134-6
4 Gb/s Active	1948135-1	1948135-2	1948135-3	1948135-4	1948135-5	1948135-6
10 Gb/s Passive	1948136-1	1948136-2	1948136-3	1948136-4	1948136-5	1948136-6
10 Gb/s Active	1812997-1	1812997-2	1812997-3	1812997-4	1812997-5	1812997-6

Note: Contact Tyco Electronics for other configuration / length requirements.

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

12

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



Pluggable Input / Output Solutions




Electronics


8.5 Gb/s Eye Pattern for SFP+ (Active SFP) — 12 meters

- Bit Rate: 8.5 Gb/s
- Source: Advantest 12 Gb/s Source
- Input Voltage: 1000 mV
- Data pattern: PRBS (2^7-1)
- Aggressor Source: HP 8133A
- Aggressor Voltage: 1600 mV
- Aggressor Bit Rate: 3.5 Gb/s
- Eye Opening: 427.0 mV
- Jitter: 34.56 ps
- 12m 24AWG SFP Cable Assembly





- 10 Gb/s Eye Pattern for SFP+ (Active SFP) — 12 meters
- Bit Rate: 10 Gb/s
- Source: Advantest 12 Gb/s Source
- Input Voltage: 1000 mV
- Data pattern: PRBS (2^7-1)
- Aggressor Source: HP 8133A
- Aggressor Voltage: 1600 mV
- Aggressor Bit Rate: 3.5 Gb/s
- Eye Opening: 302.7 mV
- Jitter: 46.8 ps
- 12m 24AWG SFP Cable Assembly



Catalog 1773408-1 Revised 8-06

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



AMP

10 Gigabit Serial Pluggable Solution (XFP)

Product Facts

- Fully compliant to XFP MSA
- RoHS compliant
- Used in conjunction with 30 pin surface mount connector
- Press fit PCB attach
- Improved EMI containment features
 - Module to XFP Cage
 - XFP Cage to Chassis
- Designed to allow for riding heat sink
- Designed for use in bellyto-belly applications

Applications

- 10 Gigabit Ethernet Switches and Routers
- 10 Gigabit Aggregator ports
- ATM/SONET/SDH (0C-192)

Technical Documents Instruction Sheet 408-8723

Application Specification 114-13096

Product Specifications 108-2127

The XFP Multi-Source Agreement (MSA) specifies the next generation pluggable transceiver. Tyco Electronics' line of XFP products is fully compliant with the XFP MSA. The MSA specifies the mechanical and electrical requirements for the pluggable modules, cage hardware, thermal heat sinks, and PCB surface mount connector. This technology converts serial electrical signals to

external serial optical or electrical signals and is intended to be flexible enough to support OC192/STM-64, G.709, and 10 Gigabit Ethernet.

The goal of the XFP MSA is to provide a universal design for the transceiver that will be suitable for all applications (one size fits all).

- Intuitive latch
- Simple design based on SFP where possible

- Provide a range of options for:
 - EMI containment and thermal dissipation that are controlled by various EMI gasket, cage and heat sink designs specified by the customer.
 - Accommodate a wide range of industry applications
 - Provide an industry accepted, robust design that will be accepted by the industry.

Part Number	Description	PCB Attachment
1489951-1	XFP Cage	Press Fit
1658871-1	XFP Cage w/Insulating Tape	Press Fit
1888101-1	XFP Cage without Rear Gasket	Press Fit
1658945-1	XFP Cage w/Insulating Tape & without Rear Gasket	Press Fit
1888116-1	XFP Kit: XFP Cage with SAN Heat Sink (6.5mm)	Press Fit
1888116-2	XFP Kit: XFP Cage with PCI Heat Sink (4.2mm)	Press Fit
1888065-1	XFP Kit: XFP Cage with Networking Heat Sink (13.5mm)	Press Fit
1888481-1	XFP Kit: XFP Cage w/insulating tape and SAN Heat Sink (6.5mm)	Press Fit
1888481-2	XFP Kit: XFP Cage w/insulating tape and PCI Heat Sink (4.2mm)	Press Fit
1888481-3	XFP Kit: XFP Cage w/insulating tape w/Networking Heat Sink (13.5mm)	Press Fit

Related Products

Part Number	Description
788862-1	30 Pos SMT XFP Conn. 15 um gold plating
788862-2	30 Pos SMT XFP Conn, 30um gold plating
1367500-1	30 Pos SMT XFP Conn, 30um gold plating with contact treatment, and enhanced contact formation for high speed signals
1489948-2	XFP Heat Sink Clip
1658294-2	XFP Dust Cap
1542618-2	PCI Heat Sink (4.2mm)
1542656-2	SAN Heat Sink (6.5mm)
1542706-2	Networking Heat Sink (13.5mm)

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

14

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444





- 10 Gb/s Serial
- Excellent EMI/RFI shielding
- XFP compliant
- Part of a complete product line
- Three stage sequencing GND, VDD, Signal addresses the sequence the pads engage the connector

Applications

- Switches
- Routers
- Desktop Applications

Product Offering

XFP Compliant

XFP active cable assembly Part Number 1902639-X

Non-compliant passive assembly

■ XFP passive (no active components, may be suitable for going 6-12 inches card to card Part Number 1902480-1


XFP, 10.0 Meter Length, 10.0 Gb/s



Part Numbers

Description	.3 meter	1 meter	2 meters	3 meters	4 meters	5 meters
XFP Passive	1902480-1	_	_	_		—
XFP Active	_	1902639-1	1902639-2	1902639-3	1902639-4	1902639-5

Note: All part numbers are RoHS compliant.



Catalog 1773408-1 Revised 8-06

millimeters unless otherwise specified. Values in brackets www.tycoelectronics.com are metric equivalents.

Dimensions are in inches and

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



■ Fully supports X2 MSA Used in conjunction with 70 position SMT connector

Product Facts

RoHS Compliant Offers full metal EMI shielding to contact X2 compliant module

Applications Switches Routers

Desktop Applications

Technical Documents


Instruction Sheet

408-8983

Pluggable Input / Output Solutions



X2 Guide Rail



Tyco Electronics, continuing to support the OEM market with high speed I/O product, offers an X2 compliant guide rail system. X2 is a next generation Xaui-based system that offers four channels of data throughput operating up to 3.125 Gb/s. The guide rail is used in

conjunction with an X2 compliant module.

Tyco Electronics offers both a stamped guide rail, with tin finish and a robust die cast rail, with nickel plate.

The X2 Guide Rail System is the latest product to be added to the

Tyco Electronics family of Pluggable I/O solutions. Other products include SFP cages and connectors, High Density SFP cages and connectors, XFP, SFP Direct Attach cable assemblies, and DWDM SFP.

Part Number	PCB Configuration	Material	PCB Attachment
1367608-1	Standard	Stamped Copper Alloy w/Tin Plate	Press Fit
1367610-1	Belly-to-Belly	Stamped Copper Alloy w/Tin Plate	Press Fit
1367709-1	Standard	Die Cast Zinc Alloy	Screw Down
1367710-1	Belly-to-Belly	Die Cast Zinc Alloy	Screw Down

Related Products

Part Number	Description
1367337-1	70 pin, surface mount connector; 15µm gold plating
1367337-2	70 pin, surface mount connector; 30µm gold plating
1658198-1	70 pin, surface mount connector; 30µm gold plating with surface treatment

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06 www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-208-420-8341






Dense Wavelength Division Multiplexing (DWDM) SFP System

Product Facts

- RoHS Complaint
- Used in conjunction with 20 pin SMT SFP Connector
- Offers full metal housing for superior grounding and EMI reduction
- Incorporates press fit eyeof-the-needle contacts for mechanical cages
- Hot Swappable
- Available in Press Fit version only
- Compatible with DWDM MSA compliant transceivers

Applications

- DWDM Switch applications
- High Density application requiring additional Thermal Management



In response to the DWDM market, Tyco Electronics introduced an SFP system incorporating a riding heat sink to the SFP to assist in managing excess heat when using SFP modules. Tyco Electronics adopted a similar design to the industry accepted 10 Gigabit or XFP form factor.

The DWDM SFP solution will include a RoHS press fit cage, a stainless steel heat

sink clip, and an aluminum heat sink.

DWDM SFP Cage product is compatible with any DWDM MSA compliant transceiver.

Part Number	Product Description	PCB Attachment
1367643-1	1x1 DWDM SFP Cage	Press Fit
1367646-1	Heat Sink Clip, Stainless Steel	N/A
1829903-2	DWDM PCI Heat Sink (4.2mm)	N/A
1829904-2	DWDM SAN Heat Sink (6.5mm)	N/A
1829905-2	DWDM Networking Heat Sink (13.5mm)	N/A
1367645-1	DWDM Kit: Cage, Clip and PCI Heat Sink (4.2mm)	Press Fit
1367645-2	DWDM Kit: Cage, Clip and SAN Heat Sink (6.5mm)	Press Fit
1367645-3	DWDM Kit: Cage, Clip and Networking Heat Sink (13.5mm)	Press Fit

Related Products

Part Number	Description
1367073-1	20 pin, surface mount connector; 15µm gold plating
1367073-2	20 pin, surface mount connector; 30µm gold plating
1658197-1	20 pin, surface mount connector; 30µm gold plating with contact surface treatment
1888247-1	20 pin, surface mount connector; enhanced contact formation
1367147-1	SFP Dust Cap with AMP logo
1367147-3	SFP Dust Cap without AMP logo

Note: All part numbers are RoHS compliant.

Catalog 1773408-1 Revised 8-06

www.tycoelectronics.com specifie are met

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444





Part Number Index

Note: This index lists all cataloged parts by base no. only. Complete part nos. (with prefixes and/or suffixes) are shown on the page(s) indicated.

Part No.	Page	Part No.	Page	Part No.	Page
788862	14	1658391	8, 9	1761939	8
1367073	4, 6, 11, 17	1658628	8, 9	1761967	10
1367147	4, 11, 17	1658629	8, 9, 10	1812997	12
1367337	16	1658706	10	1829903	17
1367500	14	1658723	6	1829904	17
1367608	16	1658744	6, 7	1829905	17
1367610	16	1658758	8, 9	1888038	6
1367629	4, 5	1658859	8, 9	1888065	14
1367643	17	1658871	14	1888101	14
1367645	17	1658894	8, 9, 10	1888116	14
1367646	17	1658895	8, 9	1888126	8
1367709	16	1658939	6, 7	1888247	4, 6, 11, 17
1367710	16	1658945	14	1888424	11
1489669	4, 5	1761007	6, 7	1888425	11
1489779	4	1761008	6, 7	1888481	14
1489948	14	1761014	6, 7	1902480	15
1489951	14	1761015	6, 7	1902495	12
1489962	4	1761322	10	1902639	15
1542618	14	1761327	8, 9, 10	1948134	12
1542656	14	1761394	6, 8, 10	1948135	12
1542706	14	1761497	11	1948136	12
1658197	4, 6, 11, 17	1761783	11	6367034	4, 5
1658198	16	1761896	11	6367035	4, 5
1658294	14	1761937	8		
1658390	8, 9, 10	1761938	8		

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444



Argentina – Buenos Aires Phone: +54-11-4733-2200 Fax: +54-11-4733-2211

Brasil - São Paulo +55-11-3611-1311 Phone: +55-11-3611-0397 Fax.

Asia/Pacific

Australia - Sydney Phone: +61-2-9554-2600 +61-2-9502-2556 **Product Information Center:** (Technical Support) +61-2-9840-8200 Phone: Fax: +61-2-9634-6188

India – Bangalore +91-80-285-40800 Phone: +91-80-285-40820 Fax:

Indonesia – Jakarta +65-6482-0311 Phone: +65-6482-1012 Fax:

Europe/Middle East/Africa

Austria - Vienna Phone: +43-1 90 5 60-0 +43-1 90 5 60-1333 Fax:

Belaium - Kessel-Lo Phone: +32-16-35-23-00 +32-16-35-23-52 Fax:

Bulgaria - Sofia +359-2-971-2152 Phone: +359-2-971-2153 Fax:

Czech Republic – Kurim Phone: +420-5-41-162-111 Fax: +420-5-41-162-223

Denmark - Glostrup +45-43-480-452 Phone: +45-43-441-414 Fax:

Egypt - Cairo +20-2-417-76-47 Phone: +20-2-419-23-34 Fax:

Finland – Helsinki +358-95-12-34-20 Phone: +358-95-12-34-250 Fax:

France - Cergy-Pontoise +33-1-3420-8888 Phone: +33-1-3420-8600 Fax: **Product Information Center:** (Technical Support) Phone: +33-1-3420-8943 Fax: +33-1-3420-8623

Canada – Toronto +905-475-6222 Phone: +905-474-5520 Fax: **Product Information Center:** (Technical Support) +905-470-4425 Phone: Fax: +905-474-5525

Colombia - Bogota Phone: +57-1-231-9398 +57-1-660-0206 Fax:

Japan – Toyko

Phone:

Fax:

Fax:

Fax.

Fax:

Fax:

Germany - Bensheim

(Technical Support)

Germany - Langen

Germany – Speyer Phone: +49-6232-30-0

Phone: +49-2247-305-0

Phone:

Phone:

Fax:

Fax:

Fax:

Phone:

Phone:

Fax:

Fax:

Fax:

Great Britain -

Stanmore Middlesex

(Technical Support)

Fax:

Phone: +49-6251-133-0 Fax: +49-6251-133-1600

Product Information Center:

+49-6251-133-1999

+49-6103-709-0

+49-6251-133-1988

+49-6103-709-1223

+49-6232-30-2243

Germany - HTS Division - Neunkirchen

+49-2247-305-122

+44-8706-080-208

Phone: +44-208-420-8341 or 8343

+44-1793-528171

+30-1-9370-655

+44-1793-572-516

+44-208-420-8081

Product Information Center:

Freephone GB: 0800-267-666

Great Britain - Raychem &

Phone: +30-1-9370-396/397

Identification Products

Greece - Athens

+44-1793-572-109

Mexico – Mexico City Phone: +52-55-1106-0800 Fax: +52-5-361-8545

United States - Harrisburg, PA +717-564-0100 Phone: +717-986-7575 Fax: Product Information Center: (Technical Support) Phone: +800-522-6752 Fax: +717-986-7575

New Zealand - Auckland +64-9-634-4580 Phone: +64-9-634-4586 Fax: Philippines - Makati City

+632-848-0171 Phone: Fax: +632-867-8661 People's Republic of China

Hong Kong +852-2735-1628 Phone: +852-2735-0243 Fax: Shanghai

+86-21-64857333/64850602 Phone: +86-21-64856222/54260190 Fax:

Hungary - Budapest +36-1-289-1000 +36-1-289-1010 Phone: Fax:

Ireland - Dublin Phone: +353-1-820-3000 Fax: +353-1-820-9790

Israel - Yokneam +972-4-959-0508 Phone: +972-4-959-0506 Fax:

Italy - Collegno (Torino) Phone: +39-011-4012-111 +39-011-4031116 Fax:

Lithuania - Vilnius +370-5-2131-402 Phone: Fax: +370-5-2131-403

Netherlands - 's-Hertogenbosch +31-73-624-62-46 Phone: Fax: +31-73-621-23-65 Product Information Center: (Technical Support) +31-73-6246-999 . Phone: Fax: +31-73-6246-998

Norway - Nesbru +47-66-77-8886 Phone: +47-66-77-8855 Fax:

Poland - Warsaw Phone: +48-22-45-76-700 +48-22-45-76-720 Fax:

Romania - Bucharest Phone: +40-21-311-3479/3596 Fax: +40-21-312-0574

Russia - Moscow +7-095-926-5506/07/08/09 Phone: Fax: +7-095-926-5505

Russia – St. Petersburg Phone: +7-812-718-8192 +7-812-718-8193 Fax:

For Latin/South American Countries not shown

Phone: +54-11-4733-2015 +54-11-4733-2083 Fax:

Singapore – Singapore Phone: +65-6482-0311 Phone: +65-6482-1012 Fax: **Raychem Products** Phone: +65-4866-151 +65-6545-514 Fax: Identification Products Phone: +65 (0) 6482-0311 +65 (0) 6481-5514 Fax:

Taiwan – Taipei +886-2-8768-2788 Phone: Fax: +886-2-8768-2268

Thailand - Bangkok +66-2-955-0500 Phone: Fax: +66-2-955-0505

Vietnam and Indochina -Ho Chi Minh City Phone: +84-8 930-5546 Phone: +84-8 930-3443 Fax:

Slovenia – Ljubljana Phone: +386-1561-3270 Fax: +386-1561-3240 Fax:

South Africa - Port Elizabeth Phone: +2741-503-4500 +2741-581-0440 Fax:

Spain - Barcelona Phone: +34-93-291-0330 Fax: +34-93-201-7879 Product Information Center:

(Technical Support): Phone: +34-93-291-0330 +34-93-200-3779 Fax:

Sweden – Upplands Väsby Phone: +46-8-50-72-50-00 Fax. +46-8-50-72-50-01

Switzerland - Steinach +41-71-447-0447 Phone: +41-71-447-0444 Fax:

Turkey - Istanbul Phone: +90-212-281-8181/2/3 +90-212-281-8184 Fax:

Ukraine – Kiev +380-044-206-2265 Phone: +380-044-206-2264 Fax:

For Middle East/African Countries Not Shown

+33-1-3420-8866 Phone: +33-1-3420-8300 Fax:

+81-44-844-8183 Phone: +81-44-844-8184 Product Information Center: (Technical Support) +81-44-844-8013 Phone: +81-44-812-3200 Korea - Seoul +82-2-3415-4500 Phone: +82-2-3486-3810 Malaysia - Kuala Lumpur Phone: +60-3-78053055 +60-3-78053066

+81-44-844-8111

+81-44-812-3207

Raychem & Identification Products



Tyco Electronics Corporation Harrisburg, Pennsylvania www.tycoelectronics.com

© 2006 Tyco Electronics Corporation 1773408-1 Revised 8-2006 2.5M LUG FP