



- NOTES:
- 1. Rating: ~~300V 16A~~ 300V 15A  $\triangle 3$   
PITCH: 5.00mm
  - 2. Insulation Withstands Voltage: AC 2500V/MIN
  - 3. Insulation Resistance: 500M $\Omega$  or more at DC500V
  - 4. Using Temperature Range: -40°C~+105°C
  - 5. Suitable Electric Wire: AWG ~~28~14~~ 28~12
  - 6. Undimensioned Tolerances:  $\triangle 4$

$\square$	$\square$	0.05/10
$\perp$	$\parallel$	0.2/10
PITCH ERROR 0.05/10		
UNDIMENSIONS TOLERANCES		

4	SOLDER PIN	O119B00100	P	BRASS	Tin Plated
3	CLAMP	X000003100	P	Stainless Steel	
2	END COVER	O119L2XX00	1	PA66(V0)	M001
1	HOUSING	O119AOXX00	P	PA66(V0)	M001

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
$\triangle 5$					
	WHM	04.09.03	DWG.	DATE	99,12,09
$\triangle 4$	YFY	03.12.30	CHK.	DATE	
$\triangle 3$	YFY	03.05.28	APP.	DATE	
$\triangle 2$	YFY	02.12.23			
REV.	CONTENT	CHK.	DATE	<b>IMO</b>	
				UNITS	MM SHEET/OF 1/2
				SCALE	3.5:1 ( : ) $\oplus$ $\square$
				NAME	20.3000M/XX
				DWG NO.	