


DVSC24 40 and DVSC48 40

Single-pole
Surge Arrester
 $I_{max} = 40kA (8/20)$

Category IEC/EN/VDE:	Class II/Type 2/C
Location of use:	DC power systems
Protection modes:	(+) - PE, (-) - PE, (+) - (-)
Protective element:	MOV
Surge discharge ratings:	$I_n = 20kA, I_{max} = 40kA$
Housing:	Compact design




T connection



Technical data

Type	24	48
In accordance with	IEC-61643-1	
Max. continuous operating voltage (AC/DC) U_c	25/31V	40/56V
(+) - (-)		75/100V
(+) - PE, (-) - PE		275/350V
Nominal discharge current (8/20) I_n	20kA	
Max. discharge current (8/20) I_{max}	40kA	
Protection level U_p (+ / -)	< 0.6kV	
(+, - / PE)	< 1.5kV	
Residual voltage U_{res} (+/-)	< 0.3V	
(+, - / PE)	< 1.0kV	
Follow current I_f	NO	
Response time t_A	< 25ns	
Residual current at U_c I_{PE}	< 2.5mA	
Thermal protection	YES	
Terminal screw torque	max. 4.5Nm	
Short-circuit withstand current	25kA / 50Hz	
Temperature range	- 40°C + 80°C	
Terminal cross section	35mm ² (solid) / 25mm ² (stranded)	
Mounting EN 60715	35mm top-hat rail	
Degree of protection	IP 20	
Housing material	Thermoplastic; extinguishing degree UL 94 V-0	
Dimensions DIN 43880	2TE	
Weight per unit	196g	196g
DVSCRXX40 (with remote contacts)		
Remote contacts	YES	
Contact ratings	AC: 250V/0.5A; 125V/3A	
Terminal cross section	max. 1.5mm ²	
Remote terminal torque	0.25Nm	
Weight per unit	202g	202g
Packaging dimensions (single unit)	109 x 76.5 x 41.5mm	

Connection diagram DVSCXX 40



Dimensions

