Euroamp 60 dc servo amplifier

MSE421

MSE 421 provides a continuous output power rating up to 60 watts with precise servo control of dc servo motors. Operating from a single rail supply which enables battery operation if required, the unit utilises a MOSFET based **linear** output stage with the following operating advantages:


- Virtually zero electrical emissions
- Improved smoothness of motor operation
- · Increased motor life
- Suitable for low inductance motors without the need for an additional choke.



Euroamp 60 is packaged on a standard extended Eurocard format using surface mount technology to provide compact overall size and high reliability. The differential amplifier based input stage incorporates control technology based on many years experience in servo system design with the following features:


- · adjustable peak output current up to 4 amps
- independently adjustable continuous output current up to 2 amps
- choice of velocity control using armature voltage sensing or tacho feedback
- optional torque control or positional control using analogue positional feedback signal
- plug-in personality header to match the drive to specific motor characteristics
- optional automatic velocity ramp for smooth starts using stepped input signal change
- directionally sensitive end of travel limit signal inputs
- remote enable signal input
- · front panel adjustments of servo loop constants for easy commissioning
- front panel diagnostic LED display of drive condition.

Euroamp 60 Block Diagram





dimensions mm.



specification

Euroamp 60 Type number		MSE 421-60
Version with 3U high front panel		PM 421 - 60
Supply 10 - 30 Vdc		
Maximum output voltage		<u>+</u> 28 Vdc
Maximum continuous output current		2 amps
Maximum peak current		4 amps
motor stall protection / over correct protection		I^2T
Input proportional control signal		<u>+</u> 10 Vdc
Control options		
Velocity Control options		using tacho or armature voltage feedback
Positional control		using analogue feedback signal
Torque control		motor torque proportional to <u>+</u> 10 V signal
Front panel adjustments		Proportional gain speed scaling
		derivative feedback zero offset
		motor acceleration
Front panel diagnostics		power on indicator
		I ² T indicator
		fault indicator
Personality header functions		Tacho feedback scaling
		Armature feedback link
		tuning of integration circuit
		derivative circuit scaling
		Armature feedback scaling
		Time constant scaling
		Peak current scaling peak / continuous current ratio
external signals		peak / continuous current ratio
reference supplies	outputs	+ 10 Vdc & - 10 Vdc output @ 3 mA
proportional command signal	•	+ 10 V dc & - 10 V dc odiput @ 3 mA
	inputs	+ 10 V
torque control command signal enable (when selected internally)	input	± 10 V + 10 V - 30 Vdc signal
,	input	
Tacho feedback signal	input	± voltage signal internally scaled on header
Motor current	output	monitors motor torque
+ Direction overtravel limit	input	inhibits drive in positive direction
- Direction overtravel limit	input	inhibits drive in negative direction
Drive healthy	output	indicates over current or over temperature
		or I ² T limiting

Connections

Recommended motherboard for fitment to 19 in. rack systems : MSB520 Recommended motherboard for mounting on cabinet back panel : 2MH

Mclennan Servo Supplies Ltd. Tel: +44 (0)8707 700 700 www.mclennan.co.uk

