DuPont	Electronics	PRODUCT SPECIFICATION	DPS-12-011				
TITLE			PAGE 1 OF 10	REV <b>F</b>			
	MINIT	K II CONNECTORS	AUTHORIZED BY: BS LOW	DATE 29JUL92			

#### 1. SCOPE

Minitek II connector is a double row, vertical card connector designed for use on 2.0 mm center to center holes and available in vertical and right angle applications. This specification is intended to cover the performance and evaluation conditions of the connector.

#### 2. MATERIAL & FINISH

#### 2.1 Terminal

Material : Phosphor Bronze

Finish : Overall 1.27 um Min Nickel underplate

Solder tail - 1.5-7.6 um Min Tin/Lead

(85/15) plating

Contact area- (a) 0.76 um Min Au

(b) 0.38 um Min Au

(c) 0.20 um Min Au

#### 2.2 Housing

a) Material : Glass-filled PBT

Color : Black Flammability: UL 94V-0

b) Material : Glass-filled PCT Color : Beige / Black

Flammability: UL 94V-0

#### 2.3 Header Pin

Material : Phosphor Bronze

Finish : (a) 0.20 um Au over 1.27 um Nickel underplate

(b) 0.76 um Au over 1.27 um Nickel underplate
(c) 0.38 um Au over 1.27 um Nickel underplate
(d) 0.38 um GXT Palladium-Nickel Alloy over 1.27

um Nickel underplate

(e) 0.76 um GXT Palladium-Nickel Alloy over 1.27

um Nickel underplate

#### 2.4 Header Body

a) Material : Glass-filled Nylon 6,6

Color : Black Flammability: UL 94V-0

b) Material : Glass-filled PCT Color : Beige / Black

Flammability: UL 94V-0

DuPont Electronics	PRODUCT SPECIFICATION	DPS-12-011	
TITLE		PAGE 2 OF 10	REV F
MINI	TEK II CONNECTORS	BS LOW	29JUL92

### PERFORMANCE REQUIREMENTS

Rating Voltage : 200V, AC/DC 3.1

Rating Current : 2A, AC/DC 3.2

Operating Temperature Range: -40°C to 105°C (For Nylon 6,6 & PBT mat'l) 3.3

-55°C to 125°C (For PCT material)

(including temperature rise caused by application of current)

Performance 3.4

> Unless otherwise specified, when tested under the ambient conditions in accordance with JIS-5020 as described below and evaluated with the sequence listed in Table 1, the connector shall meet the requirements in Para. 3.5.

: 5°C to 35°C (a) Temperature : 45 to 85% Relative Humidity (b)

: 860 to 1060 mb Atmospheric Pressure (c)

#### 3.5 Requirements

### 3.5.1 Electrical Characteristics

#### 3.5.1.1 Contact Resistance

The contact resistance shall not exceed 20mg before test or 25ma after test when measured under the following conditions :-

(a) Method of Connection : See Figure 1 : 10mA DC (b) Test Current (c) Open Circuit Voltage : 20mV DC

#### 3.5.1.2 Insulation Resistance

insulation resistance of the connector shall not be less than 1000Ms when measured in accordance with MIL-STD-202, Method 302. The following details shall apply :-

: 500V DC for 1 Minute (a) Test Voltage (b) Special Preparation : The connector shall not be mounted on PC Board

adjacent (c) Points of Measurement: Between

terminals

DuPont	Electronics	TYPE PRODUCT SPECIFICATION	DPS-12-011			
TITLE	<u> </u>		PAGE 3 OF 10	REV F		
	MINITE	K II CONNECTORS	BS LOW	DATE 29JUL92		

### 3.5.1.3 Dielectric Withstanding Voltage

There shall be no evidence of arc-over or insulation breakdown when the unmated connector is tested in accordance with MIL-STD-202, Method 301. The following details shall apply :-

(a) Test Voltage

: 650V AC for 1 Minute

(b) Special Preparation : The connector shall

not be mounted on the

PC Board

(c) Points of Measurement: Between

adjacent

terminals

#### 3.5.1.4 Temperature Rise

The temperature rise shall not exceed 30°C when measured using thermocouple under the following conditions :-

(a) Current Applied

: 2A DC

(b) Special Preparation : The connector shall

be

connected

series

(c) Points of Measurement: At a terminal located

at or near the middle

of the connector

# 3.5.2 Environmental Characteristics

### 3.5.2.1 High Temperature

There shall be no evidence of cracking, swelling or other damage which would be detrimental to the function of the connector. The contact resistance shall not exceed 25mg after the mated connector is exposed to a high temperature environment in accordance with MIL-STD-202, Method 108A.

The following details shall apply :-

(a) Ambient Temperature : 105 ± 2°C

(b) Duration

: 44 Hours

DuPont	Electronics	PRODUCT SPECIFICATION	DPS-12-011	
TITLE			PAGE 4 OF 10	REV F
	MINIT	EK II CONNECTORS	BS LOW	DATE . 29JUL92

### 3.5.2.2 Humidity

There shall be no evidence of cracking, swelling or other damage which would be detrimental to the function of the connector after the mated connector is exposed to a high humidity ambience in accordance with MIL-STD-202, Method 103B. The contact resistance shall not exceed 25m<sub>A</sub> and insulation resistance shall not be less than 100m<sub>A</sub>.

The dielectric withstanding voltage test shall be performed after the humidity test and the connector shall meet the requirements described in Para. 3.5.1.3.

The following details shall apply :-

(a) Ambient Tempeature : 40 ± 2°C (b) Relative Humidity : 90 to 95% (c) Duration : 96 Hours

#### 3.5.2.3 Salt Spray

There shall be no evidence of cracking, swelling or oxidation which would be detrimental to the function of the connector and the contact resistance shall not exceed 25m. after the mated connector is exprosed to a salt fog ambience in accordance with MIL-STD-202, Method 101D.

The following details shall apply :-

(a) Salt Solution : 5% By Weight

(b) Ambient Temperature : 35°C(c) Duration : 48 Hours

(d) Specific Treatment : The measurement shall

be conducted after the mated conductor is mildly rinsed in water running remove deposition of followed by salt, natural drying by it for 24 placing room at hours

temperature.

DuPont	Electronics	PRODUCT SPECIFICATION	DPS-12-011	
TITLE		PAGE 5 OF 10	REV F	
	MINITE	K II CONNECTORS	BS LOW	DATE 29JUL92

#### 3.5.2.4 Thermal Shock

There shall be no evidence of cracking, swelling or other damage which would be detrimental to the function of the connector after the mated connector is exposed to alternate cycles of extreme high and low temperature in accordance The contact with MIL-STD-202, Method 107D. resistance shall not exceed 25ms.

The following details shall apply :-

:  $-55^{+0}$ °Cfor 30 minutes followed by (a) Temperature Range

 $85^{+3}_{-0}^{\circ}C$  for 30 minutes

: 5 Cycles (b) Number of Cycles

# 3.5.2.5 Hydrogen Sulfide (H<sub>2</sub>S) Exposure

There shall be no evidence of cracking, swelling or oxidation which would be detrimental to the function of the connector and the contact resistance shall not exceed 25mg after the mated connector is exposed to a moist H2S environment.

The following details shall apply :-

(a) Ambient Temperature : 40°C

(b) Relative Humidity : 70 to 80% : 10 ± 5 PPM

(c) H<sub>2</sub>S Density

DuPont	Electronics PRODUCT SPECIFICATION		DPS-12-011				
TITLE			PAGE 6 OF 10	REV F			
	MINIT	EK II CONNECTORS	BS LOW	DATE 29JUL92			

# 3.5.3 Mechanical Characteristics

#### 3.5.3.1 Vibration

There shall be no evidence of physical or mechanical damage, or disassociation of parts, and no evidence of discontinuity greater than I microsecond when the mated connector is subjected to mechanical vibration. The contact resistance shall not exceed 25mm after the test. The test shall be in accordance with MIL-STD-202, Method 201A, and the following details shall apply:

(a) Frequency

: 10-55-10 Hz/Min,

Sweep Vibration

(b) Amplitude

: 1.5mm Max.

(c) Test Current

: 0.1A

(d) Duration

: 2 hours along each of three perpendicular axes (6 hours total)

(e) Mounting : See Figure 2

# 3.5.3.2 Contact Retention Force in Housing

Each contact retention force shall be more than 0.5 kg when the solder leg is pushed along axial direction at the speed of 25mm/min.

# 3.5.3.3 Post Retention Force in Header

Each post retention force shall be 1.0 kg min. when the post is pushed along axial direction at the speed of 25mm/min.

# 3.5.3.4 Mating/Unmating Force

When the connector is subjected to 20 cycles of mating/unmating operation, insertion and withdrawal forces shall conform to the following requirements at initial, 10th and 20th cycles:

(a) Insertion Force

: 180g x Pos Max.

(b) Withdrawal Force

: 20g x Pos Min.

-3005 REV 7/20/90

DuPont Electronics	PRODUCT SPECIFICATION	DPS-12-011	
TITLE	PAGE 7 0F 10	REV F	
MINIT	TEK II CONNECTORS	BS LOW	DATE 29JUL92

### 3.5.3.5 Durability

Contact resistance after 100 cycles of mating/unmating operation shall not exceed  $25m\,\Omega$ .

# 3.5.3.6 Solderability

The test shall be applied to solder leg of both contact and post. No less than 90% of the dipped surface of the solder leg is dipped in solder bath. The test shall be in accordance with MIL-STD-202, Method 208C, and the following details shall apply:

(a) Flux : Alpha 100, GX-5 or

GX-7

(b) Solder : 60-40 Tin/Lead (c) Flux Immersion Time : 5 to 10 Seconds (d) Solder Temperature : 230°C ± 5°C (e) Dipping Time : 3 ± 0.5 Seconds

# 3.5.3.7 Solder-Heat Resistance

The test shall be applied to solder leg of both contact and post. There shall be no evidence of physical damage detrimental to the function of the connector when each solder leg of the connector mounted onto a PC Board is dipped in a bath.

The following details shall apply :-

(a) Solder Temperature : 260°C ± 5°C

(b) Dipping Time :  $5 \pm 0.5$  Seconds (c) Immersion Depth : The end of the solder

) immersion pepth : The end of the solder leg coming through the PCB Board

# CONTACT RESISTANCE




Fig. 1

# VIBRATION




Fig. 2

DuPont Electr	PRODUCT SPECIFICAT	PAGE REV	
TITLE	MINITEK II CONNECTORS	9 OF 10 F  AUTHORIZED BY DATE  BS LOW 29JUL9	92

. NUMBERS	
NUMBERS	
TABLE 1 : TEST SEQUENCE NOTE : NUMBERS INDICATE SEQUENCE IN WHICH TESTS ARE PERFORMED.	

			,																_
2 2	:  =	13	12	Ξ	12	9	۵	,  -	•	O.	Ų.	4	u		,				
SOLDER HEAT RESISTANCE			POST RETENTION FORCE	CONTACT RETENTION FORCE	VIBRATION		וחפראאר טחטטי	COLL CLOCK	SALT SODAY	HUMIDITY	HIGH TEMPERATURE	TEMPERATURE RISE	DIELEC. WITHSTANDING VOCTO		INCHE ATION RESISTANCE	CONTACT RESISTANCE		TEST DESCRIPTION	
$\prod$	$\dashv$	+	+	$\dagger$	+	1	+	1		Ø	-	†	6	3	Ð Ð		٠		
H	+	+	1	1			7					E			•		^	3	
	1	+	$\dagger$	1	+	1					0	)	1			8	١	"	
H	7	十	T	$\top$	1	7	7			0						99	ŀ		
$\Box$	$\dashv$	1	$\dashv$	1	$\top$	1			0	ľ						00	,	_	
			1	1	1	7		0			1					8	ď	•	ار
		寸	1	1	7	-	9	_								തന്ദ്രത്തന്ത്രത്തെയ്യ	3	ᆀ	153
		7	1	$\top$	1	9				T						<u>e</u>	3	<u></u>	TEST GROUP
			1	1	e	$\neg$	$\overline{\cdot}$										-	<u>۷</u>	P
				0	$\neg$										L		1	티	
			Θ												_	1		듸	
		0						L	L		1	_	_		L	E	3	10 11 12 13	٠.
	Ө								L	1		_				1	_		
Θ							_	L		1	_	_	_		L	_	_	4	_
3.5.3.7	3.5.3.6	3.5.3.5	3.5.3.4	3 5 3 3	3.5.3.2	3.5.3.1	3,5,2,5	3,3.2.4	1,916.7		3.5.2.2	3.5.2.1	3.5.1.4	3.5.1.3		5.1.2	2	ME HOO	TEST

DuPont Electronics PRODUCT SPECIFICATION	PAGE	REV
TITLE	10 OF 10	F
MINITEK II CONNECTORS	AUTHORIZED BY: BS LOW	29JUL92

# REVISION RECORD

REV	PAGE	ECR	DATE
Α	01	S00028	23 APR 90
В	06	S00244	02 OCT 90
С	02	V12369	22 AUG 91
D	01	S10307	11 SEP 91
E	07	\$20204	29 JUL 92
F	02	\$30339	22 SEP 93