



213 High Temperature Masking Tape

Product Data Sheet

Updated : March 1996
Supersedes : October 1993

Product Description A naturally coloured smooth creped paper treated with a high quality saturant to prevent solvent penetration. The specially formulated adhesive performs in applications requiring very high temperatures.

Physical Properties
Not for specification purposes

Adhesive Type	Firm synthetic rubber-resin.	
Backing	Saturated creped paper.	
Thickness (ASTM D-3652)	165 µm	
Tape Colour	Natural	
Shelf Life	12 months from date of despatch by 3M when stored in the original carton at 21°C (70°F) & 50 % Relative Humidity	

Performance Characteristics
Not for specification purposes

Adhesion to Stainless Steel ASTM D-3330	3.8 N/10mm	
Tensile Strength ASTM D-3759	35.0 N/10mm	
Elongation at Break ASTM D-3759	10.0 %	
Temperature Range Maximum	175 °C	

Additional Product Information

No 213 has the firmest and generally most transfer resistant adhesive of all 3M paper tapes. A very close product is No. 214 which should always be evaluated at the same time.

This tape has often been used to overcome paint puffing complaints despite its rather high adhesion. Its firm adhesive does not anchor itself as softer adhesives often do.

This firm adhesive often makes No. 213 the best tape for use on treated metal surfaces.

This tape is not recommended for applications requiring outdoor exposure, but generally can be used on indoor applications for a reasonable length of time.

No. 213 has been used in bake cycles up to 175°C for one hour with clean, easy removal. Performance is governed by total time, temperature, surface tape is applied to, and any other coatings and conditions.

Date : March 1996
213 High Temperature
Masking Tape

Application Techniques	1. Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure develops better adhesive contact & thus improves bond strength.	surfaces must be clean dry and well unified. A typical surface cleaning solvent is isopropyl alcohol & water. Use proper safety precautions for handling solvents.	Initial tape application to surfaces at temperatures below 10°C (50°F) is not recommended because the adhesive becomes too firm to adhere readily. However once properly applied low temperature holding is generally satisfactory.
	2. To obtain optimum adhesion, the bonding	3. Ideal tape application temperature range is 21°C to 38°C (70°F to 100°F).	

Applications	No. 213 should be considered whenever treated metals, especially light metals, are encountered.	It should also be considered whenever a bake cycle exceeds one hour at 150°C or wherever a moderate tack tape is desired.
---------------------	---	---

Features	Advantages	Benefits
Highly cured adhesive.	Good high temperature holding.	Less edge lifting/less rework and labour.
Specially treated crepe paper backing.	Adhesive transfer resistance.	Clean removal/less clean up.
	Sliver resistance.	One piece removal/less labour.
	Conformability.	Easier handling/less time involved.
Exclusive backsize treatment.	Easy tear.	Better handling/less waste.
	Solvent and moisture resistance.	Reduces bleed through/less rework
	Controlled unwind.	Easier to use/less waste.

3M is a trademark of the 3M Company.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.



Specialty Tapes & Adhesives

© 3M United Kingdom PLC 1996

3M United Kingdom PLC
3M House,
28 Great Jackson Street,
Manchester,
M15 4PA

Customer Service :
Tel 0161 236 8500
Fax 0161 237 1105

3M Ireland
3M House, Adelphi Centre,
Upper Georges Street,
Dun Laoghaire, Co. Dublin,
Ireland

Customer Service :
Tel (01) 280 3555
Fax (01) 280 3509