

Convel 90000 Series Chassis Mounting AC/DC Unregulated Linear Power Supplies

A range of DC power supplies manufactured to a high standard suitable for a wide range of industrial control applications. All models feature detachable terminal covers to provide easy access for connection to the input and output terminals. This cover is recommended to be secured back in position prior to use.

- ◆ 12, 24 or 48V DC output
- ◆ 120 to 360 Watt
- ◆ Suitable for many industrial applications e.g. relays, solenoids, DC motors etc.
- ◆ Universal input
- ◆ 3.75kV isolation safety transformer
- ◆ Quality UK design and manufacture

Calex Electronics Limited

PO Box 2, Leighton Buzzard
Bedfordshire, England LU7 4AZ
Tel: +44 (0)1525 373178/853800
Fax: +44 (0)1525 851319
Lo-call Tel: 0845 3108053
E-mail: info@calex.co.uk
Online: <http://www.calex.co.uk>



GENERAL SPECIFICATIONS

Input	115/230VAC 50/60Hz
D.C. Output	See Model Chart
Load Regulation	20% or 3V whichever is the greater for 20 to 100% load change
Output Ripple & Noise	1.5Vrms maximum
Operating Temperature	0°C to +40°C
Isolation	Input to ground: 3750VAC min. Input to output: 3750VAC min. Output to ground: 500VAC min.
Safety	In accordance with EN60950 (Construction uses safety bobbin approved to VDE 0551)
Output overcurrent	Circuit breakers

Model	Output Voltage	Output Current	Output Power
91210	12V	10A	120W
91220	12V	20A	240W
92405	24V	5A	120W
92410	24V	10A	240W
92415	24V	15A	360W
94805	48V	5A	240W

MECHANICAL

Overall Dimensions	l x w x h: 210 x 152.1 x 140.1mm
Weight	91210: 3.9kg 91220: 5.8kg 92405: 3.9kg 92410: 5.8kg 92415: 7.7kg 94805: 5.8kg
Mechanical Format	All units are supplied fully enclosed as standard
Mounting Orientation	Units may be mounted horizontally as shown on the outline drawing overleaf, or vertically with the cables entering from below.
Ventilation and Cooling	Units are convection cooled and therefore require free air flow around the chassis.
Fixings	Units have 4 x 5.6mm (0.2in) mounting holes provided
Connectors	The following connectors are provided on the power supply: Screw terminals are provided for input and output connections Input voltage selection is achieved using terminal block links

OUTLINE DRAWING

All dimensions are nominal and are in mm.

