

**GD-3300****Combustible Gas Leak Detector****Features**

**Highly sensitive and reliable**

**Easy to Use:** One-hand operation with thumb controlled tick adjust knob. Tick accelerates when sensor tip approaches leak.

**Use in contaminated Environments:** Eliminates background gas concentration with fully adjustable tick rate.

**Pinpoint small leaks:** Detects all combustible gas leaks even tiny leaks.

**Specifications**

<b>Pump Driven field Calibrateable Range</b>	<b>10 PPM</b>
<b>Sensor Type</b>	<b>Solid State</b>
<b>Alarm</b>	<b>Visible &amp; Audible at 10% LEL for Methane. Can be calibrated for other concentrations or gases.</b>
<b>Warm-up</b>	<b>Approx. 1 minute</b>
<b>Response Time</b>	<b>Less than 2 sec. (up to 40% LEL)</b>
<b>Duty Cycle</b>	<b>Intermittent</b>
<b>Probe Length</b>	<b>16"</b>
<b>Battery</b>	<b>3 "C" Alkaline</b>
<b>Battery Life</b>	<b>8 hours Continuous Use Typical</b>
<b>Size (H x W x D): 221mm x 72mm x 46mm</b>	
<b>Weight: 520g</b>	

Copyright © 1999-2005 All rights reserved STANDARD Instruments Co., Ltd.

GD-3300

CE, EMC  
EN:50081-1, EN:50082-1

