



SAFETY DATA SHEET RUBBER ROLLER RESTORER

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME RUBBER ROLLER RESTORER
PRODUCT NO. RRR250 [ERRR250]
SUPPLIER ELECTROLUBE. A division of
HK WENTWORTH LTD
KINGSBURY PARK, MIDLAND
ROAD
SWADLINCOTE
DERBYSHIRE, DE11 0AN
UNITED KINGDOM
+44(0)1283 222 111
+44(0)1283 550 177
info@hkw.co.uk
EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

May cause long-term adverse effects in the aquatic environment.

CLASSIFICATION R53.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
C11-C15 ISO-ALKANES	292-460-6	90622-58-5	30-60%	Xn;R65. R66.
C9-C12 ISO-ALKANES	292-459-0	90622-57-4	30-60%	Xn;R65. R66,R53.
3-BUTOXYPROPAN-2-OL	225-878-4	5131-66-8	10-30%	Xi;R36/38

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Provide rest, warmth and fresh air.

INGESTION

Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

RUBBER ROLLER RESTORER

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact.

STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
3-BUTOXYPROPAN-2-OL	SUP	50 ppm				
C11-C15 ISO-ALKANES			1200 mg/m3			
C9-C12 ISO-ALKANES			1200 mg/m3			

ENGINEERING MEASURES

No particular ventilation requirements.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

If risk of splashing, wear safety goggles or face shield.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of skin contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid		
COLOUR	Colourless		
ODOUR	Characteristic		
SOLUBILITY	Immiscible with water		
BOILING POINT (°C)	>173 (343.4 F)	MELTING POINT (°C)	<-50 (-58 F)
RELATIVE DENSITY	>=0.790 @ 20 °c (68 F)	VISCOSITY	1.48 mPas @ 25 °c (77 F)
FLASH POINT (°C)	> 60 (140 F) CC (Closed cup).	AUTO IGNITION TEMPERATURE (°C)	> 200 (392 F)
FLAMMABILITY LIMIT - LOWER(%)	0.60	FLAMMABILITY LIMIT - UPPER(%)	7.0

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid excessive heat for prolonged periods of time.

11 TOXICOLOGICAL INFORMATION

TOXICOLOGICAL INFORMATION

No information available.

RUBBER ROLLER RESTORER

HEALTH WARNINGS

No specific health warnings noted.

No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.

OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

Name	3-BUTOXYPROPAN-2-OL
Toxic Dose 1 - LD 50	2612-5500 mg/kg (oral rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Not regarded as dangerous for the environment.

Name	3-BUTOXYPROPAN-2-OL
LC 50, 96 Hrs, FISH mg/l	560-1000
EC 50, 48 Hrs, DAPHNIA, mg/l	>1000

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION

	No transport warning sign required.		
ROAD TRANSPORT NOTES	Not Classified		
RAIL TRANSPORT NOTES	Not Classified.		
SEA TRANSPORT NOTES	Not Classified.		
AIR TRANSPORT NOTES	Not Classified.		
ADR CLASS	Not classified for transportation.	MARINE POLLUTANT	No.

15 REGULATORY INFORMATION

RISK PHRASES

R53 May cause long-term adverse effects in the aquatic environment.

SAFETY PHRASES

NC Not classified.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

EU DIRECTIVES

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

RUBBER ROLLER RESTORER

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Pawel Zmarzly

REVISION DATE

NOVEMBER 2009

REV. NO./REPL. SDS

3

GENERATED

SDS NO.

11029

RISK PHRASES IN FULL

R36/38

Irritating to eyes and skin.

R53

May cause long-term adverse effects in the aquatic environment.

R65

Harmful: may cause lung damage if swallowed.

R66

Repeated exposure may cause skin dryness or cracking.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.