

Spezifikation für Freigabe / specification for release

Kunde / customer: _____

Artikelnummer / part number: **744901012**

LF




Bezeichnung: **Dünnsfilm-SMD-Induktivität WE-TCI**

description: **Thinfilm-Chip-Inductor WE-TCI**

DATUM / DATE: 2005-08-17

A Mechanische Abmessungen / dimensions




	Größe / size 0402	
A	$1,0 \pm 0,05$	mm
B	$0,5 \pm 0,05$	mm
C	$0,32 \pm 0,05$	mm
D	$0,2 \pm 0,1$	mm
E	0,4	mm
F	0,5 - 0,6	mm
G	1,4 - 1,5	mm

B Elektrische Eigenschaften / electrical properties

Eigenschaften / properties	Testbedingungen / test conditions		Wert / value	Einheit / unit	tol.
Induktivität / inductance	500 MHz	L	1,2	nH	$\pm 0.1nH$
Güte Q / Q factor	500 MHz	Q	13		min.
Güte Q / Q factor	500 MHz	Q	21,41		typ.
DC-Widerstand / DC-resistance		R_{DC}	0,10	Ω	max.
DC-Widerstand / DC-resistance		R_{DC}	0,06	Ω	typ.
Nennstrom / rated current	$\Delta T = 30 K$	I_{DC}	700	mA	max.
Eigenres.-Frequenz / self-res.-frequency		SRF	12	GHz	min.

C Lötpad / soldering spec.:



Land Pattern

D Prüfgeräte / test equipment

HP 4287A + 16196B für/for L und/and Q/ RDC

HP 8753D für/for SRF

E Testbedingungen / test conditions

Luftfeuchtigkeit / humidity: 33%

Umgebungstemperatur / temperature: +20°C

F Werkstoffe & Zulassungen / material & approvals

Basismaterial / base material: Al_2O_3
 Terminal electrode: Sn
 Conductor: Ag + Cu

G Eigenschaften / general specifications:

Umgebungstemp. / ambient temperature: -40°C ... + 85°C

Betriebstemp. / operating temperature: -40°C ... + 125°C

Lagerbedingungen / storage conditions: -10°C ... + 40°C

30 ... 70% RH

Freigabe erteilt / general release:	Kunde / customer			
Datum / date	Unterschrift / signature			
	Würth Elektronik			
		AWe	Version 2	05-08-17
		AWe	Version 1	04-10-11
Geprüft / checked	Kontrolliert / approved	Name	Änderung / modification	Datum / date

Würth Elektronik eiSos GmbH & Co.KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 -3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer : _____

Artikelnummer / part number: **744901012**

LF



RoHS compliant





Bezeichnung : **Dünnsfilm-SMD-Induktivität WE-TCI**

description : **Thinfilm-Chip-Inductor WE-TCI**

DATUM / DATE : 2005-08-17

H Typical Frequency Characteristics



Freigabe erteilt / general release:	Kunde / customer		
Datum / date	Unterschrift / signature		
Geprüft / checked	Würth Elektronik		
Kontrolliert / approved	AWe	Version 2	05-08-17
	AWe	Version 1	04-10-11
	Name	Änderung / modification	Datum / date

This electronic component is designed and developed with the intention for use in general electronics equipments. Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body. In addition, even electronic component in general electrical equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before use. It is essential to give consideration when to install a protective circuit at the design stage.

Würth Elektronik eiSos GmbH & Co.KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 -3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400

<http://www.we-online.com>