

The Smart Choice

DECT 5 series is especially designed for people who have a keen preference for performance and quality. Simple and elegant, boosted with no nonsense features, this phone typifies the "smart choice"

Multi-pack for ultimate convenience

- Use 2 handsets in separate rooms to transmit noises
- Free intercom - free internal calls between handsets

Personalise Your Phone

- Download ringtones from dedicated sites
- Identify your friends by the ringtone

Great convenience

- Display for numbers, letters, icons and drawings
- 300-hours standby time autonomy
- Talk on the phone without holding the handset



PHILIPS

Technical specifications

Picture / Display

- **Display colours:** Black & White
- **Display technology:** Liquid Crystal Display
- **Main display resolution:** 108x65 pixel
- **Backlight**
- **Backlight colour:** Blue

Sound

- **Base station ringers:** Instrumental, Polyphonic, Recordable melody, Melody download
- **Handset ringers:** Instrumental, Polyphonic, Melody download
- **Volume Control:** Volume control up / down

Convenience

- **Alarms:** Alarm clock, Night Mode
- **Base station keys:** Answering machine keys, Paging key
- **Battery charging indication**
- **Call management:** Call waiting, Caller ID, Conference call, Explicit call transfer, Microphone mute
- **Ease of Use:** Hands free mode, Keypad lock, Menu control, Graphical user interface
- **Function:** Baby-sit function
- **Multi base capability:** 4
- **Multi handset capability:** Up to 6 handsets
- **Signal strength indication**
- **Text input:** Eatoni
- **VIP group with own melody:** Yes, 3 groups

Memory Capacity

- **Name & number shared phonebook:** 250 names and numbers
- **SMS storage capacity:** 60
- **Call log entries:** 40

Answering Machine

- Plug & Play answering machine
- **Recording time capacity:** 15 min
- VIP outgoing message
- Call screening
- Answerphone remote access

Dimensions

- **Handset dimensions:** 135 x 47 x 28 mm

Power

- **Battery type:** AAA
- **Battery type:** NiMH
- **Battery type:** Rechargeable
- **Mains power:** AC 220-240V - 50Hz
- **Number of batteries:** 2
- **Talk time:** 15 hours
- **Standby time:** 300 hours

Network Features

- **Antenna:** Integrated on base, Integrated on handset
- **Dialling:** Tone, Pulse
- **Messaging:** SMS (Short Message Service)

Green Specifications

- Green flagship

Product highlights

Ringtone download

This function offers the possibility to personalise your phone by downloading ringtones. Simply call the dedicated service provider and select your favourite song. An SMS is sent to you, together with the attached melody. You can select this melody as you would any other ringtones (country and network dependent).

VIP function

Identify who's calling by the ringtone! The VIP icons and melodies indicate to which group in the phonebook the caller belongs. Phonebook entries can be divided into different VIP groups for which you can allocate a specific ringtone.

Babysit function

Worried about your baby not sleeping? No need to constantly go and check in his bedroom. The baby-sit mode allows you to keep an ear listening wherever you are in the house.

Free intercom

No need to stop what you are doing and go to give the handset to your son when his friend calls: you can freely and easily call the handset in his bedroom and transfer the call.

Hands free on handset

The hands free speaker phone lets you hold a conversation while you're busy doing something else. With both the speaker and the microphone in front of the handset, it is just like talking face to face with your correspondent.

Full graphic display

This type of displays makes it easier to use your phone, thanks to the good quality and legibility of the characters. It also gives you more freedom of communication from your home. Now you can combine text with images or numbers.

300-hours standby autonomy

Leave your handset off the base for more than 12 days without the need to recharge it. This contributes to make a very environment friendly device.



Date of issue 2006-01-11

Version: 2.0

12 NC: 9961 400 04899
EAN: 87 10895 88868 4

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.
© 2006 Koninklijke Philips Electronics N.V.
All Rights reserved.
www.philips.com