**Screw Termination** 

# **D-ST SERIES**

#### **SPECIFICATIONS:**

# **MATERIALS AND PLATINGS**

Shells Steel Tin plated

Insulator Glass filled thermoplastic, UL94V-0
Contacts Machined brass, full gold

## **ELECTRICAL DATA**

Current Rating 7,5 A max.

Voltage Rating300 V RMS at 50 HzWithstanding Voltage1000 V RMS at 50 HzInsulation Resistance> 5000  $\Omega$  at 500 V DC

Contact Resistance < 5 9

#### CLIMATIC DATA

Damp Heat

Operating Temperature -67°F (-55°C) to +185°F (85°C),

peak at 257°F (125°C)

21 days 219°F(104°C - 95% HR)

Salt Spray 48 hours

## MECHANICAL DATA

Cable Type Solid or stranded

Cable Gauge 0,75 mm² max. (AWG 18)

- For bigger wire, please consult factory

Screw Torque 0,05 mN max.


Mating Cycles 100 (class II) or 500 (class I)





The Amphenol Screw Termination D-Sub series is especially designed for field applications.

These new connectors permit easy wiring without any specific tool; only a standard electrician's screwdriver is required. Due to their reduced overall dimensions, these connectors are compatible with all standard hoods and accessories.

- Industry control of speed variators and calculators.
- Houses and public buildings - control of heating, air conditioning, lighting, shutters and fire safety.
- Infrastructures fluids control, motorway tolls and street lighting.








SIZE	<b>A</b> +.010 (0.25) 010 (0.25)	<b>B</b> 0 008 (0.2)	+.008 (0.2)	+.004 (0.1) 004 (0.1)	<b>E</b> +.004 (0.1) 016 (0.4)
9	1.209	.646	.661	.984	.370
	(30.7)	(16.4)	(16.8)	(25)	(19.4)
15	1.535	.976	.988	1.311	1.091
	(39)	(24.8)	(25.1)	(33.3)	(27.7)
25	2.083	1.516	1.528	1.850	1.630
	(52.9)	(38.5)	(38.8)	(47)	(41.4)
37	2.724	2.161	2.177	2.500	2.280
	(69.2)	(54.9)	(55.3)	(63.5)	(57.9)

Screw Termination D-ST SERIES



# **PLASTIC HOODS**



DPPK Straight cable entry



DSSK Angled cable entry

# **METALLIC HOODS**



DTZK Straight cable entry



DVZK Angled cable entry

INCHES (MM)