


80 V, 120 °C

Applications

- Overcurrent protection
- Time delay
- Current stabilization

Features

- Thermistor chip with silver terminations
- Small size
- Short response times
- Suitable for reflow soldering, also for conductive adhesion
- Suitable for automatic placement
- Available on tape (standard delivery mode)



Termination

Dimensions (mm)
Tolerances (l, b, h) $\pm 0,2$ mm

Type	l	b	h	Size
A 1607	3,2	2,5	1,7	1210
A 1707	3,2	2,5	1,7	1210


Switching cycles (typ.)	N	100	
Reference temperature	T_{Ref}	120	°C
PTC temperature ($V = V_{max}$)	T_{PTC}	190	°C
Resistance tolerance	ΔR_N	$\pm 25\%$	
Operating temperature range ($V = 0$)	T_{op}	$-40/+125$	°C
	T_{op}	0/60	°C

Type	I_N ¹⁾ mA	I_S ¹⁾ mA	I_{Smax} ($V=V_{max}$) A	R_N Ω	R_{min} Ω	t_S s	Ordering code
$V_{max} = 80$ V, $V_N = 63$ V							
A 1707	45	90	0,3	125	75	< 2,5	B59707-A1120-A62
$V_{max} = 30$ V, $V_N = 24$ V							
A 1607	65	130	0,4	55	30	< 5,0	B59607-A1120-A62

¹⁾ Measured peak-to-peak

Characteristics (typical)

PTC resistance R_{PTC} versus
PTC temperature T_{PTC}
(measured at low signal voltage)



Rated current I_N versus ambient temperature T_A
(measured in still air)

